

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865486

Luminaire Tested: PRLX-2001-S-930-25L-G-U-S-X-X-GREY-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P865486  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-5)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2001-S-930-25L-G-U-S-X-X-GREY-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, GLOBE LENS,  
TAPERED DRUM WITH GRAY INTERIOR SHADE.  
LIGHT LEVEL 5  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 865.9 lumens  
Efficiency: N/A  
Efficacy: 29.8 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.37 / 1.55  
Luminous Opening: Circular (Dia: 0.92' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 29.1  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.5 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P865486

CATALOG NUMBER: PRLX-2001-S-930-25L-G-U-S-X-X-GREY-X

### Luminous Intensity Polar Plot



TEST NUMBER: P865486

CATALOG NUMBER: PRLX-2001-S-930-25L-G-U-S-X-X-GREY-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	107	102	97	93	105	100	95	91	95	92	88		91	88	86		88	85	83	81
2	97	88	80	74	94	86	79	73	82	76	71		79	74	70		76	72	68	66
3	88	76	67	60	85	75	66	60	71	64	59		69	63	58		66	61	56	54
4	80	67	57	50	77	65	57	50	63	55	49		60	54	48		58	52	48	45
5	73	59	50	43	71	58	49	42	56	48	42		54	47	41		52	46	41	39
6	67	53	43	37	65	52	43	37	50	42	36		48	41	36		47	40	35	33
7	62	48	39	32	60	47	38	32	45	37	32		44	37	31		42	36	31	29
8	58	43	34	28	56	43	34	28	41	34	28		40	33	28		39	32	28	26
9	54	40	31	25	52	39	31	25	38	30	25		37	30	25		36	29	25	23
10	50	36	28	23	49	36	28	23	35	28	23		34	27	22		33	27	22	21

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	3890
5°	3902
10°	3932
15°	3951
20°	3987
25°	4035
30°	4109
35°	4225
40°	4397
45°	4616
50°	4824
55°	4914
60°	4906
65°	4863
70°	4759
75°	4670
80°	4649
85°	5053

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 87.5°  
 Luminance: 6544 cd/sqm

TEST NUMBER: P865486

CATALOG NUMBER: PRLX-2001-S-930-25L-G-U-S-X-X-GREY-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	22.7	2.6
10°-20°	66.2	7.6
20°-30°	103.6	12.0
30°-40°	133.3	15.4
40°-50°	154.3	17.8
50°-60°	153.9	17.8
60°-70°	124.4	14.4
70°-80°	78.5	9.1
80°-90°	29.1	3.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	192.5	22.2
0°-40°	325.7	37.6
0°-60°	633.9	73.2
0°-90°	865.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	865.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	238	
5°	238	23
15°	234	66
25°	224	104
35°	212	133
45°	200	154
55°	173	154
65°	126	124
75°	74	78
85°	27	29
90°	0	

TEST NUMBER: P865486

CATALOG NUMBER: PRLX-2001-S-930-25L-G-U-S-X-X-GREY-X

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	238.5
2.5°	238.3
5°	238.3
7.5°	238.1
10°	237.4
12.5°	235.9
15°	234.0
17.5°	231.8
20°	229.7
22.5°	226.8
25°	224.2
27.5°	221.4
30°	218.2
32.5°	215.4
35°	212.2
37.5°	209.6
40°	206.5
42.5°	203.5
45°	200.1
47.5°	195.9
50°	190.1
52.5°	182.6
55°	172.8
57.5°	162.0
60°	150.4
62.5°	138.3
65°	126.0
67.5°	113.0
70°	99.8
72.5°	87.1
75°	74.1
77.5°	61.6
80°	49.5
82.5°	37.8
85°	27.0
87.5°	17.5
90°	0.0



TEST NUMBER: P865486  
 CATALOG NUMBER: PRLX-2001-S-930-25L-G-U-S-X-X-GREY-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.02	19.75	18.38	20.07	20.38	18.02	19.75	18.38	20.07	20.38
	3H	20.03	21.61	20.41	21.94	22.30	20.03	21.61	20.41	21.94	22.30
	4H	20.85	22.34	21.24	22.69	23.06	20.85	22.34	21.24	22.69	23.06
	6H	21.52	22.91	21.93	23.28	23.67	21.52	22.91	21.93	23.28	23.67
	8H	21.79	23.12	22.21	23.51	23.90	21.79	23.12	22.21	23.51	23.90
	12H	22.01	23.29	22.44	23.67	24.10	22.01	23.29	22.44	23.67	24.10
4H	2H	18.72	20.22	19.12	20.56	20.94	18.72	20.22	19.12	20.56	20.94
	3H	20.97	22.24	21.38	22.63	23.03	20.97	22.24	21.38	22.63	23.03
	4H	21.93	23.08	22.35	23.49	23.92	21.93	23.08	22.35	23.49	23.92
	6H	22.75	23.77	23.20	24.21	24.66	22.75	23.77	23.20	24.21	24.66
	8H	23.08	24.04	23.54	24.48	24.94	23.08	24.04	23.54	24.48	24.94
	12H	23.38	24.24	23.86	24.72	25.18	23.38	24.24	23.86	24.72	25.18
8H	4H	22.32	23.27	22.78	23.71	24.18	22.32	23.27	22.78	23.71	24.18
	6H	23.31	24.11	23.80	24.59	25.06	23.31	24.11	23.80	24.59	25.06
	8H	23.74	24.46	24.25	24.96	25.45	23.74	24.46	24.25	24.96	25.45
	12H	24.16	24.80	24.66	25.29	25.84	24.16	24.80	24.66	25.29	25.84
12H	4H	22.39	23.25	22.86	23.72	24.19	22.39	23.25	22.86	23.72	24.19
	6H	23.41	24.13	23.91	24.63	25.11	23.41	24.13	23.91	24.63	25.11
	8H	23.92	24.56	24.42	25.05	25.60	23.92	24.56	24.42	25.05	25.60