

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866553

Luminaire Tested: PRLX-2004-M-935-25L-L-U-S-X-X-BRSS-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P866553
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-55)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2004-M-935-25L-L-U-S-X-X-BRSS-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, FLAT LENS,
BELL WITH BRASS INTERIOR SHADE.
LIGHT LEVEL 3
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1309.2 lumens
Efficiency: N/A
Efficacy: 60.3 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 1
Luminous Opening: Circular (Dia: 1.31' x H: 0')
CIE Type: Direct

Input Watts (W): 21.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P866553

CATALOG NUMBER: PRLX-2004-M-935-25L-L-U-S-X-X-BRSS-X

Luminous Intensity Polar Plot





TEST NUMBER: P866553

CATALOG NUMBER: PRLX-2004-M-935-25L-L-U-S-X-X-BRSS-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	104	110	107	105	103	103	101	99	100	98	97	96	95	94	92
2	106	101	96	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77
4	95	87	80	76	93	85	80	75	83	78	74	81	77	74	79	76	73	71
5	90	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	66
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61
7	80	70	64	59	79	69	63	59	68	62	58	67	62	58	66	61	58	56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49
10	68	58	52	48	67	58	52	48	57	51	47	56	51	47	55	50	47	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	9758
5°	9416
10°	8949
15°	8577
20°	8253
25°	7914
30°	7578
35°	5706
40°	1923
45°	748
50°	663
55°	612
60°	562
65°	510
70°	475
75°	458
80°	435
85°	429

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 748 cd/sqm

TEST NUMBER: P866553

CATALOG NUMBER: PRLX-2004-M-935-25L-L-U-S-X-X-BRSS-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.3	8.4
10°-20°	293.3	22.4
20°-30°	415.2	31.7
30°-40°	336.9	25.7
40°-50°	66.2	5.1
50°-60°	39.5	3.0
60°-70°	27.2	2.1
70°-80°	15.7	1.2
80°-90°	5.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	818.8	62.5
0°-40°	1155.7	88.3
0°-60°	1261.4	96.3
0°-90°	1309.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1309.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1226	
5°	1179	110
15°	1041	293
25°	902	415
35°	588	337
45°	66	66
55°	44	39
65°	27	27
75°	15	16
85°	5	5
90°	0	

TEST NUMBER: P866553

CATALOG NUMBER: PRLX-2004-M-935-25L-L-U-S-X-X-BRSS-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	1226.5
2.5°	1215.0
5°	1179.0
7.5°	1142.4
10°	1107.8
12.5°	1074.6
15°	1041.3
17.5°	1008.8
20°	974.8
22.5°	938.2
25°	901.6
27.5°	865.6
30°	824.9
32.5°	750.3
35°	587.5
37.5°	356.8
40°	185.2
42.5°	104.5
45°	66.5
47.5°	57.7
50°	53.6
52.5°	48.8
55°	44.1
57.5°	39.3
60°	35.3
62.5°	31.2
65°	27.1
67.5°	23.7
70°	20.4
72.5°	17.6
75°	14.9
77.5°	12.2
80°	9.5
82.5°	6.8
85°	4.7
87.5°	2.0
90°	0.0



TEST NUMBER: P866553
 CATALOG NUMBER: PRLX-2004-M-935-25L-L-U-S-X-X-BRSS-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.09	6.15	5.46	6.46	6.78	5.09	6.15	5.46	6.46	6.78
	3H	6.59	7.52	6.97	7.86	8.22	6.59	7.52	6.97	7.86	8.22
	4H	7.20	8.06	7.61	8.42	8.81	7.20	8.06	7.61	8.42	8.81
	6H	7.68	8.47	8.10	8.85	9.24	7.68	8.47	8.10	8.85	9.24
	8H	7.84	8.59	8.27	8.98	9.39	7.84	8.59	8.27	8.98	9.39
	12H	7.96	8.67	8.39	9.05	9.48	7.96	8.67	8.39	9.05	9.48
4H	2H	5.53	6.40	5.94	6.75	7.14	5.53	6.40	5.94	6.75	7.14
	3H	7.25	7.96	7.67	8.37	8.77	7.25	7.96	7.67	8.37	8.77
	4H	7.99	8.63	8.43	9.05	9.50	7.99	8.63	8.43	9.05	9.50
	6H	8.61	9.16	9.08	9.60	10.08	8.61	9.16	9.08	9.60	10.08
	8H	8.82	9.32	9.29	9.77	10.25	8.82	9.32	9.29	9.77	10.25
	12H	8.98	9.42	9.47	9.91	10.39	8.98	9.42	9.47	9.91	10.39
8H	4H	8.22	8.73	8.70	9.18	9.66	8.22	8.73	8.70	9.18	9.66
	6H	8.99	9.39	9.49	9.89	10.38	8.99	9.39	9.49	9.89	10.38
	8H	9.28	9.64	9.81	10.16	10.66	9.28	9.64	9.81	10.16	10.66
	12H	9.55	9.86	10.07	10.35	10.93	9.55	9.86	10.07	10.35	10.93
12H	4H	8.23	8.67	8.72	9.16	9.63	8.23	8.67	8.72	9.16	9.63
	6H	9.03	9.39	9.56	9.91	10.40	9.03	9.39	9.56	9.91	10.40
	8H	9.38	9.69	9.90	10.19	10.77	9.38	9.69	9.90	10.19	10.77