

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865492

Luminaire Tested: PRLX-2001-S-935-05L-G-U-S-X-X-BLAK-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P865492  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-6)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2001-S-935-05L-G-U-S-X-X-BLAK-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, GLOBE LENS,  
TAPERED DRUM WITH BLACK INTERIOR SHADE.  
LIGHT LEVEL 1  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 152.0 lumens  
Efficiency: N/A  
Efficacy: 24.5 lumens/watt  
Spacing Criteria (0/90/45): 1.51 / 1.51 / 1.69  
Luminous Opening: Circular (Dia: 0.92' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 6.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.5 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P865492

CATALOG NUMBER: PRLX-2001-S-935-05L-G-U-S-X-X-BLAK-X

### Luminous Intensity Polar Plot





TEST NUMBER: P865492

CATALOG NUMBER: PRLX-2001-S-935-05L-G-U-S-X-X-BLAK-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	107	102	97	92	104	99	95	91	95	91	88		91	88	85		87	85	82	80
2	96	87	79	73	93	85	78	72	81	75	70		78	73	68		75	71	67	64
3	87	75	66	59	84	73	65	58	70	63	57		67	61	56		65	60	55	53
4	79	66	56	49	76	64	55	48	62	54	47		59	52	47		57	51	46	44
5	72	58	48	41	70	57	48	41	55	46	40		53	45	40		51	44	39	37
6	66	52	42	35	64	51	42	35	49	41	35		47	40	34		45	39	34	32
7	61	46	37	30	59	46	37	30	44	36	30		43	35	30		41	35	30	27
8	57	42	33	27	55	41	33	27	40	32	27		39	32	26		37	31	26	24
9	53	38	30	24	51	38	29	24	37	29	24		35	28	23		34	28	23	21
10	49	35	27	21	48	35	27	21	34	26	21		33	26	21		32	25	21	19

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	590
5°	594
10°	606
15°	618
20°	634
25°	653
30°	680
35°	715
40°	758
45°	814
50°	870
55°	899
60°	910
65°	903
70°	897
75°	876
80°	874
85°	973

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 87.5°  
 Luminance: 1234 cd/sqm

TEST NUMBER: P865492

CATALOG NUMBER: PRLX-2001-S-935-05L-G-U-S-X-X-BLAK-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	3.5	2.3
10°-20°	10.4	6.8
20°-30°	16.8	11.1
30°-40°	22.5	14.8
40°-50°	27.2	17.9
50°-60°	28.1	18.5
60°-70°	23.2	15.3
70°-80°	14.7	9.7
80°-90°	5.5	3.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	30.7	20.2
0°-40°	53.2	35.0
0°-60°	108.6	71.4
0°-90°	152.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	152.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	36	
5°	36	3
15°	37	10
25°	36	17
35°	36	23
45°	35	27
55°	32	28
65°	23	23
75°	14	15
85°	5	6
90°	0	

TEST NUMBER: P865492

CATALOG NUMBER: PRLX-2001-S-935-05L-G-U-S-X-X-BLAK-X

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	36.2
2.5°	36.2
5°	36.3
7.5°	36.5
10°	36.6
12.5°	36.6
15°	36.6
17.5°	36.6
20°	36.5
22.5°	36.5
25°	36.3
27.5°	36.2
30°	36.1
32.5°	36.0
35°	35.9
37.5°	35.7
40°	35.6
42.5°	35.5
45°	35.3
47.5°	35.0
50°	34.3
52.5°	33.2
55°	31.6
57.5°	29.8
60°	27.9
62.5°	25.7
65°	23.4
67.5°	21.2
70°	18.8
72.5°	16.3
75°	13.9
77.5°	11.6
80°	9.3
82.5°	7.2
85°	5.2
87.5°	3.3
90°	0.0



TEST NUMBER: P865492  
 CATALOG NUMBER: PRLX-2001-S-935-05L-G-U-S-X-X-BLAK-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.26	14.02	12.62	14.34	14.65	12.26	14.02	12.62	14.34	14.65
	3H	14.34	15.96	14.72	16.28	16.64	14.34	15.96	14.72	16.28	16.64
	4H	15.17	16.70	15.57	17.04	17.42	15.17	16.70	15.57	17.04	17.42
	6H	15.86	17.29	16.27	17.65	18.04	15.86	17.29	16.27	17.65	18.04
	8H	16.14	17.50	16.56	17.89	18.28	16.14	17.50	16.56	17.89	18.28
	12H	16.38	17.69	16.81	18.07	18.50	16.38	17.69	16.81	18.07	18.50
4H	2H	12.98	14.51	13.38	14.86	15.23	12.98	14.51	13.38	14.86	15.23
	3H	15.29	16.59	15.70	16.99	17.38	15.29	16.59	15.70	16.99	17.38
	4H	16.27	17.45	16.69	17.86	18.29	16.27	17.45	16.69	17.86	18.29
	6H	17.11	18.15	17.56	18.59	19.04	17.11	18.15	17.56	18.59	19.04
	8H	17.45	18.43	17.91	18.87	19.33	17.45	18.43	17.91	18.87	19.33
	12H	17.77	18.66	18.25	19.13	19.59	17.77	18.66	18.25	19.13	19.59
8H	4H	16.67	17.65	17.13	18.09	18.55	16.67	17.65	17.13	18.09	18.55
	6H	17.68	18.50	18.17	18.98	19.45	17.68	18.50	18.17	18.98	19.45
	8H	18.13	18.87	18.63	19.37	19.85	18.13	18.87	18.63	19.37	19.85
	12H	18.57	19.22	19.07	19.71	20.26	18.57	19.22	19.07	19.71	20.26
12H	4H	16.74	17.63	17.22	18.10	18.57	16.74	17.63	17.22	18.10	18.57
	6H	17.78	18.53	18.28	19.03	19.51	17.78	18.53	18.28	19.03	19.51
	8H	18.31	18.97	18.82	19.46	20.01	18.31	18.97	18.82	19.46	20.01