

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866593

Luminaire Tested: PRLX-2004-M-935-75L-L-U-S-X-X-BRSS-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P866593
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-55)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2004-M-935-75L-L-U-S-X-X-BRSS-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, FLAT LENS,
BELL WITH BRASS INTERIOR SHADE.
LIGHT LEVEL 8
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3927.8 lumens
Efficiency: N/A
Efficacy: 56.4 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 1
Luminous Opening: Circular (Dia: 1.31' x H: 0')
CIE Type: Direct

Input Watts (W): 69.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P866593

CATALOG NUMBER: PRLX-2004-M-935-75L-L-U-S-X-X-BRSS-X

Luminous Intensity Polar Plot





TEST NUMBER: P866593

CATALOG NUMBER: PRLX-2004-M-935-75L-L-U-S-X-X-BRSS-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	104	110	107	105	103	103	101	99	100	98	97	96	95	94	92
2	106	101	96	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77
4	95	87	80	76	93	85	80	75	83	78	74	81	77	74	79	76	73	71
5	90	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	66
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61
7	80	70	64	59	79	69	63	59	68	62	58	67	62	58	66	61	58	56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49
10	68	58	52	48	67	58	52	48	57	51	47	56	51	47	55	50	47	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	29274
5°	28248
10°	26848
15°	25731
20°	24760
25°	23742
30°	22735
35°	17118
40°	5770
45°	2243
50°	1990
55°	1835
60°	1683
65°	1532
70°	1421
75°	1377
80°	1306
85°	1296

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2243 cd/sqm

TEST NUMBER: P866593

CATALOG NUMBER: PRLX-2004-M-935-75L-L-U-S-X-X-BRSS-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	331.0	8.4
10°-20°	880.0	22.4
20°-30°	1245.6	31.7
30°-40°	1010.8	25.7
40°-50°	198.4	5.1
50°-60°	118.4	3.0
60°-70°	81.5	2.1
70°-80°	47.2	1.2
80°-90°	15.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2456.5	62.5
0°-40°	3467.2	88.3
0°-60°	3784.1	96.3
0°-90°	3927.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3927.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3680	
5°	3537	331
15°	3124	880
25°	2705	1246
35°	1762	1011
45°	199	198
55°	132	118
65°	81	82
75°	45	47
85°	14	15
90°	0	

TEST NUMBER: P866593

CATALOG NUMBER: PRLX-2004-M-935-75L-L-U-S-X-X-BRSS-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	3679.6
2.5°	3645.0
5°	3537.1
7.5°	3427.2
10°	3323.4
12.5°	3223.7
15°	3124.0
17.5°	3026.3
20°	2924.5
22.5°	2814.6
25°	2704.7
27.5°	2596.9
30°	2474.8
32.5°	2250.9
35°	1762.5
37.5°	1070.5
40°	555.6
42.5°	313.4
45°	199.4
47.5°	173.0
50°	160.8
52.5°	146.5
55°	132.3
57.5°	118.0
60°	105.8
62.5°	93.6
65°	81.4
67.5°	71.2
70°	61.1
72.5°	52.9
75°	44.8
77.5°	36.6
80°	28.5
82.5°	20.4
85°	14.2
87.5°	6.1
90°	0.0



TEST NUMBER: P866593
 CATALOG NUMBER: PRLX-2004-M-935-75L-L-U-S-X-X-BRSS-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.92	9.97	9.28	10.28	10.60	8.92	9.97	9.28	10.28	10.60
	3H	10.41	11.34	10.79	11.68	12.04	10.41	11.34	10.79	11.68	12.04
	4H	11.02	11.89	11.43	12.24	12.63	11.02	11.89	11.43	12.24	12.63
	6H	11.50	12.29	11.92	12.67	13.06	11.50	12.29	11.92	12.67	13.06
	8H	11.66	12.41	12.10	12.80	13.21	11.66	12.41	12.10	12.80	13.21
	12H	11.78	12.49	12.21	12.87	13.31	11.78	12.49	12.21	12.87	13.31
4H	2H	9.35	10.22	9.76	10.57	10.96	9.35	10.22	9.76	10.57	10.96
	3H	11.07	11.78	11.49	12.19	12.59	11.07	11.78	11.49	12.19	12.59
	4H	11.82	12.45	12.25	12.87	13.32	11.82	12.45	12.25	12.87	13.32
	6H	12.43	12.98	12.90	13.43	13.90	12.43	12.98	12.90	13.43	13.90
	8H	12.64	13.15	13.11	13.60	14.07	12.64	13.15	13.11	13.60	14.07
	12H	12.81	13.25	13.30	13.73	14.21	12.81	13.25	13.30	13.73	14.21
8H	4H	12.05	12.55	12.52	13.00	13.48	12.05	12.55	12.52	13.00	13.48
	6H	12.81	13.21	13.31	13.71	14.20	12.81	13.21	13.31	13.71	14.20
	8H	13.10	13.46	13.63	13.98	14.48	13.10	13.46	13.63	13.98	14.48
	12H	13.37	13.68	13.89	14.18	14.76	13.37	13.68	13.89	14.18	14.76
12H	4H	12.05	12.49	12.54	12.98	13.46	12.05	12.49	12.54	12.98	13.46
	6H	12.85	13.21	13.38	13.73	14.22	12.85	13.21	13.38	13.73	14.22
	8H	13.20	13.51	13.72	14.01	14.59	13.20	13.51	13.72	14.01	14.59