

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865530

Luminaire Tested: PRLX-2001-S-935-25L-L-U-S-X-X-GREY-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P865530  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-17)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2001-S-935-25L-L-U-S-X-X-GREY-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, FLAT LENS, TAPERED DRUM WITH GRAY INTERIOR SHADE.  
LIGHT LEVEL 5  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2117.7 lumens  
Efficiency: N/A  
Efficacy: 72.8 lumens/watt  
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.28  
Luminous Opening: Circular (Dia: 0.92' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 29.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.5 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P865530

CATALOG NUMBER: PRLX-2001-S-935-25L-L-U-S-X-X-GREY-X

### Luminous Intensity Polar Plot



TEST NUMBER: P865530

CATALOG NUMBER: PRLX-2001-S-935-25L-L-U-S-X-X-GREY-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89
2	103	96	91	86	101	94	89	85	91	87	83	88	84	81	85	82	80	78
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68
4	88	77	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52
6	75	63	55	50	74	62	55	49	61	54	49	59	53	49	58	52	48	46
7	70	58	50	44	68	57	49	44	56	49	44	54	48	43	53	47	43	41
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37
9	61	49	41	36	60	48	41	36	47	40	36	46	40	35	45	39	35	34
10	57	45	38	33	56	45	37	33	44	37	32	43	37	32	42	36	32	31

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	16491
5°	16443
10°	16259
15°	15926
20°	15586
25°	15225
30°	14824
35°	14322
40°	13822
45°	13304
50°	12684
55°	11770
60°	8338
65°	3057
70°	753
75°	712
80°	845
85°	842

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 13304 cd/sqm

TEST NUMBER: P865530

CATALOG NUMBER: PRLX-2001-S-935-25L-L-U-S-X-X-GREY-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	95.2	4.5
10°-20°	265.9	12.6
20°-30°	389.7	18.4
30°-40°	450.0	21.2
40°-50°	444.2	21.0
50°-60°	356.6	16.8
60°-70°	99.5	4.7
70°-80°	11.6	0.5
80°-90°	4.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	750.8	35.5
0°-40°	1200.8	56.7
0°-60°	2001.7	94.5
0°-90°	2117.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2117.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1011	
5°	1004	95
15°	943	266
25°	846	390
35°	719	450
45°	577	444
55°	414	357
65°	79	100
75°	11	12
85°	4	5
90°	0	

TEST NUMBER: P865530

CATALOG NUMBER: PRLX-2001-S-935-25L-L-U-S-X-X-GREY-X

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1011.1
2.5°	1011.1
5°	1004.3
7.5°	995.2
10°	981.7
12.5°	963.6
15°	943.2
17.5°	922.9
20°	898.0
22.5°	873.1
25°	846.0
27.5°	818.8
30°	787.1
32.5°	753.2
35°	719.3
37.5°	685.4
40°	649.2
42.5°	613.0
45°	576.8
47.5°	538.3
50°	499.9
52.5°	461.4
55°	413.9
57.5°	346.1
60°	255.6
62.5°	156.1
65°	79.2
67.5°	36.2
70°	15.8
72.5°	11.3
75°	11.3
77.5°	9.0
80°	9.0
82.5°	6.8
85°	4.5
87.5°	2.3
90°	0.0

TEST NUMBER: P865530  
 CATALOG NUMBER: PRLX-2001-S-935-25L-L-U-S-X-X-GREY-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	20.44	21.90	20.81	22.21	22.53	20.44	21.90	20.81	22.21	22.53
	3H	20.37	21.65	20.74	21.98	22.34	20.37	21.65	20.74	21.98	22.34
	4H	20.31	21.51	20.71	21.86	22.24	20.31	21.51	20.71	21.86	22.24
	6H	20.25	21.35	20.66	21.72	22.11	20.25	21.35	20.66	21.72	22.11
	8H	20.22	21.26	20.65	21.65	22.05	20.22	21.26	20.65	21.65	22.05
	12H	20.19	21.18	20.62	21.57	22.00	20.19	21.18	20.62	21.57	22.00
4H	2H	20.36	21.56	20.76	21.91	22.29	20.36	21.56	20.76	21.91	22.29
	3H	20.30	21.27	20.71	21.67	22.07	20.30	21.27	20.71	21.67	22.07
	4H	20.23	21.09	20.67	21.51	21.95	20.23	21.09	20.67	21.51	21.95
	6H	20.18	20.92	20.64	21.37	21.83	20.18	20.92	20.64	21.37	21.83
	8H	20.14	20.84	20.61	21.28	21.75	20.14	20.84	20.61	21.28	21.75
	12H	20.11	20.73	20.59	21.21	21.68	20.11	20.73	20.59	21.21	21.68
8H	4H	20.12	20.81	20.58	21.26	21.73	20.12	20.81	20.58	21.26	21.73
	6H	20.05	20.62	20.55	21.12	21.60	20.05	20.62	20.55	21.12	21.60
	8H	20.01	20.52	20.52	21.04	21.53	20.01	20.52	20.52	21.04	21.53
	12H	19.98	20.44	20.49	20.93	21.50	19.98	20.44	20.49	20.93	21.50
12H	4H	20.08	20.70	20.56	21.18	21.65	20.08	20.70	20.56	21.18	21.65
	6H	19.99	20.51	20.51	21.02	21.51	19.99	20.51	20.51	21.02	21.51
	8H	19.97	20.43	20.48	20.93	21.49	19.97	20.43	20.48	20.93	21.49