

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865547

Luminaire Tested: PRLX-2001-S-940-10L-L-U-S-X-X-WHHR-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P865547
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2001-S-940-10L-L-U-S-X-X-WHHR-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, FLAT LENS, TAPERED DRUM WITH WHITE INTERIOR SHADE.
LIGHT LEVEL 2
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1034.2 lumens
Efficiency: N/A
Efficacy: 98.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.31
Luminous Opening: Circular (Dia: 0.92' x H: 0')
CIE Type: Direct

Input Watts (W): 10.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P865547

CATALOG NUMBER: PRLX-2001-S-940-10L-L-U-S-X-X-WHHR-X

Luminous Intensity Polar Plot



TEST NUMBER: P865547

CATALOG NUMBER: PRLX-2001-S-940-10L-L-U-S-X-X-WHHR-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	106	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75
3	94	84	77	71	91	83	76	71	80	74	69	77	72	68	75	71	67	65
4	86	75	67	61	84	74	67	61	72	65	60	69	64	59	67	63	59	57
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50
6	74	61	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44
7	69	56	48	42	67	55	47	42	54	47	41	52	46	41	51	45	41	39
8	64	51	43	38	62	50	43	37	49	42	37	48	42	37	47	41	37	35
9	60	47	39	34	58	46	39	34	45	38	34	44	38	33	43	38	33	32
10	56	43	36	31	55	43	36	31	42	35	31	41	35	31	40	34	30	29

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	7372
5°	7369
10°	7299
15°	7220
20°	7097
25°	6956
30°	6820
35°	6652
40°	6475
45°	6302
50°	6102
55°	5667
60°	4365
65°	2312
70°	1340
75°	1355
80°	1493
85°	1759

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6302 cd/sqm

TEST NUMBER: P865547

CATALOG NUMBER: PRLX-2001-S-940-10L-L-U-S-X-X-WHHR-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.7	4.1
10°-20°	120.4	11.6
20°-30°	178.1	17.2
30°-40°	209.0	20.2
40°-50°	210.7	20.4
50°-60°	173.9	16.8
60°-70°	67.0	6.5
70°-80°	22.8	2.2
80°-90°	9.6	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	341.2	33.0
0°-40°	550.1	53.2
0°-60°	934.8	90.4
0°-90°	1034.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1034.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	452	
5°	450	43
15°	428	120
25°	386	178
35°	334	209
45°	273	211
55°	199	174
65°	60	67
75°	22	23
85°	9	10
90°	0	

TEST NUMBER: P865547

CATALOG NUMBER: PRLX-2001-S-940-10L-L-U-S-X-X-WHHR-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	452.0
2.5°	452.0
5°	450.1
7.5°	446.4
10°	440.7
12.5°	434.2
15°	427.6
17.5°	418.3
20°	408.9
22.5°	398.6
25°	386.5
27.5°	374.3
30°	362.1
32.5°	349.0
35°	334.1
37.5°	319.1
40°	304.1
42.5°	289.1
45°	273.2
47.5°	257.3
50°	240.5
52.5°	221.8
55°	199.3
57.5°	171.2
60°	133.8
62.5°	93.6
65°	59.9
67.5°	38.4
70°	28.1
72.5°	24.3
75°	21.5
77.5°	18.7
80°	15.9
82.5°	13.1
85°	9.4
87.5°	4.7
90°	0.0



TEST NUMBER: P865547
 CATALOG NUMBER: PRLX-2001-S-940-10L-L-U-S-X-X-WHHR-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.99	19.51	18.36	19.82	20.13	17.99	19.51	18.36	19.82	20.13
	3H	18.13	19.48	18.51	19.81	20.17	18.13	19.48	18.51	19.81	20.17
	4H	18.19	19.45	18.59	19.80	20.18	18.19	19.45	18.59	19.80	20.18
	6H	18.28	19.44	18.69	19.80	20.19	18.28	19.44	18.69	19.80	20.19
	8H	18.32	19.42	18.75	19.81	20.21	18.32	19.42	18.75	19.81	20.21
	12H	18.36	19.42	18.79	19.80	20.23	18.36	19.42	18.79	19.80	20.23
4H	2H	18.03	19.29	18.43	19.64	20.02	18.03	19.29	18.43	19.64	20.02
	3H	18.25	19.28	18.66	19.68	20.08	18.25	19.28	18.66	19.68	20.08
	4H	18.36	19.28	18.80	19.70	20.14	18.36	19.28	18.80	19.70	20.14
	6H	18.53	19.33	18.99	19.78	20.24	18.53	19.33	18.99	19.78	20.24
	8H	18.62	19.36	19.08	19.81	20.28	18.62	19.36	19.08	19.81	20.28
	12H	18.71	19.37	19.19	19.85	20.32	18.71	19.37	19.19	19.85	20.32
8H	4H	18.36	19.11	18.83	19.55	20.02	18.36	19.11	18.83	19.55	20.02
	6H	18.59	19.21	19.09	19.70	20.18	18.59	19.21	19.09	19.70	20.18
	8H	18.73	19.29	19.25	19.80	20.29	18.73	19.29	19.25	19.80	20.29
	12H	18.90	19.39	19.41	19.89	20.45	18.90	19.39	19.41	19.89	20.45
12H	4H	18.35	19.01	18.83	19.49	19.96	18.35	19.01	18.83	19.49	19.96
	6H	18.59	19.15	19.11	19.66	20.15	18.59	19.15	19.11	19.66	20.15
	8H	18.78	19.28	19.29	19.77	20.34	18.78	19.28	19.29	19.77	20.34