

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866618

Luminaire Tested: PRLX-2004-M-940-25L-L-U-S-X-X-GREY-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P866618  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-56)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2004-M-940-25L-L-U-S-X-X-GREY-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, FLAT LENS,  
BELL WITH GRAY INTERIOR SHADE.  
LIGHT LEVEL 3  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1374.5 lumens  
Efficiency: N/A  
Efficacy: 63.3 lumens/watt  
Spacing Criteria (0/90/45): 1.02 / 1.02 / 1  
Luminous Opening: Circular (Dia: 1.31' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 21.7  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.333 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P866618

CATALOG NUMBER: PRLX-2004-M-940-25L-L-U-S-X-X-GREY-X

### Luminous Intensity Polar Plot





TEST NUMBER: P866618

CATALOG NUMBER: PRLX-2004-M-940-25L-L-U-S-X-X-GREY-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84
3	101	93	88	84	98	92	87	83	89	85	82	87	83	80	85	82	79	77
4	95	87	81	76	93	85	80	76	83	78	75	81	77	74	79	76	73	71
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	74	71	67	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61
7	80	70	64	59	79	70	63	59	68	63	59	67	62	58	66	61	58	57
8	76	66	59	55	75	65	59	55	64	59	55	63	58	54	62	57	54	53
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	51	49
10	68	58	52	48	67	58	52	48	57	51	48	56	51	47	55	51	47	46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	10322
5°	9983
10°	9490
15°	9072
20°	8711
25°	8338
30°	7988
35°	6025
40°	2005
45°	744
50°	676
55°	617
60°	560
65°	514
70°	484
75°	464
80°	426
85°	393

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 744 cd/sqm

TEST NUMBER: P866618

CATALOG NUMBER: PRLX-2004-M-940-25L-L-U-S-X-X-GREY-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	116.9	8.5
10°-20°	310.2	22.6
20°-30°	437.7	31.8
30°-40°	353.7	25.7
40°-50°	67.7	4.9
50°-60°	40.0	2.9
60°-70°	27.4	2.0
70°-80°	15.9	1.2
80°-90°	5.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	864.8	62.9
0°-40°	1218.5	88.7
0°-60°	1326.3	96.5
0°-90°	1374.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1374.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1297	
5°	1250	117
15°	1101	310
25°	950	438
35°	620	354
45°	66	68
55°	44	40
65°	27	27
75°	15	16
85°	4	5
90°	0	

TEST NUMBER: P866618

CATALOG NUMBER: PRLX-2004-M-940-25L-L-U-S-X-X-GREY-X

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1297.4
2.5°	1285.9
5°	1250.0
7.5°	1210.6
10°	1174.7
12.5°	1137.3
15°	1101.4
17.5°	1066.2
20°	1028.9
22.5°	990.8
25°	949.9
27.5°	911.1
30°	869.5
32.5°	792.7
35°	620.4
37.5°	366.2
40°	193.1
42.5°	108.4
45°	66.1
47.5°	58.2
50°	54.6
52.5°	49.5
55°	44.5
57.5°	40.2
60°	35.2
62.5°	31.6
65°	27.3
67.5°	23.7
70°	20.8
72.5°	18.0
75°	15.1
77.5°	12.2
80°	9.3
82.5°	7.2
85°	4.3
87.5°	2.2
90°	0.0



TEST NUMBER: P866618  
 CATALOG NUMBER: PRLX-2004-M-940-25L-L-U-S-X-X-GREY-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.08	6.13	5.44	6.44	6.75	5.08	6.13	5.44	6.44	6.75
	3H	6.54	7.47	6.92	7.80	8.17	6.54	7.47	6.92	7.80	8.17
	4H	7.15	8.01	7.55	8.36	8.75	7.15	8.01	7.55	8.36	8.75
	6H	7.60	8.39	8.02	8.76	9.16	7.60	8.39	8.02	8.76	9.16
	8H	7.77	8.51	8.20	8.90	9.31	7.77	8.51	8.20	8.90	9.31
	12H	7.87	8.58	8.31	8.97	9.40	7.87	8.58	8.31	8.97	9.40
4H	2H	5.50	6.36	5.90	6.71	7.10	5.50	6.36	5.90	6.71	7.10
	3H	7.20	7.90	7.61	8.31	8.71	7.20	7.90	7.61	8.31	8.71
	4H	7.94	8.57	8.37	8.99	9.44	7.94	8.57	8.37	8.99	9.44
	6H	8.52	9.06	8.99	9.51	9.99	8.52	9.06	8.99	9.51	9.99
	8H	8.74	9.24	9.22	9.69	10.17	8.74	9.24	9.22	9.69	10.17
	12H	8.89	9.33	9.38	9.82	10.29	8.89	9.33	9.38	9.82	10.29
8H	4H	8.16	8.66	8.64	9.11	9.59	8.16	8.66	8.64	9.11	9.59
	6H	8.89	9.29	9.40	9.79	10.27	8.89	9.29	9.40	9.79	10.27
	8H	9.20	9.55	9.73	10.08	10.57	9.20	9.55	9.73	10.08	10.57
	12H	9.44	9.75	9.96	10.25	10.83	9.44	9.75	9.96	10.25	10.83
12H	4H	8.16	8.60	8.65	9.09	9.56	8.16	8.60	8.65	9.09	9.56
	6H	8.93	9.28	9.46	9.81	10.30	8.93	9.28	9.46	9.81	10.30
	8H	9.30	9.61	9.82	10.11	10.69	9.30	9.61	9.82	10.11	10.69