

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866621

Luminaire Tested: PRLX-2004-M-940-35L-G-U-S-X-X-BRSS-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P866621
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-43)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2004-M-940-35L-G-U-S-X-X-BRSS-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, GLOBE LENS,
BELL WITH BRASS INTERIOR SHADE.
LIGHT LEVEL 4
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 749.5 lumens
Efficiency: N/A
Efficacy: 25.0 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.14
Luminous Opening: Circular (Dia: 1.31' x H: 0')
CIE Type: Direct

Input Watts (W): 30
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P866621

CATALOG NUMBER: PRLX-2004-M-940-35L-G-U-S-X-X-BRSS-X

Luminous Intensity Polar Plot





TEST NUMBER: P866621

CATALOG NUMBER: PRLX-2004-M-940-35L-G-U-S-X-X-BRSS-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90
2	105	99	94	89	102	97	92	88	93	90	86	90	87	84	88	85	83	81
3	98	90	84	79	96	88	83	78	86	81	77	83	79	75	81	77	74	72
4	91	82	75	70	89	81	74	70	79	73	69	76	72	68	74	70	67	65
5	85	75	68	63	84	74	67	62	72	66	62	70	65	61	69	64	61	59
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53
7	75	64	57	52	74	63	56	51	62	56	51	60	55	51	59	54	50	49
8	71	59	52	47	69	59	52	47	57	51	47	56	51	46	55	50	46	45
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41
10	63	51	44	40	62	51	44	40	50	44	40	49	43	39	48	43	39	38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3734
5°	3733
10°	3719
15°	3692
20°	3625
25°	3538
30°	3371
35°	2958
40°	2422
45°	1798
50°	1157
55°	627
60°	465
65°	397
70°	351
75°	310
80°	275
85°	274

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1798 cd/sqm

TEST NUMBER: P866621

CATALOG NUMBER: PRLX-2004-M-940-35L-G-U-S-X-X-BRSS-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.4	5.9
10°-20°	126.2	16.8
20°-30°	184.9	24.7
30°-40°	188.8	25.2
40°-50°	123.4	16.5
50°-60°	45.9	6.1
60°-70°	21.4	2.9
70°-80°	11.0	1.5
80°-90°	3.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	355.5	47.4
0°-40°	544.3	72.6
0°-60°	713.6	95.2
0°-90°	749.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	749.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	469	
5°	467	44
15°	448	126
25°	403	185
35°	305	189
45°	160	123
55°	45	46
65°	21	21
75°	10	11
85°	3	4
90°	0	

TEST NUMBER: P866621

CATALOG NUMBER: PRLX-2004-M-940-35L-G-U-S-X-X-BRSS-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	469.4
2.5°	468.4
5°	467.4
7.5°	464.4
10°	460.4
12.5°	455.4
15°	448.3
17.5°	439.3
20°	428.2
22.5°	416.2
25°	403.1
27.5°	388.0
30°	366.9
32.5°	338.8
35°	304.6
37.5°	269.4
40°	233.2
42.5°	196.0
45°	159.8
47.5°	125.7
50°	93.5
52.5°	66.3
55°	45.2
57.5°	34.2
60°	29.2
62.5°	25.1
65°	21.1
67.5°	18.1
70°	15.1
72.5°	13.1
75°	10.1
77.5°	8.0
80°	6.0
82.5°	5.0
85°	3.0
87.5°	2.0
90°	0.0

TEST NUMBER: P866621
 CATALOG NUMBER: PRLX-2004-M-940-35L-G-U-S-X-X-BRSS-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.79	7.05	6.15	7.36	7.67	5.79	7.05	6.15	7.36	7.67
	3H	6.98	8.09	7.36	8.42	8.79	6.98	8.09	7.36	8.42	8.79
	4H	7.42	8.46	7.83	8.81	9.19	7.42	8.46	7.83	8.81	9.19
	6H	7.73	8.67	8.14	9.05	9.44	7.73	8.67	8.14	9.05	9.44
	8H	7.85	8.75	8.28	9.14	9.55	7.85	8.75	8.28	9.14	9.55
	12H	7.94	8.79	8.37	9.18	9.61	7.94	8.79	8.37	9.18	9.61
4H	2H	6.15	7.19	6.56	7.54	7.92	6.15	7.19	6.56	7.54	7.92
	3H	7.57	8.41	7.98	8.82	9.22	7.57	8.41	7.98	8.82	9.22
	4H	8.12	8.87	8.55	9.29	9.73	8.12	8.87	8.55	9.29	9.73
	6H	8.53	9.18	9.00	9.63	10.10	8.53	9.18	9.00	9.63	10.10
	8H	8.71	9.31	9.18	9.76	10.23	8.71	9.31	9.18	9.76	10.23
	12H	8.84	9.37	9.33	9.86	10.33	8.84	9.37	9.33	9.86	10.33
8H	4H	8.28	8.88	8.75	9.33	9.80	8.28	8.88	8.75	9.33	9.80
	6H	8.81	9.30	9.31	9.80	10.28	8.81	9.30	9.31	9.80	10.28
	8H	9.07	9.51	9.59	10.03	10.52	9.07	9.51	9.59	10.03	10.52
	12H	9.28	9.68	9.80	10.17	10.74	9.28	9.68	9.80	10.17	10.74
12H	4H	8.27	8.81	8.76	9.29	9.77	8.27	8.81	8.76	9.29	9.77
	6H	8.83	9.27	9.35	9.79	10.28	8.83	9.27	9.35	9.79	10.28
	8H	9.15	9.54	9.67	10.04	10.61	9.15	9.54	9.67	10.04	10.61