

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865566

Luminaire Tested: PRLX-2001-S-940-25L-G-U-S-X-X-GREY-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P865566
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2001-S-940-25L-G-U-S-X-X-GREY-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, GLOBE LENS,
TAPERED DRUM WITH GRAY INTERIOR SHADE.
LIGHT LEVEL 5
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 937.5 lumens
Efficiency: N/A
Efficacy: 32.2 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.37 / 1.55
Luminous Opening: Circular (Dia: 0.92' x H: 0')
CIE Type: Direct

Input Watts (W): 29.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P865566

CATALOG NUMBER: PRLX-2001-S-940-25L-G-U-S-X-X-GREY-X

Luminous Intensity Polar Plot





TEST NUMBER: P865566

CATALOG NUMBER: PRLX-2001-S-940-25L-G-U-S-X-X-GREY-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	107	102	97	93	105	100	95	91	95	92	88		91	88	86		88	85	83	81
2	97	88	80	74	94	86	79	73	82	76	71		79	74	70		76	72	68	66
3	88	76	67	60	85	75	66	60	71	64	59		69	63	58		66	61	56	54
4	80	67	57	50	77	65	57	50	63	55	49		60	54	48		58	52	48	45
5	73	59	50	43	71	58	49	42	56	48	42		54	47	41		52	46	41	39
6	67	53	44	37	65	52	43	37	50	42	36		48	41	36		47	40	35	33
7	62	48	39	32	60	47	38	32	45	37	32		44	37	31		42	36	31	29
8	58	43	34	28	56	43	34	28	41	34	28		40	33	28		39	32	28	26
9	54	40	31	25	52	39	31	25	38	30	25		37	30	25		36	29	25	23
10	50	36	28	23	49	36	28	23	35	28	23		34	27	22		33	27	22	21

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4213
5°	4224
10°	4258
15°	4279
20°	4317
25°	4369
30°	4450
35°	4574
40°	4761
45°	4996
50°	5225
55°	5320
60°	5311
65°	5264
70°	5155
75°	5054
80°	5034
85°	5464

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 87.5°
 Luminance: 7067 cd/sqm

TEST NUMBER: P865566

CATALOG NUMBER: PRLX-2001-S-940-25L-G-U-S-X-X-GREY-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	24.6	2.6
10°-20°	71.6	7.6
20°-30°	112.2	12.0
30°-40°	144.3	15.4
40°-50°	167.1	17.8
50°-60°	166.6	17.8
60°-70°	134.6	14.4
70°-80°	85.0	9.1
80°-90°	31.5	3.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	208.4	22.2
0°-40°	352.7	37.6
0°-60°	686.4	73.2
0°-90°	937.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	937.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	258	
5°	258	25
15°	253	72
25°	243	112
35°	230	144
45°	217	167
55°	187	167
65°	136	135
75°	80	85
85°	29	32
90°	0	

TEST NUMBER: P865566

CATALOG NUMBER: PRLX-2001-S-940-25L-G-U-S-X-X-GREY-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	258.3
2.5°	258.0
5°	258.0
7.5°	257.8
10°	257.1
12.5°	255.5
15°	253.4
17.5°	251.0
20°	248.7
22.5°	245.6
25°	242.8
27.5°	239.8
30°	236.3
32.5°	233.2
35°	229.7
37.5°	226.9
40°	223.6
42.5°	220.4
45°	216.6
47.5°	212.2
50°	205.9
52.5°	197.7
55°	187.1
57.5°	175.5
60°	162.8
62.5°	149.7
65°	136.4
67.5°	122.3
70°	108.1
72.5°	94.3
75°	80.2
77.5°	66.7
80°	53.6
82.5°	40.9
85°	29.2
87.5°	18.9
90°	0.0



TEST NUMBER: P865566
 CATALOG NUMBER: PRLX-2001-S-940-25L-G-U-S-X-X-GREY-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.30	20.03	18.66	20.35	20.66	18.30	20.03	18.66	20.35	20.66
	3H	20.31	21.89	20.69	22.22	22.57	20.31	21.89	20.69	22.22	22.57
	4H	21.12	22.62	21.52	22.96	23.34	21.12	22.62	21.52	22.96	23.34
	6H	21.80	23.19	22.21	23.55	23.94	21.80	23.19	22.21	23.55	23.94
	8H	22.06	23.40	22.49	23.78	24.18	22.06	23.40	22.49	23.78	24.18
	12H	22.29	23.57	22.72	23.95	24.38	22.29	23.57	22.72	23.95	24.38
4H	2H	19.00	20.50	19.40	20.84	21.22	19.00	20.50	19.40	20.84	21.22
	3H	21.25	22.51	21.65	22.91	23.31	21.25	22.51	21.65	22.91	23.31
	4H	22.20	23.35	22.63	23.77	24.20	22.20	23.35	22.63	23.77	24.20
	6H	23.03	24.04	23.48	24.48	24.93	23.03	24.04	23.48	24.48	24.93
	8H	23.36	24.31	23.82	24.75	25.22	23.36	24.31	23.82	24.75	25.22
	12H	23.66	24.52	24.14	24.99	25.46	23.66	24.52	24.14	24.99	25.46
8H	4H	22.60	23.55	23.05	23.99	24.45	22.60	23.55	23.05	23.99	24.45
	6H	23.58	24.38	24.07	24.87	25.34	23.58	24.38	24.07	24.87	25.34
	8H	24.02	24.74	24.52	25.24	25.72	24.02	24.74	24.52	25.24	25.72
	12H	24.43	25.07	24.94	25.56	26.12	24.43	25.07	24.94	25.56	26.12
12H	4H	22.66	23.52	23.14	24.00	24.46	22.66	23.52	23.14	24.00	24.46
	6H	23.68	24.41	24.19	24.91	25.39	23.68	24.41	24.19	24.91	25.39
	8H	24.20	24.84	24.70	25.32	25.88	24.20	24.84	24.70	25.32	25.88