

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866655

Luminaire Tested: PRLX-2004-M-940-75L-G-U-S-X-X-WHHR-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P866655  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-42)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2004-M-940-75L-G-U-S-X-X-WHHR-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, GLOBE LENS,  
BELL WITH WHITE INTERIOR SHADE.  
LIGHT LEVEL 8  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4858.6 lumens  
Efficiency: N/A  
Efficacy: 69.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.2  
Luminous Opening: Circular (Dia: 1.31' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 69.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.5 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P866655

CATALOG NUMBER: PRLX-2004-M-940-75L-G-U-S-X-X-WHHR-X

### Luminous Intensity Polar Plot





TEST NUMBER: P866655

CATALOG NUMBER: PRLX-2004-M-940-75L-G-U-S-X-X-WHHR-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	89	87
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	79	77	75
3	94	84	77	71	91	83	76	70	80	74	69	77	72	68	75	70	67	65
4	87	76	68	62	84	74	67	61	72	66	60	70	64	60	68	63	59	57
5	80	69	60	54	78	67	60	54	65	59	53	64	58	53	62	57	52	50
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40
8	65	53	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37
9	61	49	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33
10	57	45	38	33	56	45	37	33	44	37	32	43	37	32	42	36	32	31

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	18405
5°	18458
10°	18497
15°	18469
20°	18401
25°	18190
30°	17236
35°	15628
40°	13825
45°	11996
50°	10211
55°	8575
60°	7642
65°	7097
70°	6664
75°	6357
80°	6116
85°	5897

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 11996 cd/sqm

TEST NUMBER: P866655

CATALOG NUMBER: PRLX-2004-M-940-75L-G-U-S-X-X-WHHR-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	219.9	4.5
10°-20°	633.0	13.0
20°-30°	946.2	19.5
30°-40°	1004.2	20.7
40°-50°	824.8	17.0
50°-60°	564.2	11.6
60°-70°	375.1	7.7
70°-80°	219.6	4.5
80°-90°	71.5	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1799.1	37.0
0°-40°	2803.3	57.7
0°-60°	4192.4	86.3
0°-90°	4858.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4858.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2313	
5°	2311	220
15°	2242	633
25°	2072	946
35°	1609	1004
45°	1066	825
55°	618	564
65°	377	375
75°	207	220
85°	65	71
90°	0	

TEST NUMBER: P866655

CATALOG NUMBER: PRLX-2004-M-940-75L-G-U-S-X-X-WHHR-X

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2313.4
2.5°	2313.4
5°	2311.3
7.5°	2302.6
10°	2289.7
12.5°	2270.3
15°	2242.3
17.5°	2212.2
20°	2173.4
22.5°	2130.3
25°	2072.2
27.5°	1983.9
30°	1876.2
32.5°	1753.4
35°	1609.1
37.5°	1471.2
40°	1331.2
42.5°	1195.5
45°	1066.2
47.5°	947.8
50°	825.0
52.5°	715.1
55°	618.2
57.5°	542.8
60°	480.3
62.5°	426.5
65°	377.0
67.5°	329.6
70°	286.5
72.5°	245.6
75°	206.8
77.5°	170.2
80°	133.5
82.5°	99.1
85°	64.6
87.5°	32.3
90°	0.0



TEST NUMBER: P866655  
 CATALOG NUMBER: PRLX-2004-M-940-75L-G-U-S-X-X-WHHR-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.25	19.72	18.61	20.03	20.35	18.25	19.72	18.61	20.03	20.35
	3H	19.83	21.15	20.21	21.48	21.84	19.83	21.15	20.21	21.48	21.84
	4H	20.47	21.71	20.87	22.06	22.44	20.47	21.71	20.87	22.06	22.44
	6H	20.99	22.14	21.40	22.50	22.90	20.99	22.14	21.40	22.50	22.90
	8H	21.18	22.27	21.61	22.66	23.06	21.18	22.27	21.61	22.66	23.06
	12H	21.32	22.37	21.75	22.75	23.18	21.32	22.37	21.75	22.75	23.18
4H	2H	18.77	20.01	19.17	20.36	20.74	18.77	20.01	19.17	20.36	20.74
	3H	20.60	21.62	21.01	22.02	22.43	20.60	21.62	21.01	22.02	22.43
	4H	21.37	22.30	21.81	22.72	23.16	21.37	22.30	21.81	22.72	23.16
	6H	22.04	22.85	22.50	23.29	23.75	22.04	22.85	22.50	23.29	23.75
	8H	22.29	23.04	22.75	23.48	23.95	22.29	23.04	22.75	23.48	23.95
	12H	22.48	23.15	22.97	23.63	24.11	22.48	23.15	22.97	23.63	24.11
8H	4H	21.67	22.42	22.13	22.86	23.33	21.67	22.42	22.13	22.86	23.33
	6H	22.47	23.10	22.97	23.59	24.07	22.47	23.10	22.97	23.59	24.07
	8H	22.81	23.37	23.32	23.88	24.37	22.81	23.37	23.32	23.88	24.37
	12H	23.10	23.59	23.61	24.09	24.65	23.10	23.59	23.61	24.09	24.65
12H	4H	21.70	22.37	22.18	22.85	23.32	21.70	22.37	22.18	22.85	23.32
	6H	22.54	23.10	23.05	23.61	24.10	22.54	23.10	23.05	23.61	24.10
	8H	22.94	23.43	23.45	23.93	24.49	22.94	23.43	23.45	23.93	24.49