

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866990

Luminaire Tested: PRLX-2002-L-930-117L-L-X-X-GREY-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P866990  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-82)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2002-L-930-117L-L-X-X-GREY-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, FLAT LENS, TRUNCATED DOME WITH GRAY INTERIOR SHADE.  
LIGHT LEVEL 7  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9593.7 lumens  
Efficiency: N/A  
Efficacy: 100.8 lumens/watt  
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.27  
Luminous Opening: Circular (Dia: 1.67' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 95.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.5 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P866990

CATALOG NUMBER: PRLX-2002-L-930-117L-L-X-X-GREY-X

### Luminous Intensity Polar Plot





TEST NUMBER: P866990

CATALOG NUMBER: PRLX-2002-L-930-117L-L-X-X-GREY-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	90
2	104	97	92	87	101	95	91	86	92	88	84	89	86	83	86	83	81	79
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	71	69
4	89	79	72	66	87	78	71	66	75	70	65	73	68	64	71	67	63	61
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54
6	77	65	57	52	75	64	57	52	63	56	51	61	55	51	60	54	50	48
7	72	60	52	46	70	59	51	46	57	51	46	56	50	46	55	49	45	43
8	67	55	47	42	65	54	47	42	53	46	41	52	46	41	50	45	41	39
9	63	50	43	38	61	50	43	38	49	42	38	48	42	37	47	41	37	36
10	59	47	39	35	58	46	39	34	45	39	34	44	38	34	43	38	34	32

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	24083
5°	24011
10°	23744
15°	23364
20°	22938
25°	22434
30°	21802
35°	21030
40°	20023
45°	18790
50°	17316
55°	13765
60°	6479
65°	2340
70°	900
75°	999
80°	1145
85°	1370

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 18790 cd/sqm

TEST NUMBER: P866990

CATALOG NUMBER: PRLX-2002-L-930-117L-L-X-X-GREY-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	459.3	4.8
10°-20°	1289.0	13.4
20°-30°	1896.1	19.8
30°-40°	2178.3	22.7
40°-50°	2074.8	21.6
50°-60°	1364.4	14.2
60°-70°	252.0	2.6
70°-80°	55.0	0.6
80°-90°	24.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3644.4	38.0
0°-40°	5822.8	60.7
0°-60°	9262.0	96.5
0°-90°	9593.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9593.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4881	
5°	4848	459
15°	4574	1289
25°	4121	1896
35°	3492	2178
45°	2693	2075
55°	1600	1364
65°	200	252
75°	52	55
85°	24	25
90°	0	

TEST NUMBER: P866990

CATALOG NUMBER: PRLX-2002-L-930-117L-L-X-X-GREY-X

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4881.3
2.5°	4876.3
5°	4848.1
7.5°	4802.8
10°	4739.3
12.5°	4661.8
15°	4574.1
17.5°	4475.5
20°	4368.7
22.5°	4249.9
25°	4121.0
27.5°	3980.0
30°	3826.9
32.5°	3662.7
35°	3491.5
37.5°	3304.2
40°	3108.8
42.5°	2908.4
45°	2692.9
47.5°	2479.4
50°	2255.9
52.5°	1994.0
55°	1600.2
57.5°	1096.7
60°	656.6
62.5°	369.6
65°	200.4
67.5°	100.7
70°	62.4
72.5°	57.4
75°	52.4
77.5°	47.3
80°	40.3
82.5°	33.2
85°	24.2
87.5°	13.1
90°	0.0



TEST NUMBER: P866990  
 CATALOG NUMBER: PRLX-2002-L-930-117L-L-X-X-GREY-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.05	20.45	19.41	20.76	21.08	19.05	20.45	19.41	20.76	21.08
	3H	18.96	20.20	19.34	20.53	20.89	18.96	20.20	19.34	20.53	20.89
	4H	18.91	20.06	19.32	20.41	20.79	18.91	20.06	19.32	20.41	20.79
	6H	18.87	19.92	19.28	20.29	20.68	18.87	19.92	19.28	20.29	20.68
	8H	18.84	19.84	19.27	20.23	20.63	18.84	19.84	19.27	20.23	20.63
	12H	18.82	19.77	19.25	20.15	20.58	18.82	19.77	19.25	20.15	20.58
4H	2H	18.92	20.07	19.32	20.42	20.80	18.92	20.07	19.32	20.42	20.80
	3H	18.85	19.78	19.26	20.18	20.58	18.85	19.78	19.26	20.18	20.58
	4H	18.80	19.62	19.24	20.04	20.48	18.80	19.62	19.24	20.04	20.48
	6H	18.77	19.48	19.23	19.92	20.39	18.77	19.48	19.23	19.92	20.39
	8H	18.74	19.40	19.21	19.85	20.32	18.74	19.40	19.21	19.85	20.32
	12H	18.72	19.31	19.21	19.79	20.27	18.72	19.31	19.21	19.79	20.27
8H	4H	18.69	19.35	19.16	19.80	20.27	18.69	19.35	19.16	19.80	20.27
	6H	18.65	19.20	19.15	19.69	20.17	18.65	19.20	19.15	19.69	20.17
	8H	18.63	19.12	19.15	19.64	20.13	18.63	19.12	19.15	19.64	20.13
	12H	18.62	19.07	19.14	19.56	20.13	18.62	19.07	19.14	19.56	20.13
12H	4H	18.65	19.23	19.13	19.72	20.19	18.65	19.23	19.13	19.72	20.19
	6H	18.59	19.09	19.11	19.60	20.10	18.59	19.09	19.11	19.60	20.10
	8H	18.60	19.04	19.11	19.53	20.10	18.60	19.04	19.11	19.53	20.10