

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P867052

Luminaire Tested: PRLX-2002-L-935-117L-L-X-X-BLAK-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P867052  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-83)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2002-L-935-117L-L-X-X-BLAK-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, FLAT LENS, TRUNCATED DOME WITH BLACK INTERIOR SHADE.  
LIGHT LEVEL 7  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9175.1 lumens  
Efficiency: N/A  
Efficacy: 96.4 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.27  
Luminous Opening: Circular (Dia: 1.67' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 95.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.5 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P867052

CATALOG NUMBER: PRLX-2002-L-935-117L-L-X-X-BLAK-X

### Luminous Intensity Polar Plot





TEST NUMBER: P867052

CATALOG NUMBER: PRLX-2002-L-935-117L-L-X-X-BLAK-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	105	103	109	106	104	101	102	100	98	98	97	95	95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	79	76	73	71
4	90	80	73	68	88	79	72	67	77	71	66	75	70	66	73	68	65	63
5	84	73	65	60	82	72	65	60	70	64	59	68	63	58	66	62	58	56
6	78	66	59	53	76	66	58	53	64	57	53	62	57	52	61	56	52	50
7	73	61	53	48	71	60	53	48	59	52	47	57	51	47	56	51	47	45
8	68	56	48	43	66	55	48	43	54	47	43	53	47	43	52	46	42	41
9	64	52	44	39	62	51	44	39	50	43	39	49	43	39	48	43	39	37
10	60	48	41	36	59	47	40	36	46	40	36	45	40	35	45	39	35	34

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	23934
5°	23866
10°	23610
15°	23259
20°	22853
25°	22387
30°	21780
35°	20995
40°	19951
45°	18681
50°	17028
55°	11385
60°	4046
65°	935
70°	150
75°	158
80°	207
85°	238

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 18681 cd/sqm

TEST NUMBER: P867052

CATALOG NUMBER: PRLX-2002-L-935-117L-L-X-X-BLAK-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	456.6	5.0
10°-20°	1283.3	14.0
20°-30°	1892.4	20.6
30°-40°	2174.6	23.7
40°-50°	2058.8	22.4
50°-60°	1172.2	12.8
60°-70°	124.3	1.4
70°-80°	8.9	0.1
80°-90°	4.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3632.2	39.6
0°-40°	5806.9	63.3
0°-60°	9037.8	98.5
0°-90°	9175.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9175.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4851	
5°	4819	457
15°	4554	1283
25°	4112	1892
35°	3486	2175
45°	2677	2059
55°	1324	1172
65°	80	124
75°	8	9
85°	4	4
90°	0	

TEST NUMBER: P867052

CATALOG NUMBER: PRLX-2002-L-935-117L-L-X-X-BLAK-X

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4851.0
2.5°	4845.8
5°	4818.8
7.5°	4774.0
10°	4712.7
12.5°	4637.7
15°	4553.5
17.5°	4457.7
20°	4352.6
22.5°	4238.2
25°	4112.3
27.5°	3977.0
30°	3823.0
32.5°	3660.7
35°	3485.8
37.5°	3296.5
40°	3097.7
42.5°	2896.9
45°	2677.3
47.5°	2449.5
50°	2218.5
52.5°	1873.0
55°	1323.6
57.5°	789.8
60°	410.0
62.5°	205.0
65°	80.1
67.5°	15.6
70°	10.4
72.5°	9.4
75°	8.3
77.5°	7.3
80°	7.3
82.5°	5.2
85°	4.2
87.5°	2.1
90°	0.0

TEST NUMBER: P867052

CATALOG NUMBER: PRLX-2002-L-935-117L-L-X-X-BLAK-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.93	18.29	17.29	18.60	18.92	16.93	18.29	17.29	18.60	18.92
	3H	16.80	18.00	17.18	18.33	18.69	16.80	18.00	17.18	18.33	18.69
	4H	16.73	17.84	17.14	18.19	18.57	16.73	17.84	17.14	18.19	18.57
	6H	16.66	17.67	17.07	18.04	18.44	16.66	17.67	17.07	18.04	18.44
	8H	16.62	17.58	17.05	17.97	18.37	16.62	17.58	17.05	17.97	18.37
	12H	16.58	17.49	17.01	17.88	18.31	16.58	17.49	17.01	17.88	18.31
4H	2H	16.75	17.86	17.16	18.21	18.60	16.75	17.86	17.16	18.21	18.60
	3H	16.63	17.52	17.04	17.92	18.33	16.63	17.52	17.04	17.92	18.33
	4H	16.55	17.33	16.98	17.75	18.20	16.55	17.33	16.98	17.75	18.20
	6H	16.47	17.15	16.93	17.59	18.06	16.47	17.15	16.93	17.59	18.06
	8H	16.41	17.04	16.88	17.49	17.96	16.41	17.04	16.88	17.49	17.96
	12H	16.36	16.92	16.85	17.41	17.88	16.36	16.92	16.85	17.41	17.88
8H	4H	16.41	17.04	16.88	17.49	17.96	16.41	17.04	16.88	17.49	17.96
	6H	16.30	16.82	16.80	17.32	17.80	16.30	16.82	16.80	17.32	17.80
	8H	16.23	16.71	16.76	17.23	17.72	16.23	16.71	16.76	17.23	17.72
	12H	16.19	16.61	16.70	17.11	17.68	16.19	16.61	16.70	17.11	17.68
12H	4H	16.36	16.92	16.84	17.40	17.88	16.36	16.92	16.84	17.40	17.88
	6H	16.23	16.71	16.76	17.22	17.72	16.23	16.71	16.76	17.22	17.72
	8H	16.18	16.61	16.70	17.10	17.68	16.18	16.61	16.70	17.10	17.68