

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P867054

Luminaire Tested: PRLX-2002-L-935-117L-L-X-X-GREY-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P867054  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-82)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Pentalux  
Catalog Number: PRLX-2002-L-935-117L-L-X-X-GREY-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, FLAT LENS, TRUNCATED DOME WITH GRAY INTERIOR SHADE.  
LIGHT LEVEL 7  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9912.6 lumens  
Efficiency: N/A  
Efficacy: 104.1 lumens/watt  
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.27  
Luminous Opening: Circular (Dia: 1.67' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 95.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.5 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P867054

CATALOG NUMBER: PRLX-2002-L-935-117L-L-X-X-GREY-X

### Luminous Intensity Polar Plot





TEST NUMBER: P867054

CATALOG NUMBER: PRLX-2002-L-935-117L-L-X-X-GREY-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	90
2	104	97	92	87	101	95	91	86	92	88	84	89	86	83	86	83	81	79
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	71	69
4	89	79	72	66	87	78	71	66	75	70	65	73	68	64	71	67	63	61
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54
6	77	65	57	52	75	64	57	52	63	56	51	61	55	51	60	54	50	48
7	72	60	52	46	70	59	51	46	57	51	46	56	50	46	55	49	45	43
8	67	55	47	42	65	54	47	42	53	46	41	52	46	41	50	45	41	39
9	63	50	43	38	61	50	43	38	49	42	38	48	42	37	47	41	37	36
10	59	47	39	35	58	46	39	34	45	39	34	44	38	34	43	38	34	32

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	24884
5°	24809
10°	24533
15°	24141
20°	23700
25°	23179
30°	22527
35°	21729
40°	20689
45°	19414
50°	17890
55°	14222
60°	6694
65°	2418
70°	930
75°	1031
80°	1182
85°	1415

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 19414 cd/sqm

TEST NUMBER: P867054

CATALOG NUMBER: PRLX-2002-L-935-117L-L-X-X-GREY-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	474.6	4.8
10°-20°	1331.9	13.4
20°-30°	1959.1	19.8
30°-40°	2250.8	22.7
40°-50°	2143.8	21.6
50°-60°	1409.8	14.2
60°-70°	260.4	2.6
70°-80°	56.9	0.6
80°-90°	25.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3765.5	38.0
0°-40°	6016.3	60.7
0°-60°	9569.8	96.5
0°-90°	9912.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9912.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5044	
5°	5009	475
15°	4726	1332
25°	4258	1959
35°	3608	2251
45°	2782	2144
55°	1653	1410
65°	207	260
75°	54	57
85°	25	25
90°	0	

TEST NUMBER: P867054

CATALOG NUMBER: PRLX-2002-L-935-117L-L-X-X-GREY-X

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	5043.6
2.5°	5038.3
5°	5009.2
7.5°	4962.4
10°	4896.8
12.5°	4816.7
15°	4726.2
17.5°	4624.2
20°	4513.9
22.5°	4391.1
25°	4257.9
27.5°	4112.3
30°	3954.1
32.5°	3784.5
35°	3607.6
37.5°	3414.0
40°	3212.2
42.5°	3005.1
45°	2782.4
47.5°	2561.8
50°	2330.8
52.5°	2060.3
55°	1653.4
57.5°	1133.2
60°	678.4
62.5°	381.9
65°	207.1
67.5°	104.1
70°	64.5
72.5°	59.3
75°	54.1
77.5°	48.9
80°	41.6
82.5°	34.3
85°	25.0
87.5°	13.5
90°	0.0



TEST NUMBER: P867054  
 CATALOG NUMBER: PRLX-2002-L-935-117L-L-X-X-GREY-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.16	20.56	19.53	20.88	21.19	19.16	20.56	19.53	20.88	21.19
	3H	19.08	20.31	19.46	20.64	21.01	19.08	20.31	19.46	20.64	21.01
	4H	19.03	20.18	19.43	20.53	20.91	19.03	20.18	19.43	20.53	20.91
	6H	18.98	20.03	19.40	20.40	20.80	18.98	20.03	19.40	20.40	20.80
	8H	18.96	19.95	19.38	20.34	20.75	18.96	19.95	19.38	20.34	20.75
	12H	18.93	19.88	19.36	20.27	20.70	18.93	19.88	19.36	20.27	20.70
4H	2H	19.03	20.18	19.44	20.53	20.91	19.03	20.18	19.44	20.53	20.91
	3H	18.97	19.89	19.38	20.29	20.70	18.97	19.89	19.38	20.29	20.70
	4H	18.91	19.74	19.35	20.16	20.60	18.91	19.74	19.35	20.16	20.60
	6H	18.88	19.59	19.35	20.04	20.50	18.88	19.59	19.35	20.04	20.50
	8H	18.85	19.52	19.32	19.96	20.43	18.85	19.52	19.32	19.96	20.43
	12H	18.84	19.42	19.32	19.91	20.38	18.84	19.42	19.32	19.91	20.38
8H	4H	18.80	19.46	19.27	19.91	20.38	18.80	19.46	19.27	19.91	20.38
	6H	18.76	19.31	19.26	19.81	20.29	18.76	19.31	19.26	19.81	20.29
	8H	18.74	19.24	19.26	19.75	20.24	18.74	19.24	19.26	19.75	20.24
	12H	18.74	19.18	19.25	19.68	20.24	18.74	19.18	19.25	19.68	20.24
12H	4H	18.76	19.35	19.25	19.83	20.30	18.76	19.35	19.25	19.83	20.30
	6H	18.71	19.20	19.23	19.72	20.21	18.71	19.20	19.23	19.72	20.21
	8H	18.71	19.15	19.22	19.65	20.22	18.71	19.15	19.22	19.65	20.22