

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P867078

Luminaire Tested: PRLX-2002-L-935-32L-L-X-X-GREY-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P867078
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-82)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2002-L-935-32L-L-X-X-GREY-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, FLAT LENS, TRUNCATED DOME WITH GRAY INTERIOR SHADE.
LIGHT LEVEL 2
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2721.6 lumens
Efficiency: N/A
Efficacy: 104.3 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.27
Luminous Opening: Circular (Dia: 1.67' x H: 0')
CIE Type: Direct

Input Watts (W): 26.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P867078

CATALOG NUMBER: PRLX-2002-L-935-32L-L-X-X-GREY-X

Luminous Intensity Polar Plot





TEST NUMBER: P867078

CATALOG NUMBER: PRLX-2002-L-935-32L-L-X-X-GREY-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97		98	96	94		94	93	91	90
2	104	97	92	87	101	95	91	86	92	88	84		89	86	83		86	83	81	79
3	96	88	81	76	94	86	80	75	83	78	74		81	76	73		78	75	71	69
4	89	79	72	66	87	78	71	66	75	70	65		73	68	64		71	67	63	61
5	83	72	64	58	81	71	63	58	69	62	57		67	61	57		65	60	56	54
6	77	65	57	52	75	64	57	52	63	56	51		61	55	51		60	54	50	48
7	72	60	52	46	70	59	51	46	57	51	46		56	50	46		55	49	45	43
8	67	55	47	42	65	54	47	42	53	46	41		52	46	41		50	45	41	39
9	63	50	43	38	61	50	43	38	49	42	38		48	42	37		47	41	37	36
10	59	47	39	35	58	46	39	34	45	39	34		44	38	34		43	38	34	32

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	6832
5°	6811
10°	6736
15°	6628
20°	6507
25°	6364
30°	6185
35°	5966
40°	5680
45°	5330
50°	4912
55°	3905
60°	1838
65°	664
70°	255
75°	284
80°	324
85°	391

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5330 cd/sqm

TEST NUMBER: P867078

CATALOG NUMBER: PRLX-2002-L-935-32L-L-X-X-GREY-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.3	4.8
10°-20°	365.7	13.4
20°-30°	537.9	19.8
30°-40°	618.0	22.7
40°-50°	588.6	21.6
50°-60°	387.1	14.2
60°-70°	71.5	2.6
70°-80°	15.6	0.6
80°-90°	7.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1033.9	38.0
0°-40°	1651.8	60.7
0°-60°	2627.5	96.5
0°-90°	2721.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2721.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1385	
5°	1375	130
15°	1298	366
25°	1169	538
35°	990	618
45°	764	589
55°	454	387
65°	57	72
75°	15	16
85°	7	7
90°	0	

TEST NUMBER: P867078

CATALOG NUMBER: PRLX-2002-L-935-32L-L-X-X-GREY-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	1384.7
2.5°	1383.3
5°	1375.3
7.5°	1362.5
10°	1344.5
12.5°	1322.5
15°	1297.6
17.5°	1269.6
20°	1239.3
22.5°	1205.6
25°	1169.1
27.5°	1129.1
30°	1085.6
32.5°	1039.1
35°	990.5
37.5°	937.4
40°	881.9
42.5°	825.1
45°	763.9
47.5°	703.4
50°	640.0
52.5°	565.7
55°	454.0
57.5°	311.1
60°	186.3
62.5°	104.8
65°	56.9
67.5°	28.6
70°	17.7
72.5°	16.3
75°	14.9
77.5°	13.4
80°	11.4
82.5°	9.4
85°	6.9
87.5°	3.7
90°	0.0

TEST NUMBER: P867078
 CATALOG NUMBER: PRLX-2002-L-935-32L-L-X-X-GREY-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.67	16.07	15.03	16.38	16.70	14.67	16.07	15.03	16.38	16.70
	3H	14.59	15.82	14.97	16.15	16.51	14.59	15.82	14.97	16.15	16.51
	4H	14.54	15.68	14.94	16.03	16.42	14.54	15.68	14.94	16.03	16.42
	6H	14.49	15.54	14.90	15.91	16.30	14.49	15.54	14.90	15.91	16.30
	8H	14.46	15.46	14.89	15.85	16.26	14.46	15.46	14.89	15.85	16.26
	12H	14.44	15.39	14.87	15.77	16.20	14.44	15.39	14.87	15.77	16.20
4H	2H	14.54	15.69	14.94	16.04	16.42	14.54	15.69	14.94	16.04	16.42
	3H	14.47	15.40	14.89	15.80	16.21	14.47	15.40	14.89	15.80	16.21
	4H	14.42	15.25	14.86	15.66	16.11	14.42	15.25	14.86	15.66	16.11
	6H	14.39	15.10	14.85	15.55	16.01	14.39	15.10	14.85	15.55	16.01
	8H	14.36	15.03	14.83	15.47	15.94	14.36	15.03	14.83	15.47	15.94
	12H	14.34	14.93	14.83	15.41	15.89	14.34	14.93	14.83	15.41	15.89
8H	4H	14.31	14.97	14.78	15.42	15.89	14.31	14.97	14.78	15.42	15.89
	6H	14.27	14.82	14.77	15.31	15.79	14.27	14.82	14.77	15.31	15.79
	8H	14.25	14.74	14.77	15.26	15.75	14.25	14.74	14.77	15.26	15.75
	12H	14.25	14.69	14.76	15.18	15.75	14.25	14.69	14.76	15.18	15.75
12H	4H	14.27	14.86	14.75	15.34	15.81	14.27	14.86	14.75	15.34	15.81
	6H	14.22	14.71	14.74	15.23	15.72	14.22	14.71	14.74	15.23	15.72
	8H	14.22	14.66	14.73	15.16	15.73	14.22	14.66	14.73	15.16	15.73