

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865751

Luminaire Tested: PRLX-2004-S-927-15L-G-U-S-X-X-WHHR-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P865751
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2004-S-927-15L-G-U-S-X-X-WHHR-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, GLOBE LENS,
BELL WITH WHITE INTERIOR SHADE.
LIGHT LEVEL 3
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 717.7 lumens
Efficiency: N/A
Efficacy: 46.0 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.21
Luminous Opening: Circular (Dia: 0.92' x H: 0')
CIE Type: Direct

Input Watts (W): 15.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P865751

CATALOG NUMBER: PRLX-2004-S-927-15L-G-U-S-X-X-WHHR-X

Luminous Intensity Polar Plot





TEST NUMBER: P865751

CATALOG NUMBER: PRLX-2004-S-927-15L-G-U-S-X-X-WHHR-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	102	98	107	103	100	97	99	96	94	95	93	91	92	90	88	86
2	101	94	88	83	99	92	86	82	88	84	80	85	81	78	82	79	76	74
3	93	84	76	70	91	82	75	70	79	73	69	77	72	67	74	70	66	64
4	86	75	67	61	84	74	66	61	71	65	60	69	64	59	67	62	58	56
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	50	46	44
7	69	56	48	43	67	56	48	42	54	47	42	53	47	42	52	46	42	40
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36
9	61	48	40	35	59	47	40	35	46	39	35	45	39	35	44	39	34	33
10	57	44	37	32	56	44	37	32	43	36	32	42	36	32	41	36	32	30

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	5497
5°	5498
10°	5482
15°	5468
20°	5433
25°	5287
30°	5038
35°	4633
40°	4162
45°	3707
50°	3225
55°	2795
60°	2427
65°	2223
70°	2117
75°	1966
80°	1916
85°	1797

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3707 cd/sqm

TEST NUMBER: P865751

CATALOG NUMBER: PRLX-2004-S-927-15L-G-U-S-X-X-WHHR-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	31.9	4.4
10°-20°	91.2	12.7
20°-30°	134.8	18.8
30°-40°	144.9	20.2
40°-50°	124.1	17.3
50°-60°	88.6	12.3
60°-70°	57.7	8.0
70°-80°	33.9	4.7
80°-90°	10.6	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	258.0	35.9
0°-40°	402.9	56.1
0°-60°	615.5	85.8
0°-90°	717.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	717.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	337	
5°	336	32
15°	324	91
25°	294	135
35°	233	145
45°	161	124
55°	98	89
65°	58	58
75°	31	34
85°	10	11
90°	0	

TEST NUMBER: P865751

CATALOG NUMBER: PRLX-2004-S-927-15L-G-U-S-X-X-WHHR-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	337.0
2.5°	337.0
5°	335.8
7.5°	334.6
10°	331.0
12.5°	327.4
15°	323.8
17.5°	317.8
20°	313.0
22.5°	304.6
25°	293.8
27.5°	281.8
30°	267.5
32.5°	250.7
35°	232.7
37.5°	213.5
40°	195.5
42.5°	178.7
45°	160.7
47.5°	143.9
50°	127.1
52.5°	112.7
55°	98.3
57.5°	85.2
60°	74.4
62.5°	66.0
65°	57.6
67.5°	50.4
70°	44.4
72.5°	38.4
75°	31.2
77.5°	26.4
80°	20.4
82.5°	14.4
85°	9.6
87.5°	4.8
90°	0.0



TEST NUMBER: P865751
 CATALOG NUMBER: PRLX-2004-S-927-15L-G-U-S-X-X-WHHR-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.49	15.98	14.85	16.29	16.61	14.49	15.98	14.85	16.29	16.61
	3H	16.02	17.36	16.40	17.69	18.05	16.02	17.36	16.40	17.69	18.05
	4H	16.64	17.89	17.04	18.24	18.62	16.64	17.89	17.04	18.24	18.62
	6H	17.15	18.32	17.57	18.68	19.07	17.15	18.32	17.57	18.68	19.07
	8H	17.33	18.43	17.75	18.82	19.22	17.33	18.43	17.75	18.82	19.22
	12H	17.45	18.51	17.88	18.89	19.32	17.45	18.51	17.88	18.89	19.32
4H	2H	14.99	16.24	15.39	16.59	16.97	14.99	16.24	15.39	16.59	16.97
	3H	16.78	17.82	17.19	18.22	18.62	16.78	17.82	17.19	18.22	18.62
	4H	17.53	18.46	17.96	18.88	19.32	17.53	18.46	17.96	18.88	19.32
	6H	18.19	19.01	18.65	19.45	19.91	18.19	19.01	18.65	19.45	19.91
	8H	18.41	19.18	18.88	19.62	20.09	18.41	19.18	18.88	19.62	20.09
	12H	18.59	19.27	19.07	19.75	20.22	18.59	19.27	19.07	19.75	20.22
8H	4H	17.82	18.58	18.28	19.03	19.49	17.82	18.58	18.28	19.03	19.49
	6H	18.61	19.25	19.11	19.74	20.22	18.61	19.25	19.11	19.74	20.22
	8H	18.92	19.49	19.43	20.00	20.49	18.92	19.49	19.43	20.00	20.49
	12H	19.18	19.69	19.69	20.18	20.75	19.18	19.69	19.69	20.18	20.75
12H	4H	17.85	18.53	18.33	19.01	19.48	17.85	18.53	18.33	19.01	19.48
	6H	18.67	19.24	19.19	19.75	20.24	18.67	19.24	19.19	19.75	20.24
	8H	19.04	19.54	19.55	20.03	20.60	19.04	19.54	19.55	20.03	20.60