

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P867145

Luminaire Tested: PRLX-2002-L-940-32L-G-X-X-BRSS-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P867145
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-69)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2002-L-940-32L-G-X-X-BRSS-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, GLOBE LENS, TRUNCATED DOME WITH BRASS INTERIOR SHADE.
LIGHT LEVEL 2
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1242.3 lumens
Efficiency: N/A
Efficacy: 47.6 lumens/watt
Spacing Criteria (0/90/45): 1.36 / 1.36 / 1.52
Luminous Opening: Circular (Dia: 1.67' x H: 0')
CIE Type: Direct

Input Watts (W): 26.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P867145

CATALOG NUMBER: PRLX-2002-L-940-32L-G-X-X-BRSS-X

Luminous Intensity Polar Plot





TEST NUMBER: P867145

CATALOG NUMBER: PRLX-2002-L-940-32L-G-X-X-BRSS-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	108	103	99	95	105	101	97	93	97	93	90		93	90	87		89	87	85	83
2	98	89	82	76	95	87	81	75	84	78	73		80	76	72		77	73	70	68
3	89	78	69	62	86	76	68	62	73	66	61		70	65	60		68	63	59	56
4	81	68	59	52	79	67	59	52	65	57	51		62	56	50		60	54	50	48
5	74	61	51	45	72	60	51	44	58	50	44		55	49	43		54	48	43	41
6	68	54	45	39	66	54	45	38	52	44	38		50	43	38		48	42	37	35
7	63	49	40	34	61	48	40	34	47	39	33		45	38	33		44	38	33	31
8	59	45	36	30	57	44	36	30	43	35	30		41	34	29		40	34	29	27
9	55	41	32	27	53	40	32	27	39	32	27		38	31	26		37	31	26	24
10	51	38	30	24	50	37	29	24	36	29	24		35	28	24		34	28	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1825
5°	1830
10°	1838
15°	1845
20°	1857
25°	1875
30°	1908
35°	1960
40°	2031
45°	2093
50°	2120
55°	2109
60°	2072
65°	2006
70°	1884
75°	1729
80°	1543
85°	1268

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 50°
 Luminance: 2120 cd/sqm



TEST NUMBER: P867145

CATALOG NUMBER: PRLX-2002-L-940-32L-G-X-X-BRSS-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.2	2.8
10°-20°	102.1	8.2
20°-30°	159.2	12.8
30°-40°	204.1	16.4
40°-50°	230.7	18.6
50°-60°	218.7	17.6
60°-70°	169.4	13.6
70°-80°	96.4	7.8
80°-90°	26.5	2.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	296.5	23.9
0°-40°	500.6	40.3
0°-60°	950.0	76.5
0°-90°	1242.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1242.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	370	
5°	370	35
15°	361	102
25°	344	159
35°	325	204
45°	300	231
55°	245	219
65°	172	169
75°	91	96
85°	22	26
90°	0	

TEST NUMBER: P867145

CATALOG NUMBER: PRLX-2002-L-940-32L-G-X-X-BRSS-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	369.8
2.5°	369.8
5°	369.5
7.5°	368.9
10°	366.9
12.5°	364.2
15°	361.2
17.5°	357.9
20°	353.7
22.5°	349.3
25°	344.5
27.5°	339.7
30°	334.9
32.5°	330.2
35°	325.4
37.5°	320.3
40°	315.3
42.5°	309.0
45°	300.0
47.5°	289.0
50°	276.2
52.5°	261.3
55°	245.2
57.5°	228.2
60°	210.0
62.5°	191.2
65°	171.8
67.5°	151.5
70°	130.6
72.5°	110.4
75°	90.7
77.5°	71.9
80°	54.3
82.5°	37.6
85°	22.4
87.5°	10.1
90°	0.0



TEST NUMBER: P867145
 CATALOG NUMBER: PRLX-2002-L-940-32L-G-X-X-BRSS-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.04	16.73	15.40	17.05	17.36	15.04	16.73	15.40	17.05	17.36
	3H	16.87	18.41	17.25	18.74	19.10	16.87	18.41	17.25	18.74	19.10
	4H	17.54	18.99	17.94	19.34	19.71	17.54	18.99	17.94	19.34	19.71
	6H	18.03	19.38	18.44	19.74	20.13	18.03	19.38	18.44	19.74	20.13
	8H	18.18	19.47	18.61	19.86	20.26	18.18	19.47	18.61	19.86	20.26
	12H	18.28	19.52	18.71	19.90	20.33	18.28	19.52	18.71	19.90	20.33
4H	2H	15.70	17.15	16.10	17.50	17.87	15.70	17.15	16.10	17.50	17.87
	3H	17.75	18.97	18.15	19.36	19.76	17.75	18.97	18.15	19.36	19.76
	4H	18.54	19.65	18.97	20.06	20.49	18.54	19.65	18.97	20.06	20.49
	6H	19.15	20.12	19.61	20.56	21.02	19.15	20.12	19.61	20.56	21.02
	8H	19.36	20.26	19.81	20.71	21.17	19.36	20.26	19.81	20.71	21.17
	12H	19.50	20.32	19.98	20.79	21.26	19.50	20.32	19.98	20.79	21.26
8H	4H	18.86	19.77	19.32	20.21	20.67	18.86	19.77	19.32	20.21	20.67
	6H	19.59	20.35	20.08	20.83	21.31	19.59	20.35	20.08	20.83	21.31
	8H	19.86	20.54	20.37	21.05	21.53	19.86	20.54	20.37	21.05	21.53
	12H	20.08	20.68	20.58	21.17	21.73	20.08	20.68	20.58	21.17	21.73
12H	4H	18.90	19.71	19.37	20.19	20.66	18.90	19.71	19.37	20.19	20.66
	6H	19.65	20.33	20.16	20.83	21.32	19.65	20.33	20.16	20.83	21.32
	8H	19.98	20.58	20.48	21.07	21.63	19.98	20.58	20.48	21.07	21.63