

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865762

Luminaire Tested: PRLX-2004-S-927-20L-L-U-S-X-X-GREY-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P865762  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-25)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2004-S-927-20L-L-U-S-X-X-GREY-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, FLAT LENS,  
BELL WITH GRAY INTERIOR SHADE.  
LIGHT LEVEL 4  
Light Source: 2700K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 918.3 lumens  
Efficiency: N/A  
Efficacy: 42.1 lumens/watt  
Spacing Criteria (0/90/45): 1.07 / 1.07 / 1.02  
Luminous Opening: Circular (Dia: 0.92' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 21.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.5 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P865762

CATALOG NUMBER: PRLX-2004-S-927-20L-L-U-S-X-X-GREY-X

### Luminous Intensity Polar Plot





TEST NUMBER: P865762

CATALOG NUMBER: PRLX-2004-S-927-20L-L-U-S-X-X-GREY-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	104	110	107	105	103	103	101	99	100	98	96	96	95	94	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84
3	100	93	88	83	98	92	87	82	89	85	81	86	83	80	84	81	79	77
4	95	86	80	75	93	85	79	75	83	78	74	81	76	73	79	75	72	71
5	89	80	74	69	87	79	73	68	77	72	68	75	71	67	74	70	67	65
6	84	74	68	63	83	74	67	63	72	67	63	71	66	62	69	65	62	60
7	80	70	63	58	78	69	63	58	67	62	58	66	61	58	65	61	57	56
8	75	65	59	54	74	64	58	54	63	58	54	62	57	53	61	57	53	52
9	71	61	55	50	70	60	54	50	59	54	50	59	53	50	58	53	50	48
10	68	57	51	47	67	57	51	47	56	50	47	55	50	47	54	50	46	45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	13276
5°	12987
10°	12448
15°	11962
20°	11546
25°	11167
30°	10722
35°	8343
40°	3439
45°	1366
50°	893
55°	864
60°	783
65°	741
70°	687
75°	706
80°	601
85°	599

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1366 cd/sqm

TEST NUMBER: P865762

CATALOG NUMBER: PRLX-2004-S-927-20L-L-U-S-X-X-GREY-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	74.4	8.1
10°-20°	199.7	21.7
20°-30°	285.6	31.1
30°-40°	242.7	26.4
40°-50°	55.2	6.0
50°-60°	26.6	2.9
60°-70°	19.4	2.1
70°-80°	11.2	1.2
80°-90°	3.5	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	559.6	60.9
0°-40°	802.4	87.4
0°-60°	884.2	96.3
0°-90°	918.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	918.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	814	
5°	793	74
15°	708	200
25°	620	286
35°	419	243
45°	59	55
55°	30	27
65°	19	19
75°	11	11
85°	3	3
90°	0	

TEST NUMBER: P865762

CATALOG NUMBER: PRLX-2004-S-927-20L-L-U-S-X-X-GREY-X

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	814.0
2.5°	810.8
5°	793.2
7.5°	772.4
10°	751.6
12.5°	730.8
15°	708.4
17.5°	687.6
20°	665.2
22.5°	642.9
25°	620.5
27.5°	598.1
30°	569.3
32.5°	513.3
35°	419.0
37.5°	281.4
40°	161.5
42.5°	94.3
45°	59.2
47.5°	40.0
50°	35.2
52.5°	32.0
55°	30.4
57.5°	27.2
60°	24.0
62.5°	22.4
65°	19.2
67.5°	17.6
70°	14.4
72.5°	12.8
75°	11.2
77.5°	8.0
80°	6.4
82.5°	4.8
85°	3.2
87.5°	1.6
90°	0.0

TEST NUMBER: P865762  
 CATALOG NUMBER: PRLX-2004-S-927-20L-L-U-S-X-X-GREY-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.24	7.31	6.61	7.62	7.93	6.24	7.31	6.61	7.62	7.93
	3H	7.88	8.83	8.27	9.16	9.53	7.88	8.83	8.27	9.16	9.53
	4H	8.56	9.44	8.97	9.79	10.18	8.56	9.44	8.97	9.79	10.18
	6H	8.97	9.77	9.39	10.14	10.54	8.97	9.77	9.39	10.14	10.54
	8H	9.12	9.88	9.56	10.27	10.68	9.12	9.88	9.56	10.27	10.68
	12H	9.23	9.95	9.67	10.34	10.77	9.23	9.95	9.67	10.34	10.77
4H	2H	6.72	7.59	7.12	7.94	8.33	6.72	7.59	7.12	7.94	8.33
	3H	8.56	9.28	8.98	9.69	10.09	8.56	9.28	8.98	9.69	10.09
	4H	9.38	10.02	9.82	10.45	10.89	9.38	10.02	9.82	10.45	10.89
	6H	9.91	10.46	10.38	10.91	11.38	9.91	10.46	10.38	10.91	11.38
	8H	10.11	10.62	10.58	11.07	11.55	10.11	10.62	10.58	11.07	11.55
	12H	10.27	10.71	10.76	11.20	11.68	10.27	10.71	10.76	11.20	11.68
8H	4H	9.60	10.12	10.08	10.57	11.04	9.60	10.12	10.08	10.57	11.04
	6H	10.26	10.67	10.77	11.17	11.66	10.26	10.67	10.77	11.17	11.66
	8H	10.55	10.92	11.08	11.44	11.93	10.55	10.92	11.08	11.44	11.93
	12H	10.81	11.12	11.33	11.62	12.20	10.81	11.12	11.33	11.62	12.20
12H	4H	9.60	10.05	10.09	10.53	11.01	9.60	10.05	10.09	10.53	11.01
	6H	10.30	10.66	10.83	11.18	11.68	10.30	10.66	10.83	11.18	11.68
	8H	10.65	10.97	11.17	11.46	12.04	10.65	10.97	11.17	11.46	12.04