

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866149

Luminaire Tested: PRLX-2002-M-927-07L-G-U-S-X-X-BRSS-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P866149
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-39)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2002-M-927-07L-G-U-S-X-X-BRSS-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, GLOBE LENS, TRUNCATED DOME WITH BRASS INTERIOR SHADE.
LIGHT LEVEL 1
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 252.3 lumens
Efficiency: N/A
Efficacy: 30.8 lumens/watt
Spacing Criteria (0/90/45): 1.36 / 1.36 / 1.53
Luminous Opening: Circular (Dia: 1.31' x H: 0')
CIE Type: Direct

Input Watts (W): 8.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P866149

CATALOG NUMBER: PRLX-2002-M-927-07L-G-U-S-X-X-BRSS-X

Luminous Intensity Polar Plot





TEST NUMBER: P866149

CATALOG NUMBER: PRLX-2002-M-927-07L-G-U-S-X-X-BRSS-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	105	101	97	93	97	93	90	93	90	87	89	87	85	83
2	98	89	82	76	95	87	81	75	84	78	73	80	76	72	77	73	70	68
3	89	78	69	62	86	76	68	62	73	66	61	70	64	60	68	63	58	56
4	81	68	59	52	78	67	58	52	64	57	51	62	56	50	60	54	50	47
5	74	61	51	44	72	59	51	44	57	50	44	55	48	43	53	47	43	40
6	68	54	45	38	66	53	45	38	51	44	38	50	43	37	48	42	37	35
7	63	49	40	34	61	48	40	33	47	39	33	45	38	33	44	37	33	31
8	59	45	36	30	57	44	35	30	42	35	29	41	34	29	40	34	29	27
9	55	41	32	27	53	40	32	26	39	31	26	38	31	26	37	31	26	24
10	51	37	29	24	50	37	29	24	36	29	24	35	28	24	34	28	23	22

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	591
5°	593
10°	596
15°	597
20°	600
25°	606
30°	617
35°	633
40°	656
45°	685
50°	705
55°	706
60°	692
65°	665
70°	621
75°	569
80°	490
85°	393

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 52.5°
 Luminance: 710 cd/sqm

TEST NUMBER: P866149

CATALOG NUMBER: PRLX-2002-M-927-07L-G-U-S-X-X-BRSS-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	7.1	2.8
10°-20°	20.5	8.1
20°-30°	31.9	12.6
30°-40°	40.9	16.2
40°-50°	46.9	18.6
50°-60°	45.4	18.0
60°-70°	34.9	13.8
70°-80°	19.6	7.8
80°-90°	5.2	2.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	59.5	23.6
0°-40°	100.4	39.8
0°-60°	192.6	76.3
0°-90°	252.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	252.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	74	
5°	74	7
15°	72	20
25°	69	32
35°	65	41
45°	61	47
55°	51	45
65°	35	35
75°	18	20
85°	4	5
90°	0	

TEST NUMBER: P866149

CATALOG NUMBER: PRLX-2002-M-927-07L-G-U-S-X-X-BRSS-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	74.3
2.5°	74.3
5°	74.2
7.5°	74.0
10°	73.8
12.5°	73.3
15°	72.5
17.5°	71.7
20°	70.9
22.5°	69.9
25°	69.0
27.5°	68.1
30°	67.2
32.5°	66.1
35°	65.2
37.5°	64.3
40°	63.2
42.5°	62.3
45°	60.9
47.5°	59.1
50°	57.0
52.5°	54.3
55°	50.9
57.5°	47.3
60°	43.5
62.5°	39.6
65°	35.3
67.5°	31.2
70°	26.7
72.5°	22.6
75°	18.5
77.5°	14.5
80°	10.7
82.5°	7.3
85°	4.3
87.5°	2.0
90°	0.0



TEST NUMBER: P866149
 CATALOG NUMBER: PRLX-2002-M-927-07L-G-U-S-X-X-BRSS-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.29	12.99	11.66	13.31	13.62	11.29	12.99	11.66	13.31	13.62
	3H	13.10	14.65	13.48	14.97	15.33	13.10	14.65	13.48	14.97	15.33
	4H	13.76	15.21	14.15	15.56	15.93	13.76	15.21	14.15	15.56	15.93
	6H	14.22	15.57	14.63	15.93	16.32	14.22	15.57	14.63	15.93	16.32
	8H	14.35	15.65	14.78	16.04	16.43	14.35	15.65	14.78	16.04	16.43
	12H	14.44	15.68	14.87	16.06	16.49	14.44	15.68	14.87	16.06	16.49
4H	2H	11.94	13.40	12.34	13.75	14.12	11.94	13.40	12.34	13.75	14.12
	3H	13.96	15.19	14.37	15.59	15.98	13.96	15.19	14.37	15.59	15.98
	4H	14.74	15.85	15.17	16.27	16.70	14.74	15.85	15.17	16.27	16.70
	6H	15.33	16.30	15.78	16.74	17.19	15.33	16.30	15.78	16.74	17.19
	8H	15.51	16.42	15.96	16.86	17.32	15.51	16.42	15.96	16.86	17.32
	12H	15.63	16.45	16.11	16.93	17.40	15.63	16.45	16.11	16.93	17.40
8H	4H	15.05	15.96	15.51	16.41	16.87	15.05	15.96	15.51	16.41	16.87
	6H	15.75	16.50	16.24	16.99	17.46	15.75	16.50	16.24	16.99	17.46
	8H	15.99	16.67	16.50	17.18	17.66	15.99	16.67	16.50	17.18	17.66
	12H	16.18	16.79	16.69	17.28	17.83	16.18	16.79	16.69	17.28	17.83
12H	4H	15.09	15.91	15.57	16.38	16.85	15.09	15.91	15.57	16.38	16.85
	6H	15.80	16.48	16.30	16.98	17.47	15.80	16.48	16.30	16.98	17.47
	8H	16.10	16.70	16.60	17.19	17.75	16.10	16.70	16.60	17.19	17.75