

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865767

Luminaire Tested: PRLX-2004-S-927-25L-G-U-S-X-X-WHHR-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P865767
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2004-S-927-25L-G-U-S-X-X-WHHR-X
Description: PRENATALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, GLOBE LENS,
BELL WITH WHITE INTERIOR SHADE.
LIGHT LEVEL 5
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1196.2 lumens
Efficiency: N/A
Efficacy: 41.1 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.21
Luminous Opening: Circular (Dia: 0.92' x H: 0')
CIE Type: Direct

Input Watts (W): 29.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P865767

CATALOG NUMBER: PRLX-2004-S-927-25L-G-U-S-X-X-WHHR-X

Luminous Intensity Polar Plot





TEST NUMBER: P865767

CATALOG NUMBER: PRLX-2004-S-927-25L-G-U-S-X-X-WHHR-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	102	98	107	103	100	97	99	96	94	95	93	91	92	90	88	86
2	101	94	88	83	99	92	86	82	88	84	80	85	81	78	82	79	76	74
3	93	84	76	70	91	82	75	70	79	73	69	77	72	67	74	70	66	64
4	86	75	67	61	84	74	66	61	71	65	60	69	64	59	67	62	58	56
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	50	46	44
7	69	56	48	43	67	56	48	42	54	47	42	53	47	42	52	46	42	40
8	65	52	44	38	63	51	44	38	50	43	38	49	43	38	48	42	38	36
9	61	48	40	35	59	47	40	35	46	39	35	45	39	35	44	39	34	33
10	57	44	37	32	56	44	37	32	43	36	32	42	36	32	41	36	32	30

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	9161
5°	9164
10°	9137
15°	9113
20°	9055
25°	8813
30°	8396
35°	7721
40°	6937
45°	6179
50°	5377
55°	4661
60°	4042
65°	3701
70°	3529
75°	3277
80°	3193
85°	2994

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6179 cd/sqm

TEST NUMBER: P865767

CATALOG NUMBER: PRLX-2004-S-927-25L-G-U-S-X-X-WHHR-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.2	4.4
10°-20°	152.0	12.7
20°-30°	224.7	18.8
30°-40°	241.5	20.2
40°-50°	206.8	17.3
50°-60°	147.6	12.3
60°-70°	96.1	8.0
70°-80°	56.4	4.7
80°-90°	17.7	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	430.0	35.9
0°-40°	671.5	56.1
0°-60°	1025.9	85.8
0°-90°	1196.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1196.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	562	
5°	560	53
15°	540	152
25°	490	225
35°	388	241
45°	268	207
55°	164	148
65°	96	96
75°	52	56
85°	16	18
90°	0	

TEST NUMBER: P865767

CATALOG NUMBER: PRLX-2004-S-927-25L-G-U-S-X-X-WHHR-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	561.7
2.5°	561.7
5°	559.7
7.5°	557.7
10°	551.7
12.5°	545.7
15°	539.7
17.5°	529.7
20°	521.7
22.5°	507.7
25°	489.7
27.5°	469.7
30°	445.8
32.5°	417.8
35°	387.8
37.5°	355.8
40°	325.8
42.5°	297.8
45°	267.9
47.5°	239.9
50°	211.9
52.5°	187.9
55°	163.9
57.5°	141.9
60°	123.9
62.5°	109.9
65°	95.9
67.5°	84.0
70°	74.0
72.5°	64.0
75°	52.0
77.5°	44.0
80°	34.0
82.5°	24.0
85°	16.0
87.5°	8.0
90°	0.0



TEST NUMBER: P865767
 CATALOG NUMBER: PRLX-2004-S-927-25L-G-U-S-X-X-WHHR-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.26	17.75	16.62	18.06	18.38	16.26	17.75	16.62	18.06	18.38
	3H	17.79	19.13	18.17	19.46	19.82	17.79	19.13	18.17	19.46	19.82
	4H	18.41	19.66	18.81	20.01	20.39	18.41	19.66	18.81	20.01	20.39
	6H	18.93	20.09	19.34	20.45	20.85	18.93	20.09	19.34	20.45	20.85
	8H	19.10	20.20	19.53	20.59	21.00	19.10	20.20	19.53	20.59	21.00
	12H	19.23	20.28	19.66	20.66	21.09	19.23	20.28	19.66	20.66	21.09
4H	2H	16.75	18.01	17.15	18.36	18.74	16.75	18.01	17.15	18.36	18.74
	3H	18.55	19.59	18.96	19.99	20.39	18.55	19.59	18.96	19.99	20.39
	4H	19.30	20.24	19.73	20.65	21.09	19.30	20.24	19.73	20.65	21.09
	6H	19.96	20.78	20.42	21.22	21.68	19.96	20.78	20.42	21.22	21.68
	8H	20.18	20.95	20.65	21.39	21.86	20.18	20.95	20.65	21.39	21.86
	12H	20.36	21.05	20.84	21.52	22.00	20.36	21.05	20.84	21.52	22.00
8H	4H	19.59	20.35	20.05	20.80	21.27	19.59	20.35	20.05	20.80	21.27
	6H	20.39	21.02	20.88	21.51	21.99	20.39	21.02	20.88	21.51	21.99
	8H	20.69	21.26	21.21	21.77	22.26	20.69	21.26	21.21	21.77	22.26
	12H	20.96	21.46	21.47	21.95	22.52	20.96	21.46	21.47	21.95	22.52
12H	4H	19.62	20.30	20.10	20.78	21.25	19.62	20.30	20.10	20.78	21.25
	6H	20.44	21.02	20.96	21.53	22.01	20.44	21.02	20.96	21.53	22.01
	8H	20.81	21.31	21.32	21.81	22.37	20.81	21.31	21.32	21.81	22.37