

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866157

Luminaire Tested: PRLX-2002-M-927-15L-G-U-S-X-X-BRSS-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P866157
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-39)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2002-M-927-15L-G-U-S-X-X-BRSS-X
Description: PRENATALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, GLOBE LENS, TRUNCATED DOME WITH BRASS INTERIOR SHADE.
LIGHT LEVEL 2
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 535.9 lumens
Efficiency: N/A
Efficacy: 38.3 lumens/watt
Spacing Criteria (0/90/45): 1.36 / 1.36 / 1.53
Luminous Opening: Circular (Dia: 1.31' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P866157

CATALOG NUMBER: PRLX-2002-M-927-15L-G-U-S-X-X-BRSS-X

Luminous Intensity Polar Plot





TEST NUMBER: P866157

CATALOG NUMBER: PRLX-2002-M-927-15L-G-U-S-X-X-BRSS-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	108	103	99	95	105	101	97	93	97	93	90		93	90	87		89	87	85	83
2	98	89	82	76	95	87	81	75	84	78	73		80	76	72		77	73	70	68
3	89	78	69	62	86	76	68	62	73	66	61		70	64	60		68	63	58	56
4	81	68	59	52	78	67	58	52	64	57	51		62	56	50		60	54	50	47
5	74	61	51	44	72	59	51	44	57	50	44		55	48	43		53	47	43	40
6	68	54	45	38	66	53	45	38	51	44	38		50	43	37		48	42	37	35
7	63	49	40	34	61	48	40	33	47	39	33		45	38	33		44	37	33	31
8	59	45	36	30	57	44	35	30	42	35	29		41	34	29		40	34	29	27
9	55	41	32	27	53	40	32	26	39	31	26		38	31	26		37	31	26	24
10	51	37	29	24	50	37	29	24	36	29	24		35	28	24		34	28	23	22

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1256
5°	1259
10°	1267
15°	1269
20°	1276
25°	1286
30°	1311
35°	1345
40°	1395
45°	1456
50°	1498
55°	1499
60°	1472
65°	1412
70°	1319
75°	1205
80°	1045
85°	831

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 52.5°
 Luminance: 1507 cd/sqm

TEST NUMBER: P866157

CATALOG NUMBER: PRLX-2002-M-927-15L-G-U-S-X-X-BRSS-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	15.0	2.8
10°-20°	43.5	8.1
20°-30°	67.7	12.6
30°-40°	86.9	16.2
40°-50°	99.6	18.6
50°-60°	96.3	18.0
60°-70°	74.2	13.8
70°-80°	41.6	7.8
80°-90°	11.0	2.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	126.3	23.6
0°-40°	213.2	39.8
0°-60°	409.1	76.3
0°-90°	535.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	535.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	158	
5°	158	15
15°	154	44
25°	146	68
35°	138	87
45°	129	100
55°	108	96
65°	75	74
75°	39	42
85°	9	11
90°	0	

TEST NUMBER: P866157

CATALOG NUMBER: PRLX-2002-M-927-15L-G-U-S-X-X-BRSS-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	157.9
2.5°	157.9
5°	157.6
7.5°	157.2
10°	156.8
12.5°	155.7
15°	154.1
17.5°	152.2
20°	150.7
22.5°	148.4
25°	146.5
27.5°	144.6
30°	142.7
32.5°	140.4
35°	138.5
37.5°	136.6
40°	134.3
42.5°	132.4
45°	129.4
47.5°	125.6
50°	121.0
52.5°	115.3
55°	108.1
57.5°	100.5
60°	92.5
62.5°	84.1
65°	75.0
67.5°	66.2
70°	56.7
72.5°	48.0
75°	39.2
77.5°	30.8
80°	22.8
82.5°	15.6
85°	9.1
87.5°	4.2
90°	0.0



TEST NUMBER: P866157
 CATALOG NUMBER: PRLX-2002-M-927-15L-G-U-S-X-X-BRSS-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.91	15.61	14.28	15.93	16.24	13.91	15.61	14.28	15.93	16.24
	3H	15.72	17.26	16.09	17.59	17.95	15.72	17.26	16.09	17.59	17.95
	4H	16.37	17.83	16.77	18.17	18.55	16.37	17.83	16.77	18.17	18.55
	6H	16.83	18.19	17.24	18.55	18.94	16.83	18.19	17.24	18.55	18.94
	8H	16.97	18.27	17.40	18.65	19.05	16.97	18.27	17.40	18.65	19.05
	12H	17.06	18.30	17.49	18.68	19.11	17.06	18.30	17.49	18.68	19.11
4H	2H	14.56	16.02	14.96	16.37	16.74	14.56	16.02	14.96	16.37	16.74
	3H	16.58	17.81	16.99	18.20	18.60	16.58	17.81	16.99	18.20	18.60
	4H	17.36	18.47	17.79	18.88	19.31	17.36	18.47	17.79	18.88	19.31
	6H	17.94	18.91	18.39	19.35	19.81	17.94	18.91	18.39	19.35	19.81
	8H	18.13	19.04	18.58	19.48	19.94	18.13	19.04	18.58	19.48	19.94
	12H	18.25	19.07	18.73	19.55	20.01	18.25	19.07	18.73	19.55	20.01
8H	4H	17.67	18.58	18.13	19.02	19.48	17.67	18.58	18.13	19.02	19.48
	6H	18.36	19.12	18.85	19.61	20.08	18.36	19.12	18.85	19.61	20.08
	8H	18.61	19.29	19.12	19.80	20.28	18.61	19.29	19.12	19.80	20.28
	12H	18.80	19.41	19.31	19.90	20.45	18.80	19.41	19.31	19.90	20.45
12H	4H	17.70	18.52	18.18	19.00	19.46	17.70	18.52	18.18	19.00	19.46
	6H	18.41	19.10	18.92	19.60	20.09	18.41	19.10	18.92	19.60	20.09
	8H	18.72	19.32	19.22	19.81	20.37	18.72	19.32	19.22	19.81	20.37