

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865770

Luminaire Tested: PRLX-2004-S-927-25L-L-U-S-X-X-GREY-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P865770  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-25)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2004-S-927-25L-L-U-S-X-X-GREY-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, FLAT LENS, BELL WITH GRAY INTERIOR SHADE.  
LIGHT LEVEL 5  
Light Source: 2700K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1147.9 lumens  
Efficiency: N/A  
Efficacy: 39.4 lumens/watt  
Spacing Criteria (0/90/45): 1.07 / 1.07 / 1.02  
Luminous Opening: Circular (Dia: 0.92' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 29.1  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.5 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P865770

CATALOG NUMBER: PRLX-2004-S-927-25L-L-U-S-X-X-GREY-X

### Luminous Intensity Polar Plot





TEST NUMBER: P865770

CATALOG NUMBER: PRLX-2004-S-927-25L-L-U-S-X-X-GREY-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	104	110	107	105	103	103	101	99	100	98	96	96	95	94	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84
3	100	93	88	83	98	92	87	82	89	85	81	86	83	80	84	81	79	77
4	95	86	80	75	93	85	79	75	83	78	74	81	76	73	79	75	72	71
5	89	80	74	69	87	79	73	68	77	72	68	75	71	67	74	70	67	65
6	84	74	68	63	83	74	67	63	72	67	63	71	66	62	69	65	62	60
7	80	70	63	58	78	69	63	58	67	62	58	66	61	58	65	61	57	56
8	75	65	59	54	74	64	58	54	63	58	54	62	57	53	61	57	53	52
9	71	61	55	50	70	60	54	50	59	54	50	59	53	50	58	53	50	48
10	68	57	51	47	67	57	51	47	56	50	47	55	50	47	54	50	46	45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	16596
5°	16233
10°	15560
15°	14952
20°	14434
25°	13958
30°	13402
35°	10427
40°	4299
45°	1707
50°	1116
55°	1081
60°	979
65°	926
70°	858
75°	882
80°	751
85°	749

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1707 cd/sqm

TEST NUMBER: P865770

CATALOG NUMBER: PRLX-2004-S-927-25L-L-U-S-X-X-GREY-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	93.0	8.1
10°-20°	249.6	21.7
20°-30°	357.0	31.1
30°-40°	303.4	26.4
40°-50°	69.1	6.0
50°-60°	33.3	2.9
60°-70°	24.2	2.1
70°-80°	14.0	1.2
80°-90°	4.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	699.5	60.9
0°-40°	1003.0	87.4
0°-60°	1105.3	96.3
0°-90°	1147.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1147.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1018	
5°	992	93
15°	886	250
25°	776	357
35°	524	303
45°	74	69
55°	38	33
65°	24	24
75°	14	14
85°	4	4
90°	0	

TEST NUMBER: P865770

CATALOG NUMBER: PRLX-2004-S-927-25L-L-U-S-X-X-GREY-X

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1017.5
2.5°	1013.5
5°	991.5
7.5°	965.5
10°	939.5
12.5°	913.5
15°	885.5
17.5°	859.5
20°	831.6
22.5°	803.6
25°	775.6
27.5°	747.6
30°	711.6
32.5°	641.7
35°	523.7
37.5°	351.8
40°	201.9
42.5°	117.9
45°	74.0
47.5°	50.0
50°	44.0
52.5°	40.0
55°	38.0
57.5°	34.0
60°	30.0
62.5°	28.0
65°	24.0
67.5°	22.0
70°	18.0
72.5°	16.0
75°	14.0
77.5°	10.0
80°	8.0
82.5°	6.0
85°	4.0
87.5°	2.0
90°	0.0

TEST NUMBER: P865770

CATALOG NUMBER: PRLX-2004-S-927-25L-L-U-S-X-X-GREY-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.02	8.08	7.38	8.39	8.71	7.02	8.08	7.38	8.39	8.71
	3H	8.66	9.60	9.04	9.93	10.30	8.66	9.60	9.04	9.93	10.30
	4H	9.34	10.21	9.74	10.56	10.95	9.34	10.21	9.74	10.56	10.95
	6H	9.74	10.54	10.16	10.92	11.31	9.74	10.54	10.16	10.92	11.31
	8H	9.90	10.65	10.33	11.04	11.45	9.90	10.65	10.33	11.04	11.45
	12H	10.01	10.73	10.44	11.11	11.54	10.01	10.73	10.44	11.11	11.54
4H	2H	7.49	8.37	7.90	8.72	9.11	7.49	8.37	7.90	8.72	9.11
	3H	9.34	10.05	9.75	10.46	10.87	9.34	10.05	9.75	10.46	10.87
	4H	10.16	10.80	10.60	11.22	11.67	10.16	10.80	10.60	11.22	11.67
	6H	10.69	11.23	11.15	11.68	12.16	10.69	11.23	11.15	11.68	12.16
	8H	10.88	11.40	11.36	11.85	12.32	10.88	11.40	11.36	11.85	12.32
	12H	11.04	11.49	11.53	11.97	12.45	11.04	11.49	11.53	11.97	12.45
8H	4H	10.38	10.89	10.85	11.34	11.82	10.38	10.89	10.85	11.34	11.82
	6H	11.04	11.45	11.55	11.95	12.43	11.04	11.45	11.55	11.95	12.43
	8H	11.33	11.69	11.86	12.21	12.71	11.33	11.69	11.86	12.21	12.71
	12H	11.58	11.90	12.10	12.40	12.98	11.58	11.90	12.10	12.40	12.98
12H	4H	10.38	10.82	10.87	11.31	11.79	10.38	10.82	10.87	11.31	11.79
	6H	11.08	11.44	11.61	11.96	12.46	11.08	11.44	11.61	11.96	12.46
	8H	11.43	11.74	11.95	12.24	12.82	11.43	11.74	11.95	12.24	12.82