

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866176

Luminaire Tested: PRLX-2002-M-927-35L-L-U-S-X-X-BLAK-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P866176
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-53)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2002-M-927-35L-L-U-S-X-X-BLAK-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, FLAT LENS, TRUNCATED DOME WITH BLACK INTERIOR SHADE.
LIGHT LEVEL 4
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2562.1 lumens
Efficiency: N/A
Efficacy: 85.4 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Circular (Dia: 1.31' x H: 0')
CIE Type: Direct

Input Watts (W): 30
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P866176

CATALOG NUMBER: PRLX-2002-M-927-35L-L-U-S-X-X-BLAK-X

Luminous Intensity Polar Plot





TEST NUMBER: P866176

CATALOG NUMBER: PRLX-2002-M-927-35L-L-U-S-X-X-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	95	93	92	90
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	71	69
4	89	79	72	66	87	78	71	66	75	69	65	73	68	64	71	67	63	61
5	83	71	64	58	81	70	63	58	68	62	57	67	61	57	65	60	56	54
6	77	65	57	51	75	64	57	51	62	56	51	61	55	50	59	54	50	48
7	71	59	51	46	70	58	51	46	57	50	45	56	50	45	54	49	45	43
8	67	54	47	41	65	54	46	41	52	46	41	51	45	41	50	45	41	39
9	62	50	43	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	10245
5°	10206
10°	10080
15°	9903
20°	9684
25°	9456
30°	9202
35°	8910
40°	8568
45°	8213
50°	7781
55°	6738
60°	3448
65°	668
70°	63
75°	83
80°	82
85°	82

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8213 cd/sqm

TEST NUMBER: P866176

CATALOG NUMBER: PRLX-2002-M-927-35L-L-U-S-X-X-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.0	4.7
10°-20°	338.6	13.2
20°-30°	495.8	19.3
30°-40°	572.1	22.3
40°-50°	560.9	21.9
50°-60°	407.6	15.9
60°-70°	62.5	2.4
70°-80°	2.5	0.1
80°-90°	1.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	955.3	37.3
0°-40°	1527.4	59.6
0°-60°	2495.9	97.4
0°-90°	2562.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2562.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1288	
5°	1278	121
15°	1202	339
25°	1077	496
35°	917	572
45°	730	561
55°	486	408
65°	36	62
75°	3	2
85°	1	1
90°	0	

TEST NUMBER: P866176

CATALOG NUMBER: PRLX-2002-M-927-35L-L-U-S-X-X-BLAK-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	1287.7
2.5°	1285.9
5°	1277.9
7.5°	1264.6
10°	1247.7
12.5°	1226.4
15°	1202.4
17.5°	1174.0
20°	1143.8
22.5°	1111.0
25°	1077.2
27.5°	1039.9
30°	1001.7
32.5°	957.3
35°	917.4
37.5°	868.5
40°	825.0
42.5°	775.3
45°	730.0
47.5°	675.8
50°	628.7
52.5°	565.7
55°	485.8
57.5°	358.8
60°	216.7
62.5°	103.0
65°	35.5
67.5°	8.9
70°	2.7
72.5°	2.7
75°	2.7
77.5°	1.8
80°	1.8
82.5°	1.8
85°	0.9
87.5°	0.9
90°	0.0

TEST NUMBER: P866176
 CATALOG NUMBER: PRLX-2002-M-927-35L-L-U-S-X-X-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.52	18.93	17.88	19.25	19.56	17.52	18.93	17.88	19.25	19.56
	3H	17.40	18.64	17.78	18.97	19.34	17.40	18.64	17.78	18.97	19.34
	4H	17.34	18.49	17.74	18.84	19.22	17.34	18.49	17.74	18.84	19.22
	6H	17.26	18.32	17.68	18.69	19.08	17.26	18.32	17.68	18.69	19.08
	8H	17.22	18.22	17.65	18.61	19.02	17.22	18.22	17.65	18.61	19.02
	12H	17.18	18.14	17.62	18.52	18.95	17.18	18.14	17.62	18.52	18.95
4H	2H	17.36	18.51	17.76	18.86	19.24	17.36	18.51	17.76	18.86	19.24
	3H	17.24	18.17	17.65	18.57	18.97	17.24	18.17	17.65	18.57	18.97
	4H	17.16	17.98	17.60	18.40	18.84	17.16	17.98	17.60	18.40	18.84
	6H	17.09	17.79	17.55	18.24	18.70	17.09	17.79	17.55	18.24	18.70
	8H	17.03	17.69	17.50	18.14	18.61	17.03	17.69	17.50	18.14	18.61
	12H	16.99	17.57	17.47	18.05	18.53	16.99	17.57	17.47	18.05	18.53
8H	4H	17.03	17.69	17.50	18.14	18.61	17.03	17.69	17.50	18.14	18.61
	6H	16.93	17.47	17.43	17.97	18.45	16.93	17.47	17.43	17.97	18.45
	8H	16.86	17.36	17.38	17.87	18.36	16.86	17.36	17.38	17.87	18.36
	12H	16.81	17.26	17.32	17.75	18.32	16.81	17.26	17.32	17.75	18.32
12H	4H	16.98	17.57	17.47	18.05	18.53	16.98	17.57	17.47	18.05	18.53
	6H	16.86	17.36	17.38	17.87	18.36	16.86	17.36	17.38	17.87	18.36
	8H	16.81	17.26	17.32	17.75	18.32	16.81	17.26	17.32	17.75	18.32