

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865777

Luminaire Tested: PRLX-2004-S-930-05L-L-U-S-X-X-BRSS-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P865777
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-24)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2004-S-930-05L-L-U-S-X-X-BRSS-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, FLAT LENS, BELL WITH BRASS INTERIOR SHADE.
LIGHT LEVEL 1
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 249.1 lumens
Efficiency: N/A
Efficacy: 40.2 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.02
Luminous Opening: Circular (Dia: 0.92' x H: 0')
CIE Type: Direct

Input Watts (W): 6.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P865777

CATALOG NUMBER: PRLX-2004-S-930-05L-L-U-S-X-X-BRSS-X

Luminous Intensity Polar Plot





TEST NUMBER: P865777

CATALOG NUMBER: PRLX-2004-S-930-05L-L-U-S-X-X-BRSS-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	104	110	107	105	103	103	101	99	99	98	96	96	95	94	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77
4	94	86	80	75	93	85	79	75	83	78	74	81	76	73	79	75	72	70
5	89	80	73	69	87	79	73	68	77	72	68	75	71	67	74	70	67	65
6	84	74	68	63	83	74	67	63	72	67	62	71	66	62	69	65	62	60
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	60	57	56
8	75	65	58	54	74	64	58	54	63	58	54	62	57	53	61	57	53	52
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	58	53	50	48
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3608
5°	3502
10°	3349
15°	3232
20°	3112
25°	3016
30°	2914
35°	2324
40°	901
45°	360
50°	241
55°	233
60°	225
65°	201
70°	186
75°	189
80°	160
85°	168

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 360 cd/sqm

TEST NUMBER: P865777

CATALOG NUMBER: PRLX-2004-S-930-05L-L-U-S-X-X-BRSS-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	20.0	8.0
10°-20°	53.8	21.6
20°-30°	77.2	31.0
30°-40°	66.7	26.8
40°-50°	14.7	5.9
50°-60°	7.3	2.9
60°-70°	5.3	2.1
70°-80°	3.1	1.3
80°-90°	0.9	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	151.1	60.6
0°-40°	217.8	87.4
0°-60°	239.8	96.2
0°-90°	249.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	249.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	221	
5°	214	20
15°	191	54
25°	168	77
35°	117	67
45°	16	15
55°	8	7
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P865777

CATALOG NUMBER: PRLX-2004-S-930-05L-L-U-S-X-X-BRSS-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	221.2
2.5°	219.9
5°	213.9
7.5°	207.8
10°	202.2
12.5°	197.0
15°	191.4
17.5°	185.4
20°	179.3
22.5°	173.3
25°	167.6
27.5°	162.0
30°	154.7
32.5°	141.3
35°	116.7
37.5°	77.3
40°	42.3
42.5°	25.1
45°	15.6
47.5°	10.8
50°	9.5
52.5°	9.1
55°	8.2
57.5°	7.3
60°	6.9
62.5°	6.0
65°	5.2
67.5°	4.8
70°	3.9
72.5°	3.5
75°	3.0
77.5°	2.6
80°	1.7
82.5°	1.3
85°	0.9
87.5°	0.4
90°	0.0

TEST NUMBER: P865777

CATALOG NUMBER: PRLX-2004-S-930-05L-L-U-S-X-X-BRSS-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	1.67	2.73	2.03	3.04	3.36	1.67	2.73	2.03	3.04	3.36
	3H	3.33	4.28	3.72	4.61	4.98	3.33	4.28	3.72	4.61	4.98
	4H	4.01	4.88	4.41	5.24	5.62	4.01	4.88	4.41	5.24	5.62
	6H	4.54	5.34	4.96	5.72	6.11	4.54	5.34	4.96	5.72	6.11
	8H	4.69	5.44	5.12	5.83	6.24	4.69	5.44	5.12	5.83	6.24
	12H	4.80	5.52	5.23	5.90	6.33	4.80	5.52	5.23	5.90	6.33
4H	2H	2.15	3.02	2.55	3.37	3.76	2.15	3.02	2.55	3.37	3.76
	3H	4.02	4.73	4.43	5.14	5.55	4.02	4.73	4.43	5.14	5.55
	4H	4.84	5.48	5.28	5.90	6.35	4.84	5.48	5.28	5.90	6.35
	6H	5.50	6.05	5.96	6.49	6.97	5.50	6.05	5.96	6.49	6.97
	8H	5.68	6.19	6.16	6.64	7.12	5.68	6.19	6.16	6.64	7.12
	12H	5.84	6.29	6.33	6.77	7.25	5.84	6.29	6.33	6.77	7.25
8H	4H	5.11	5.62	5.59	6.07	6.55	5.11	5.62	5.59	6.07	6.55
	6H	5.88	6.29	6.39	6.79	7.27	5.88	6.29	6.39	6.79	7.27
	8H	6.15	6.51	6.68	7.03	7.53	6.15	6.51	6.68	7.03	7.53
	12H	6.41	6.72	6.93	7.22	7.80	6.41	6.72	6.93	7.22	7.80
12H	4H	5.11	5.56	5.60	6.04	6.52	5.11	5.56	5.60	6.04	6.52
	6H	5.91	6.28	6.44	6.80	7.29	5.91	6.28	6.44	6.80	7.29
	8H	6.24	6.56	6.76	7.06	7.63	6.24	6.56	6.76	7.06	7.63