

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865790

Luminaire Tested: PRLX-2004-S-930-15L-G-U-S-X-X-GREY-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P865790
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-13)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2004-S-930-15L-G-U-S-X-X-GREY-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, GLOBE LENS,
BELL WITH GRAY INTERIOR SHADE.
LIGHT LEVEL 3
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 268.8 lumens
Efficiency: N/A
Efficacy: 17.2 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.16
Luminous Opening: Circular (Dia: 0.92' x H: 0')
CIE Type: Direct

Input Watts (W): 15.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P865790

CATALOG NUMBER: PRLX-2004-S-930-15L-G-U-S-X-X-GREY-X

Luminous Intensity Polar Plot





TEST NUMBER: P865790

CATALOG NUMBER: PRLX-2004-S-930-15L-G-U-S-X-X-GREY-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76	82	78	75	80	76	73	72
4	91	81	74	69	89	80	74	68	78	72	68	76	71	67	74	69	66	64
5	85	74	67	62	83	73	66	61	71	65	61	70	64	60	68	63	60	58
6	79	68	61	55	78	67	60	55	66	59	55	64	59	54	63	58	54	52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47
8	70	58	51	46	68	57	51	46	56	50	45	55	49	45	54	49	45	43
9	66	54	47	42	64	53	47	42	52	46	42	51	46	42	50	45	41	40
10	62	50	43	39	61	50	43	39	49	43	38	48	42	38	47	42	38	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2613
5°	2616
10°	2615
15°	2594
20°	2558
25°	2498
30°	2381
35°	2111
40°	1771
45°	1400
50°	1007
55°	620
60°	362
65°	309
70°	277
75°	246
80°	235
85°	225

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1400 cd/sqm

TEST NUMBER: P865790

CATALOG NUMBER: PRLX-2004-S-930-15L-G-U-S-X-X-GREY-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	15.2	5.7
10°-20°	43.3	16.1
20°-30°	63.7	23.7
30°-40°	65.8	24.5
40°-50°	46.8	17.4
50°-60°	20.5	7.6
60°-70°	8.1	3.0
70°-80°	4.2	1.6
80°-90°	1.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	122.2	45.4
0°-40°	188.0	69.9
0°-60°	255.2	94.9
0°-90°	268.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	268.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	160	
5°	160	15
15°	154	43
25°	139	64
35°	106	66
45°	61	47
55°	22	20
65°	8	8
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P865790

CATALOG NUMBER: PRLX-2004-S-930-15L-G-U-S-X-X-GREY-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	160.2
2.5°	160.2
5°	159.8
7.5°	159.0
10°	157.9
12.5°	156.1
15°	153.6
17.5°	150.7
20°	147.4
22.5°	143.4
25°	138.8
27.5°	133.5
30°	126.4
32.5°	116.8
35°	106.0
37.5°	94.8
40°	83.2
42.5°	71.8
45°	60.7
47.5°	50.0
50°	39.7
52.5°	30.2
55°	21.8
57.5°	15.0
60°	11.1
62.5°	9.3
65°	8.0
67.5°	6.9
70°	5.8
72.5°	4.8
75°	3.9
77.5°	3.2
80°	2.5
82.5°	1.8
85°	1.2
87.5°	0.5
90°	0.0



TEST NUMBER: P865790
 CATALOG NUMBER: PRLX-2004-S-930-15L-G-U-S-X-X-GREY-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.01	7.31	6.38	7.62	7.93	6.01	7.31	6.38	7.62	7.93
	3H	6.95	8.09	7.33	8.42	8.79	6.95	8.09	7.33	8.42	8.79
	4H	7.30	8.37	7.71	8.72	9.10	7.30	8.37	7.71	8.72	9.10
	6H	7.60	8.57	8.01	8.94	9.34	7.60	8.57	8.01	8.94	9.34
	8H	7.70	8.62	8.13	9.01	9.42	7.70	8.62	8.13	9.01	9.42
	12H	7.77	8.65	8.20	9.03	9.46	7.77	8.65	8.20	9.03	9.46
4H	2H	6.25	7.31	6.65	7.66	8.05	6.25	7.31	6.65	7.66	8.05
	3H	7.41	8.27	7.82	8.68	9.08	7.41	8.27	7.82	8.68	9.08
	4H	7.88	8.65	8.31	9.07	9.51	7.88	8.65	8.31	9.07	9.51
	6H	8.30	8.97	8.76	9.41	9.88	8.30	8.97	8.76	9.41	9.88
	8H	8.44	9.07	8.91	9.51	9.99	8.44	9.07	8.91	9.51	9.99
	12H	8.56	9.11	9.05	9.59	10.07	8.56	9.11	9.05	9.59	10.07
8H	4H	8.02	8.64	8.49	9.09	9.56	8.02	8.64	8.49	9.09	9.56
	6H	8.56	9.06	9.06	9.56	10.04	8.56	9.06	9.06	9.56	10.04
	8H	8.77	9.23	9.29	9.74	10.24	8.77	9.23	9.29	9.74	10.24
	12H	8.96	9.37	9.48	9.86	10.44	8.96	9.37	9.48	9.86	10.44
12H	4H	8.02	8.57	8.50	9.05	9.52	8.02	8.57	8.50	9.05	9.52
	6H	8.57	9.03	9.10	9.55	10.04	8.57	9.03	9.10	9.55	10.04
	8H	8.84	9.25	9.36	9.74	10.32	8.84	9.25	9.36	9.74	10.32