

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866213

Luminaire Tested: PRLX-2002-M-930-07L-G-U-S-X-X-BRSS-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P866213
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-39)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2002-M-930-07L-G-U-S-X-X-BRSS-X
Description: PRENATALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, GLOBE LENS, TRUNCATED DOME WITH BRASS INTERIOR SHADE.
LIGHT LEVEL 1
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 264.4 lumens
Efficiency: N/A
Efficacy: 32.2 lumens/watt
Spacing Criteria (0/90/45): 1.36 / 1.36 / 1.53
Luminous Opening: Circular (Dia: 1.31' x H: 0')
CIE Type: Direct

Input Watts (W): 8.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P866213

CATALOG NUMBER: PRLX-2002-M-930-07L-G-U-S-X-X-BRSS-X

Luminous Intensity Polar Plot





TEST NUMBER: P866213

CATALOG NUMBER: PRLX-2002-M-930-07L-G-U-S-X-X-BRSS-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	105	101	97	93	97	93	90	93	90	87	89	87	85	83
2	98	89	82	76	95	87	81	75	84	78	73	80	76	72	77	73	70	68
3	89	78	69	62	86	76	68	62	73	66	61	70	64	60	68	63	58	56
4	81	68	59	52	78	67	58	52	64	57	51	62	56	50	60	54	50	47
5	74	61	51	44	72	59	51	44	57	50	44	55	48	43	53	47	43	40
6	68	54	45	38	66	53	45	38	51	44	38	50	43	37	48	42	37	35
7	63	49	40	34	61	48	40	33	47	39	33	45	38	33	44	37	33	31
8	59	45	36	30	57	44	35	30	42	35	29	41	34	29	40	34	29	27
9	55	41	32	27	53	40	32	26	39	31	26	38	31	26	37	31	26	24
10	51	37	29	24	50	37	29	24	36	29	24	35	28	24	34	28	23	22

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	620
5°	621
10°	625
15°	626
20°	630
25°	635
30°	647
35°	663
40°	689
45°	718
50°	739
55°	739
60°	726
65°	697
70°	651
75°	593
80°	518
85°	411

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 52.5°
 Luminance: 744 cd/sqm

TEST NUMBER: P866213

CATALOG NUMBER: PRLX-2002-M-930-07L-G-U-S-X-X-BRSS-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	7.4	2.8
10°-20°	21.5	8.1
20°-30°	33.4	12.6
30°-40°	42.9	16.2
40°-50°	49.1	18.6
50°-60°	47.5	18.0
60°-70°	36.6	13.8
70°-80°	20.5	7.8
80°-90°	5.4	2.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	62.3	23.6
0°-40°	105.2	39.8
0°-60°	201.9	76.3
0°-90°	264.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	264.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	78	
5°	78	7
15°	76	21
25°	72	33
35°	68	43
45°	64	49
55°	53	48
65°	37	37
75°	19	21
85°	4	5
90°	0	

TEST NUMBER: P866213

CATALOG NUMBER: PRLX-2002-M-930-07L-G-U-S-X-X-BRSS-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	77.9
2.5°	77.9
5°	77.7
7.5°	77.5
10°	77.4
12.5°	76.8
15°	76.0
17.5°	75.1
20°	74.4
22.5°	73.2
25°	72.3
27.5°	71.4
30°	70.4
32.5°	69.3
35°	68.3
37.5°	67.4
40°	66.3
42.5°	65.3
45°	63.8
47.5°	62.0
50°	59.7
52.5°	56.9
55°	53.3
57.5°	49.6
60°	45.6
62.5°	41.5
65°	37.0
67.5°	32.7
70°	28.0
72.5°	23.7
75°	19.3
77.5°	15.2
80°	11.3
82.5°	7.7
85°	4.5
87.5°	2.1
90°	0.0



TEST NUMBER: P866213
 CATALOG NUMBER: PRLX-2002-M-930-07L-G-U-S-X-X-BRSS-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.46	13.16	11.82	13.47	13.79	11.46	13.16	11.82	13.47	13.79
	3H	13.27	14.81	13.64	15.14	15.50	13.27	14.81	13.64	15.14	15.50
	4H	13.92	15.38	14.32	15.72	16.10	13.92	15.38	14.32	15.72	16.10
	6H	14.38	15.73	14.79	16.10	16.49	14.38	15.73	14.79	16.10	16.49
	8H	14.52	15.81	14.94	16.20	16.60	14.52	15.81	14.94	16.20	16.60
	12H	14.61	15.85	15.04	16.23	16.66	14.61	15.85	15.04	16.23	16.66
4H	2H	12.11	13.57	12.51	13.91	14.29	12.11	13.57	12.51	13.91	14.29
	3H	14.13	15.36	14.54	15.75	16.15	14.13	15.36	14.54	15.75	16.15
	4H	14.90	16.01	15.33	16.43	16.86	14.90	16.01	15.33	16.43	16.86
	6H	15.49	16.46	15.94	16.90	17.35	15.49	16.46	15.94	16.90	17.35
	8H	15.67	16.58	16.13	17.03	17.49	15.67	16.58	16.13	17.03	17.49
	12H	15.80	16.62	16.28	17.10	17.56	15.80	16.62	16.28	17.10	17.56
8H	4H	15.21	16.12	15.67	16.57	17.03	15.21	16.12	15.67	16.57	17.03
	6H	15.91	16.67	16.40	17.16	17.63	15.91	16.67	16.40	17.16	17.63
	8H	16.16	16.84	16.67	17.35	17.83	16.16	16.84	16.67	17.35	17.83
	12H	16.35	16.96	16.86	17.44	18.00	16.35	16.96	16.86	17.44	18.00
12H	4H	15.25	16.07	15.73	16.54	17.01	15.25	16.07	15.73	16.54	17.01
	6H	15.96	16.65	16.47	17.15	17.63	15.96	16.65	16.47	17.15	17.63
	8H	16.27	16.87	16.77	17.36	17.92	16.27	16.87	16.77	17.36	17.92