

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866218

Luminaire Tested: PRLX-2002-M-930-07L-L-U-S-X-X-GREY-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P866218  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-52)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2002-M-930-07L-L-U-S-X-X-GREY-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, FLAT LENS, TRUNCATED DOME WITH GRAY INTERIOR SHADE.  
LIGHT LEVEL 1  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 576.2 lumens  
Efficiency: N/A  
Efficacy: 70.3 lumens/watt  
Spacing Criteria (0/90/45): 1.15 / 1.15 / 1.27  
Luminous Opening: Circular (Dia: 1.31' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 8.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.5 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P866218

CATALOG NUMBER: PRLX-2002-M-930-07L-L-U-S-X-X-GREY-X

### Luminous Intensity Polar Plot





TEST NUMBER: P866218

CATALOG NUMBER: PRLX-2002-M-930-07L-L-U-S-X-X-GREY-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89
2	103	97	91	87	101	95	90	86	92	88	84	89	85	82	86	83	80	78
3	96	87	80	75	93	86	79	74	83	77	73	80	76	72	78	74	71	69
4	89	78	71	65	86	77	70	65	75	69	64	73	67	63	71	66	62	60
5	82	71	63	57	80	70	63	57	68	61	56	66	60	56	64	59	55	53
6	76	64	56	51	74	64	56	51	62	55	50	60	54	50	59	53	49	48
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	48	44	43
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	40	36	35
10	58	46	39	34	57	45	38	34	45	38	34	44	38	33	43	37	33	32

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2289
5°	2279
10°	2248
15°	2202
20°	2151
25°	2094
30°	2032
35°	1964
40°	1890
45°	1813
50°	1718
55°	1513
60°	807
65°	213
70°	88
75°	98
80°	110
85°	137

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1813 cd/sqm

TEST NUMBER: P866218

CATALOG NUMBER: PRLX-2002-M-930-07L-L-U-S-X-X-GREY-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	27.0	4.7
10°-20°	75.3	13.1
20°-30°	109.8	19.1
30°-40°	126.4	21.9
40°-50°	124.0	21.5
50°-60°	91.8	15.9
60°-70°	17.0	2.9
70°-80°	3.4	0.6
80°-90°	1.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	212.1	36.8
0°-40°	338.5	58.7
0°-60°	554.3	96.2
0°-90°	576.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	576.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	288	
5°	285	27
15°	267	75
25°	238	110
35°	202	126
45°	161	124
55°	109	92
65°	11	17
75°	3	3
85°	2	2
90°	0	

TEST NUMBER: P866218

CATALOG NUMBER: PRLX-2002-M-930-07L-L-U-S-X-X-GREY-X

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	287.7
2.5°	287.3
5°	285.4
7.5°	282.4
10°	278.3
12.5°	273.2
15°	267.4
17.5°	260.8
20°	254.1
22.5°	246.5
25°	238.5
27.5°	230.0
30°	221.2
32.5°	211.8
35°	202.2
37.5°	192.1
40°	182.0
42.5°	171.4
45°	161.1
47.5°	149.8
50°	138.8
52.5°	126.6
55°	109.1
57.5°	82.4
60°	50.7
62.5°	26.1
65°	11.3
67.5°	4.9
70°	3.8
72.5°	3.6
75°	3.2
77.5°	2.8
80°	2.4
82.5°	2.1
85°	1.5
87.5°	0.8
90°	0.0



TEST NUMBER: P866218  
 CATALOG NUMBER: PRLX-2002-M-930-07L-L-U-S-X-X-GREY-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.47	13.90	12.83	14.21	14.52	12.47	13.90	12.83	14.21	14.52
	3H	12.37	13.63	12.75	13.95	14.32	12.37	13.63	12.75	13.95	14.32
	4H	12.31	13.48	12.72	13.83	14.21	12.31	13.48	12.72	13.83	14.21
	6H	12.26	13.33	12.67	13.70	14.09	12.26	13.33	12.67	13.70	14.09
	8H	12.23	13.25	12.66	13.64	14.04	12.23	13.25	12.66	13.64	14.04
	12H	12.20	13.17	12.63	13.56	13.99	12.20	13.17	12.63	13.56	13.99
4H	2H	12.32	13.49	12.72	13.84	14.22	12.32	13.49	12.72	13.84	14.22
	3H	12.23	13.18	12.65	13.58	13.98	12.23	13.18	12.65	13.58	13.98
	4H	12.17	13.01	12.61	13.43	13.87	12.17	13.01	12.61	13.43	13.87
	6H	12.13	12.85	12.59	13.30	13.76	12.13	12.85	12.59	13.30	13.76
	8H	12.09	12.77	12.56	13.22	13.69	12.09	12.77	12.56	13.22	13.69
	12H	12.07	12.67	12.55	13.15	13.62	12.07	12.67	12.55	13.15	13.62
8H	4H	12.06	12.73	12.53	13.18	13.65	12.06	12.73	12.53	13.18	13.65
	6H	12.00	12.56	12.50	13.05	13.53	12.00	12.56	12.50	13.05	13.53
	8H	11.96	12.47	12.48	12.98	13.47	11.96	12.47	12.48	12.98	13.47
	12H	11.95	12.40	12.46	12.90	13.46	11.95	12.40	12.46	12.90	13.46
12H	4H	12.02	12.62	12.50	13.10	13.57	12.02	12.62	12.50	13.10	13.57
	6H	11.94	12.45	12.46	12.96	13.45	11.94	12.45	12.46	12.96	13.45
	8H	11.93	12.38	12.44	12.88	13.44	11.93	12.38	12.44	12.88	13.44