

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866219

Luminaire Tested: PRLX-2002-M-930-07L-L-U-S-X-X-WHHR-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P866219
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-50)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2002-M-930-07L-L-U-S-X-X-WHHR-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, FLAT LENS, TRUNCATED DOME WITH WHITE INTERIOR SHADE.
LIGHT LEVEL 1
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 700.4 lumens
Efficiency: N/A
Efficacy: 85.4 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.3
Luminous Opening: Circular (Dia: 1.31' x H: 0')
CIE Type: Direct

Input Watts (W): 8.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.333 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P866219

CATALOG NUMBER: PRLX-2002-M-930-07L-L-U-S-X-X-WHHR-X

Luminous Intensity Polar Plot





TEST NUMBER: P866219

CATALOG NUMBER: PRLX-2002-M-930-07L-L-U-S-X-X-WHHR-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	89	87
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	83	80	78	76
3	94	85	77	72	92	83	76	71	80	75	70	78	73	69	75	71	68	66
4	87	76	68	62	84	75	67	62	72	66	61	70	64	60	68	63	59	57
5	80	68	60	54	78	67	60	54	65	58	53	63	57	53	62	56	52	50
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40
8	64	52	44	38	63	51	43	38	50	43	38	48	42	38	47	42	37	36
9	60	47	40	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	41	35	31	29

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2495
5°	2486
10°	2462
15°	2426
20°	2385
25°	2339
30°	2289
35°	2232
40°	2173
45°	2106
50°	2029
55°	1891
60°	1270
65°	601
70°	442
75°	473
80°	527
85°	584

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2106 cd/sqm

TEST NUMBER: P866219

CATALOG NUMBER: PRLX-2002-M-930-07L-L-U-S-X-X-WHHR-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.5	4.2
10°-20°	83.0	11.9
20°-30°	122.7	17.5
30°-40°	143.8	20.5
40°-50°	144.3	20.6
50°-60°	116.5	16.6
60°-70°	37.6	5.4
70°-80°	16.3	2.3
80°-90°	6.7	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	235.2	33.6
0°-40°	379.0	54.1
0°-60°	639.7	91.3
0°-90°	700.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	700.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	314	
5°	311	30
15°	295	83
25°	266	123
35°	230	144
45°	187	144
55°	136	116
65°	32	38
75°	15	16
85°	6	7
90°	0	

TEST NUMBER: P866219

CATALOG NUMBER: PRLX-2002-M-930-07L-L-U-S-X-X-WHHR-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	313.6
2.5°	313.2
5°	311.3
7.5°	308.5
10°	304.8
12.5°	299.9
15°	294.6
17.5°	288.2
20°	281.7
22.5°	274.3
25°	266.4
27.5°	258.0
30°	249.2
32.5°	239.8
35°	229.8
37.5°	219.7
40°	209.2
42.5°	198.3
45°	187.2
47.5°	175.8
50°	163.9
52.5°	151.7
55°	136.3
57.5°	112.5
60°	79.8
62.5°	49.9
65°	31.9
67.5°	22.0
70°	19.0
72.5°	17.5
75°	15.4
77.5°	13.5
80°	11.5
82.5°	9.2
85°	6.4
87.5°	3.4
90°	0.0



TEST NUMBER: P866219
 CATALOG NUMBER: PRLX-2002-M-930-07L-L-U-S-X-X-WHHR-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.91	15.41	14.28	15.73	16.04	13.91	15.41	14.28	15.73	16.04
	3H	14.02	15.35	14.40	15.68	16.04	14.02	15.35	14.40	15.68	16.04
	4H	14.11	15.35	14.51	15.70	16.08	14.11	15.35	14.51	15.70	16.08
	6H	14.22	15.37	14.64	15.74	16.13	14.22	15.37	14.64	15.74	16.13
	8H	14.28	15.37	14.71	15.76	16.16	14.28	15.37	14.71	15.76	16.16
	12H	14.33	15.37	14.76	15.75	16.18	14.33	15.37	14.76	15.75	16.18
4H	2H	13.88	15.12	14.28	15.47	15.85	13.88	15.12	14.28	15.47	15.85
	3H	14.08	15.10	14.49	15.50	15.90	14.08	15.10	14.49	15.50	15.90
	4H	14.24	15.15	14.67	15.56	16.00	14.24	15.15	14.67	15.56	16.00
	6H	14.46	15.25	14.92	15.69	16.15	14.46	15.25	14.92	15.69	16.15
	8H	14.56	15.30	15.03	15.75	16.21	14.56	15.30	15.03	15.75	16.21
	12H	14.66	15.32	15.15	15.80	16.28	14.66	15.32	15.15	15.80	16.28
8H	4H	14.25	14.99	14.72	15.44	15.91	14.25	14.99	14.72	15.44	15.91
	6H	14.55	15.17	15.05	15.66	16.14	14.55	15.17	15.05	15.66	16.14
	8H	14.72	15.28	15.24	15.79	16.28	14.72	15.28	15.24	15.79	16.28
	12H	14.90	15.39	15.41	15.89	16.45	14.90	15.39	15.41	15.89	16.45
12H	4H	14.24	14.90	14.73	15.38	15.86	14.24	14.90	14.73	15.38	15.86
	6H	14.56	15.11	15.07	15.62	16.11	14.56	15.11	15.07	15.62	16.11
	8H	14.78	15.27	15.29	15.76	16.33	14.78	15.27	15.29	15.76	16.33