

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865804

Luminaire Tested: PRLX-2004-S-930-25L-G-U-S-X-X-BLAK-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P865804  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-14)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2004-S-930-25L-G-U-S-X-X-BLAK-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, GLOBE LENS,  
BELL WITH BLACK INTERIOR SHADE.  
LIGHT LEVEL 5  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 307.9 lumens  
Efficiency: N/A  
Efficacy: 10.6 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.2  
Luminous Opening: Circular (Dia: 0.92' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 29.1  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.5 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P865804

CATALOG NUMBER: PRLX-2004-S-930-25L-G-U-S-X-X-BLAK-X

### Luminous Intensity Polar Plot





TEST NUMBER: P865804

CATALOG NUMBER: PRLX-2004-S-930-25L-G-U-S-X-X-BLAK-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89	86	84	83
3	99	91	85	81	97	90	84	80	87	82	79		85	81	77		82	79	76	74
4	93	84	77	72	91	82	76	71	80	75	71		78	73	70		76	72	69	67
5	87	77	70	65	85	76	69	64	74	68	64		72	67	63		70	66	62	61
6	81	71	63	58	79	70	63	58	68	62	58		67	61	57		65	60	57	55
7	76	65	58	53	75	64	58	53	63	57	52		62	56	52		60	56	52	50
8	71	60	53	48	70	60	53	48	58	52	48		57	52	48		56	51	47	46
9	67	56	49	44	66	55	49	44	54	48	44		53	48	44		52	47	44	42
10	63	52	45	41	62	52	45	41	51	45	41		50	44	40		49	44	40	39

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	3006
5°	3021
10°	3049
15°	3065
20°	3076
25°	3103
30°	3047
35°	2710
40°	2236
45°	1679
50°	1068
55°	481
60°	98
65°	73
70°	62
75°	57
80°	56
85°	37

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1679 cd/sqm

TEST NUMBER: P865804

CATALOG NUMBER: PRLX-2004-S-930-25L-G-U-S-X-X-BLAK-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	17.6	5.7
10°-20°	51.3	16.6
20°-30°	79.2	25.7
30°-40°	84.2	27.3
40°-50°	55.9	18.2
50°-60°	16.6	5.4
60°-70°	1.9	0.6
70°-80°	0.9	0.3
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	148.0	48.1
0°-40°	232.2	75.4
0°-60°	304.7	99.0
0°-90°	307.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	307.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	184	
5°	184	18
15°	182	51
25°	172	79
35°	136	84
45°	73	56
55°	17	17
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P865804

CATALOG NUMBER: PRLX-2004-S-930-25L-G-U-S-X-X-BLAK-X

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	184.3
2.5°	184.5
5°	184.5
7.5°	184.5
10°	184.1
12.5°	183.0
15°	181.5
17.5°	179.5
20°	177.2
22.5°	175.0
25°	172.4
27.5°	168.9
30°	161.8
32.5°	150.1
35°	136.1
37.5°	121.0
40°	105.0
42.5°	89.0
45°	72.8
47.5°	57.0
50°	42.1
52.5°	28.7
55°	16.9
57.5°	7.3
60°	3.0
62.5°	2.2
65°	1.9
67.5°	1.5
70°	1.3
72.5°	1.1
75°	0.9
77.5°	0.6
80°	0.6
82.5°	0.4
85°	0.2
87.5°	0.2
90°	0.0

TEST NUMBER: P865804

CATALOG NUMBER: PRLX-2004-S-930-25L-G-U-S-X-X-BLAK-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.47	1.67	0.83	1.98	2.30	0.47	1.67	0.83	1.98	2.30
	3H	0.57	1.63	0.96	1.96	2.33	0.57	1.63	0.96	1.96	2.33
	4H	0.63	1.61	1.03	1.96	2.34	0.63	1.61	1.03	1.96	2.34
	6H	0.64	1.53	1.06	1.91	2.30	0.64	1.53	1.06	1.91	2.30
	8H	0.64	1.49	1.07	1.88	2.28	0.64	1.49	1.07	1.88	2.28
	12H	0.62	1.43	1.06	1.81	2.24	0.62	1.43	1.06	1.81	2.24
4H	2H	0.35	1.33	0.75	1.68	2.07	0.35	1.33	0.75	1.68	2.07
	3H	0.55	1.34	0.97	1.75	2.15	0.55	1.34	0.97	1.75	2.15
	4H	0.65	1.35	1.09	1.77	2.22	0.65	1.35	1.09	1.77	2.22
	6H	0.73	1.33	1.20	1.78	2.25	0.73	1.33	1.20	1.78	2.25
	8H	0.75	1.31	1.22	1.76	2.23	0.75	1.31	1.22	1.76	2.23
	12H	0.74	1.23	1.23	1.72	2.20	0.74	1.23	1.23	1.72	2.20
8H	4H	0.59	1.15	1.06	1.60	2.07	0.59	1.15	1.06	1.60	2.07
	6H	0.72	1.17	1.22	1.67	2.15	0.72	1.17	1.22	1.67	2.15
	8H	0.77	1.18	1.29	1.70	2.19	0.77	1.18	1.29	1.70	2.19
	12H	0.79	1.16	1.31	1.65	2.23	0.79	1.16	1.31	1.65	2.23
12H	4H	0.55	1.05	1.04	1.53	2.01	0.55	1.05	1.04	1.53	2.01
	6H	0.68	1.09	1.21	1.61	2.11	0.68	1.09	1.21	1.61	2.11
	8H	0.76	1.13	1.28	1.63	2.20	0.76	1.13	1.28	1.63	2.20