

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866254

Luminaire Tested: PRLX-2002-M-930-55L-G-U-S-X-X-GREY-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P866254  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-40)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2002-M-930-55L-G-U-S-X-X-GREY-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, GLOBE LENS, TRUNCATED DOME WITH GRAY INTERIOR SHADE.  
LIGHT LEVEL 6  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2061.1 lumens  
Efficiency: N/A  
Efficacy: 42.7 lumens/watt  
Spacing Criteria (0/90/45): 1.36 / 1.36 / 1.53  
Luminous Opening: Circular (Dia: 1.31' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 48.3  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.5 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P866254

CATALOG NUMBER: PRLX-2002-M-930-55L-G-U-S-X-X-GREY-X

### Luminous Intensity Polar Plot





TEST NUMBER: P866254

CATALOG NUMBER: PRLX-2002-M-930-55L-G-U-S-X-X-GREY-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	105	101	97	93	97	93	90	93	90	87	89	87	85	83
2	98	89	82	76	95	87	81	75	84	78	73	80	76	72	77	73	70	68
3	89	78	69	62	86	76	68	62	73	66	61	70	64	59	68	63	58	56
4	81	68	59	52	78	67	58	52	64	57	51	62	55	50	60	54	49	47
5	74	61	51	44	72	59	51	44	57	49	44	55	48	43	53	47	43	40
6	68	54	45	38	66	53	44	38	51	44	38	50	43	37	48	42	37	35
7	63	49	40	33	61	48	39	33	47	39	33	45	38	33	44	37	33	31
8	58	44	36	30	57	44	35	30	42	35	29	41	34	29	40	34	29	27
9	55	41	32	26	53	40	32	26	39	31	26	38	31	26	37	31	26	24
10	51	37	29	24	50	37	29	24	36	29	24	35	28	24	34	28	23	22

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	4818
5°	4836
10°	4857
15°	4868
20°	4892
25°	4944
30°	5026
35°	5172
40°	5363
45°	5596
50°	5739
55°	5783
60°	5657
65°	5452
70°	5103
75°	4675
80°	4087
85°	3341

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 55°  
 Luminance: 5783 cd/sqm

TEST NUMBER: P866254

CATALOG NUMBER: PRLX-2002-M-930-55L-G-U-S-X-X-GREY-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	57.7	2.8
10°-20°	167.1	8.1
20°-30°	260.2	12.6
30°-40°	334.0	16.2
40°-50°	382.1	18.5
50°-60°	370.2	18.0
60°-70°	285.7	13.9
70°-80°	161.0	7.8
80°-90°	43.2	2.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	484.9	23.5
0°-40°	818.9	39.7
0°-60°	1571.2	76.2
0°-90°	2061.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2061.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	606	
5°	606	58
15°	591	167
25°	563	260
35°	532	334
45°	497	382
55°	417	370
65°	290	286
75°	152	161
85°	37	43
90°	0	

TEST NUMBER: P866254

CATALOG NUMBER: PRLX-2002-M-930-55L-G-U-S-X-X-GREY-X

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	605.6
2.5°	605.6
5°	605.6
7.5°	604.1
10°	601.2
12.5°	596.8
15°	591.0
17.5°	585.1
20°	577.8
22.5°	570.5
25°	563.2
27.5°	555.9
30°	547.1
32.5°	539.8
35°	532.5
37.5°	525.1
40°	516.4
42.5°	507.6
45°	497.4
47.5°	481.3
50°	463.7
52.5°	441.8
55°	416.9
57.5°	386.2
60°	355.5
62.5°	323.3
65°	289.6
67.5°	254.5
70°	219.4
72.5°	185.8
75°	152.1
77.5°	118.5
80°	89.2
82.5°	61.4
85°	36.6
87.5°	16.1
90°	0.0



TEST NUMBER: P866254  
 CATALOG NUMBER: PRLX-2002-M-930-55L-G-U-S-X-X-GREY-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.58	20.29	18.95	20.60	20.91	18.58	20.29	18.95	20.60	20.91
	3H	20.40	21.94	20.78	22.27	22.63	20.40	21.94	20.78	22.27	22.63
	4H	21.06	22.52	21.46	22.87	23.24	21.06	22.52	21.46	22.87	23.24
	6H	21.53	22.88	21.94	23.24	23.63	21.53	22.88	21.94	23.24	23.63
	8H	21.67	22.97	22.10	23.36	23.75	21.67	22.97	22.10	23.36	23.75
	12H	21.77	23.01	22.20	23.39	23.82	21.77	23.01	22.20	23.39	23.82
4H	2H	19.24	20.70	19.64	21.05	21.42	19.24	20.70	19.64	21.05	21.42
	3H	21.27	22.50	21.68	22.89	23.29	21.27	22.50	21.68	22.89	23.29
	4H	22.06	23.17	22.49	23.58	24.01	22.06	23.17	22.49	23.58	24.01
	6H	22.65	23.62	23.10	24.06	24.51	22.65	23.62	23.10	24.06	24.51
	8H	22.84	23.75	23.29	24.19	24.65	22.84	23.75	23.29	24.19	24.65
	12H	22.97	23.79	23.45	24.27	24.74	22.97	23.79	23.45	24.27	24.74
8H	4H	22.37	23.28	22.83	23.72	24.19	22.37	23.28	22.83	23.72	24.19
	6H	23.07	23.83	23.56	24.32	24.79	23.07	23.83	23.56	24.32	24.79
	8H	23.33	24.01	23.84	24.52	25.00	23.33	24.01	23.84	24.52	25.00
	12H	23.53	24.14	24.04	24.63	25.19	23.53	24.14	24.04	24.63	25.19
12H	4H	22.40	23.23	22.88	23.70	24.17	22.40	23.23	22.88	23.70	24.17
	6H	23.13	23.81	23.63	24.31	24.80	23.13	23.81	23.63	24.31	24.80
	8H	23.44	24.05	23.95	24.53	25.09	23.44	24.05	23.95	24.53	25.09