

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865847

Luminaire Tested: PRLX-2004-S-935-25L-G-U-S-X-X-WHHR-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P865847
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2004-S-935-25L-G-U-S-X-X-WHHR-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, GLOBE LENS,
BELL WITH WHITE INTERIOR SHADE.
LIGHT LEVEL 5
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1353.5 lumens
Efficiency: N/A
Efficacy: 46.5 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.21
Luminous Opening: Circular (Dia: 0.92' x H: 0')
CIE Type: Direct

Input Watts (W): 29.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P865847

CATALOG NUMBER: PRLX-2004-S-935-25L-G-U-S-X-X-WHHR-X

Luminous Intensity Polar Plot





TEST NUMBER: P865847

CATALOG NUMBER: PRLX-2004-S-935-25L-G-U-S-X-X-WHHR-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	102	98	107	103	100	97	99	96	94	95	93	91	92	90	88	86
2	101	94	88	83	99	92	86	82	88	84	80	85	81	78	82	79	76	74
3	93	84	76	70	91	82	75	70	79	73	69	77	72	67	74	70	66	64
4	86	75	67	61	84	74	66	61	71	65	60	69	64	59	67	62	58	56
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	50	46	44
7	69	56	48	43	67	56	48	42	54	47	42	53	47	42	52	46	42	40
8	65	52	44	38	63	51	44	38	50	43	38	49	43	38	48	42	38	36
9	61	48	40	35	59	47	40	35	46	39	35	45	39	35	44	39	34	33
10	57	44	37	32	56	44	37	32	43	36	32	42	36	32	41	36	32	30

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	10367
5°	10369
10°	10339
15°	10312
20°	10247
25°	9974
30°	9500
35°	8737
40°	7850
45°	6991
50°	6085
55°	5275
60°	4573
65°	4191
70°	3991
75°	3705
80°	3616
85°	3387

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6991 cd/sqm

TEST NUMBER: P865847

CATALOG NUMBER: PRLX-2004-S-935-25L-G-U-S-X-X-WHHR-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.2	4.4
10°-20°	172.1	12.7
20°-30°	254.3	18.8
30°-40°	273.3	20.2
40°-50°	234.0	17.3
50°-60°	167.1	12.3
60°-70°	108.8	8.0
70°-80°	63.9	4.7
80°-90°	20.0	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	486.6	35.9
0°-40°	759.8	56.1
0°-60°	1160.9	85.8
0°-90°	1353.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1353.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	636	
5°	633	60
15°	611	172
25°	554	254
35°	439	273
45°	303	234
55°	186	167
65°	109	109
75°	59	64
85°	18	20
90°	0	

TEST NUMBER: P865847

CATALOG NUMBER: PRLX-2004-S-935-25L-G-U-S-X-X-WHHR-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	635.6
2.5°	635.6
5°	633.3
7.5°	631.1
10°	624.3
12.5°	617.5
15°	610.7
17.5°	599.4
20°	590.4
22.5°	574.5
25°	554.2
27.5°	531.5
30°	504.4
32.5°	472.7
35°	438.8
37.5°	402.6
40°	368.7
42.5°	337.0
45°	303.1
47.5°	271.4
50°	239.8
52.5°	212.6
55°	185.5
57.5°	160.6
60°	140.2
62.5°	124.4
65°	108.6
67.5°	95.0
70°	83.7
72.5°	72.4
75°	58.8
77.5°	49.8
80°	38.5
82.5°	27.1
85°	18.1
87.5°	9.0
90°	0.0

TEST NUMBER: P865847

CATALOG NUMBER: PRLX-2004-S-935-25L-G-U-S-X-X-WHHR-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.69	18.18	17.05	18.49	18.81	16.69	18.18	17.05	18.49	18.81
	3H	18.22	19.56	18.60	19.89	20.25	18.22	19.56	18.60	19.89	20.25
	4H	18.84	20.09	19.24	20.44	20.82	18.84	20.09	19.24	20.44	20.82
	6H	19.36	20.52	19.77	20.88	21.28	19.36	20.52	19.77	20.88	21.28
	8H	19.53	20.63	19.95	21.02	21.42	19.53	20.63	19.95	21.02	21.42
	12H	19.65	20.71	20.08	21.09	21.52	19.65	20.71	20.08	21.09	21.52
4H	2H	17.19	18.44	17.59	18.79	19.17	17.19	18.44	17.59	18.79	19.17
	3H	18.98	20.02	19.39	20.42	20.82	18.98	20.02	19.39	20.42	20.82
	4H	19.73	20.67	20.16	21.08	21.52	19.73	20.67	20.16	21.08	21.52
	6H	20.39	21.21	20.85	21.65	22.11	20.39	21.21	20.85	21.65	22.11
	8H	20.61	21.38	21.08	21.82	22.29	20.61	21.38	21.08	21.82	22.29
	12H	20.79	21.47	21.27	21.95	22.42	20.79	21.47	21.27	21.95	22.42
8H	4H	20.02	20.78	20.48	21.23	21.70	20.02	20.78	20.48	21.23	21.70
	6H	20.82	21.45	21.31	21.94	22.42	20.82	21.45	21.31	21.94	22.42
	8H	21.12	21.69	21.63	22.20	22.69	21.12	21.69	21.63	22.20	22.69
	12H	21.39	21.89	21.89	22.38	22.95	21.39	21.89	21.89	22.38	22.95
12H	4H	20.05	20.73	20.53	21.21	21.68	20.05	20.73	20.53	21.21	21.68
	6H	20.87	21.44	21.39	21.95	22.44	20.87	21.44	21.39	21.95	22.44
	8H	21.24	21.74	21.75	22.24	22.80	21.24	21.74	21.75	22.24	22.80