

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866256

Luminaire Tested: PRLX-2002-M-930-55L-L-U-S-X-X-BLAK-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P866256
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-53)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2002-M-930-55L-L-U-S-X-X-BLAK-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, FLAT LENS, TRUNCATED DOME WITH BLACK INTERIOR SHADE.
LIGHT LEVEL 6
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4220.3 lumens
Efficiency: N/A
Efficacy: 87.4 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Circular (Dia: 1.31' x H: 0')
CIE Type: Direct

Input Watts (W): 48.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P866256

CATALOG NUMBER: PRLX-2002-M-930-55L-L-U-S-X-X-BLAK-X

Luminous Intensity Polar Plot





TEST NUMBER: P866256

CATALOG NUMBER: PRLX-2002-M-930-55L-L-U-S-X-X-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	95	93	92	90
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	71	69
4	89	79	72	66	87	78	71	66	75	69	65	73	68	64	71	67	63	61
5	83	71	64	58	81	70	63	58	68	62	57	67	61	57	65	60	56	54
6	77	65	57	51	75	64	57	51	62	56	51	61	55	50	59	54	50	48
7	71	59	51	46	70	58	51	46	57	50	45	56	50	45	54	49	45	43
8	67	54	47	41	65	54	46	41	52	46	41	51	45	41	50	45	41	39
9	62	50	43	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	16875
5°	16811
10°	16604
15°	16314
20°	15951
25°	15576
30°	15159
35°	14676
40°	14114
45°	13528
50°	12819
55°	11099
60°	5679
65°	1101
70°	102
75°	135
80°	133
85°	137

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 13528 cd/sqm

TEST NUMBER: P866256

CATALOG NUMBER: PRLX-2002-M-930-55L-L-U-S-X-X-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	199.3	4.7
10°-20°	557.7	13.2
20°-30°	816.6	19.3
30°-40°	942.4	22.3
40°-50°	924.0	21.9
50°-60°	671.4	15.9
60°-70°	102.9	2.4
70°-80°	4.1	0.1
80°-90°	2.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1573.6	37.3
0°-40°	2516.0	59.6
0°-60°	4111.3	97.4
0°-90°	4220.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4220.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2121	
5°	2105	199
15°	1981	558
25°	1774	817
35°	1511	942
45°	1202	924
55°	800	671
65°	58	103
75°	4	4
85°	2	2
90°	0	

TEST NUMBER: P866256

CATALOG NUMBER: PRLX-2002-M-930-55L-L-U-S-X-X-BLAK-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	2121.1
2.5°	2118.2
5°	2105.0
7.5°	2083.1
10°	2055.3
12.5°	2020.1
15°	1980.7
17.5°	1933.8
20°	1884.1
22.5°	1830.0
25°	1774.4
27.5°	1713.0
30°	1650.1
32.5°	1576.9
35°	1511.1
37.5°	1430.6
40°	1359.0
42.5°	1277.0
45°	1202.4
47.5°	1113.2
50°	1035.7
52.5°	931.8
55°	800.2
57.5°	591.0
60°	356.9
62.5°	169.7
65°	58.5
67.5°	14.6
70°	4.4
72.5°	4.4
75°	4.4
77.5°	2.9
80°	2.9
82.5°	2.9
85°	1.5
87.5°	1.5
90°	0.0



TEST NUMBER: P866256
 CATALOG NUMBER: PRLX-2002-M-930-55L-L-U-S-X-X-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.25	20.67	19.62	20.98	21.29	19.25	20.67	19.62	20.98	21.29
	3H	19.14	20.38	19.51	20.71	21.07	19.14	20.38	19.51	20.71	21.07
	4H	19.07	20.22	19.47	20.57	20.95	19.07	20.22	19.47	20.57	20.95
	6H	19.00	20.05	19.41	20.42	20.82	19.00	20.05	19.41	20.42	20.82
	8H	18.96	19.96	19.39	20.35	20.75	18.96	19.96	19.39	20.35	20.75
	12H	18.92	19.87	19.35	20.26	20.69	18.92	19.87	19.35	20.26	20.69
4H	2H	19.09	20.24	19.49	20.59	20.97	19.09	20.24	19.49	20.59	20.97
	3H	18.98	19.90	19.39	20.30	20.71	18.98	19.90	19.39	20.30	20.71
	4H	18.89	19.72	19.33	20.13	20.58	18.89	19.72	19.33	20.13	20.58
	6H	18.82	19.53	19.28	19.97	20.44	18.82	19.53	19.28	19.97	20.44
	8H	18.76	19.43	19.23	19.87	20.34	18.76	19.43	19.23	19.87	20.34
	12H	18.72	19.31	19.20	19.79	20.26	18.72	19.31	19.20	19.79	20.26
8H	4H	18.76	19.42	19.23	19.87	20.34	18.76	19.42	19.23	19.87	20.34
	6H	18.66	19.21	19.16	19.70	20.18	18.66	19.21	19.16	19.70	20.18
	8H	18.59	19.09	19.11	19.60	20.09	18.59	19.09	19.11	19.60	20.09
	12H	18.54	18.99	19.06	19.48	20.05	18.54	18.99	19.06	19.48	20.05
12H	4H	18.72	19.30	19.20	19.79	20.26	18.72	19.30	19.20	19.79	20.26
	6H	18.59	19.09	19.11	19.60	20.09	18.59	19.09	19.11	19.60	20.09
	8H	18.54	18.99	19.06	19.48	20.05	18.54	18.99	19.06	19.48	20.05