

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866334

Luminaire Tested: PRLX-2002-M-935-75L-G-U-S-X-X-GREY-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P866334
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-40)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2002-M-935-75L-G-U-S-X-X-GREY-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, GLOBE LENS, TRUNCATED DOME WITH GRAY INTERIOR SHADE.
LIGHT LEVEL 8
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2867.5 lumens
Efficiency: N/A
Efficacy: 41.1 lumens/watt
Spacing Criteria (0/90/45): 1.36 / 1.36 / 1.53
Luminous Opening: Circular (Dia: 1.31' x H: 0')
CIE Type: Direct

Input Watts (W): 69.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P866334

CATALOG NUMBER: PRLX-2002-M-935-75L-G-U-S-X-X-GREY-X

Luminous Intensity Polar Plot





TEST NUMBER: P866334

CATALOG NUMBER: PRLX-2002-M-935-75L-G-U-S-X-X-GREY-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	105	101	97	93	97	93	90	93	90	87	89	87	85	83
2	98	89	82	76	95	87	81	75	84	78	73	80	76	72	77	73	70	68
3	89	78	69	62	86	76	68	62	73	66	61	70	64	59	68	63	58	56
4	81	68	59	52	78	67	58	52	64	57	51	62	55	50	60	54	49	47
5	74	61	51	44	72	59	51	44	57	49	44	55	48	43	53	47	43	40
6	68	54	45	38	66	53	44	38	51	44	38	50	43	37	48	42	37	35
7	63	49	40	33	61	48	39	33	47	39	33	45	38	33	44	37	33	31
8	58	44	36	30	57	44	35	30	42	35	29	41	34	29	40	34	29	27
9	55	41	32	26	53	40	32	26	39	31	26	38	31	26	37	31	26	24
10	51	37	29	24	50	37	29	24	36	29	24	35	28	24	34	28	23	22

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	6704
5°	6729
10°	6758
15°	6772
20°	6806
25°	6878
30°	6993
35°	7195
40°	7461
45°	7786
50°	7984
55°	8045
60°	7868
65°	7586
70°	7102
75°	6507
80°	5686
85°	4646

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 55°
 Luminance: 8045 cd/sqm

TEST NUMBER: P866334

CATALOG NUMBER: PRLX-2002-M-935-75L-G-U-S-X-X-GREY-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.2	2.8
10°-20°	232.5	8.1
20°-30°	362.0	12.6
30°-40°	464.7	16.2
40°-50°	531.6	18.5
50°-60°	514.9	18.0
60°-70°	397.5	13.9
70°-80°	224.0	7.8
80°-90°	60.1	2.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	674.7	23.5
0°-40°	1139.4	39.7
0°-60°	2185.9	76.2
0°-90°	2867.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2867.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	843	
5°	843	80
15°	822	232
25°	784	362
35°	741	465
45°	692	532
55°	580	515
65°	403	398
75°	212	224
85°	51	60
90°	0	

TEST NUMBER: P866334

CATALOG NUMBER: PRLX-2002-M-935-75L-G-U-S-X-X-GREY-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	842.6
2.5°	842.6
5°	842.6
7.5°	840.5
10°	836.5
12.5°	830.3
15°	822.2
17.5°	814.1
20°	803.9
22.5°	793.7
25°	783.5
27.5°	773.4
30°	761.2
32.5°	751.0
35°	740.8
37.5°	730.6
40°	718.4
42.5°	706.2
45°	692.0
47.5°	669.6
50°	645.1
52.5°	614.6
55°	580.0
57.5°	537.3
60°	494.5
62.5°	449.8
65°	403.0
67.5°	354.1
70°	305.3
72.5°	258.5
75°	211.7
77.5°	164.8
80°	124.1
82.5°	85.5
85°	50.9
87.5°	22.4
90°	0.0



TEST NUMBER: P866334
 CATALOG NUMBER: PRLX-2002-M-935-75L-G-U-S-X-X-GREY-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.73	21.43	20.10	21.75	22.06	19.73	21.43	20.10	21.75	22.06
	3H	21.55	23.09	21.92	23.42	23.78	21.55	23.09	21.92	23.42	23.78
	4H	22.21	23.67	22.61	24.02	24.39	22.21	23.67	22.61	24.02	24.39
	6H	22.68	24.03	23.09	24.39	24.78	22.68	24.03	23.09	24.39	24.78
	8H	22.82	24.12	23.24	24.50	24.90	22.82	24.12	23.24	24.50	24.90
	12H	22.92	24.16	23.34	24.54	24.97	22.92	24.16	23.34	24.54	24.97
4H	2H	20.39	21.85	20.79	22.19	22.57	20.39	21.85	20.79	22.19	22.57
	3H	22.42	23.64	22.83	24.04	24.44	22.42	23.64	22.83	24.04	24.44
	4H	23.21	24.32	23.64	24.73	25.16	23.21	24.32	23.64	24.73	25.16
	6H	23.79	24.77	24.24	25.21	25.66	23.79	24.77	24.24	25.21	25.66
	8H	23.98	24.90	24.44	25.34	25.80	23.98	24.90	24.44	25.34	25.80
	12H	24.12	24.94	24.60	25.42	25.88	24.12	24.94	24.60	25.42	25.88
8H	4H	23.52	24.43	23.97	24.87	25.33	23.52	24.43	23.97	24.87	25.33
	6H	24.22	24.98	24.71	25.47	25.94	24.22	24.98	24.71	25.47	25.94
	8H	24.48	25.16	24.99	25.67	26.15	24.48	25.16	24.99	25.67	26.15
	12H	24.68	25.29	25.19	25.78	26.33	24.68	25.29	25.19	25.78	26.33
12H	4H	23.55	24.37	24.03	24.85	25.32	23.55	24.37	24.03	24.85	25.32
	6H	24.27	24.96	24.78	25.46	25.95	24.27	24.96	24.78	25.46	25.95
	8H	24.59	25.19	25.09	25.68	26.24	24.59	25.19	25.09	25.68	26.24