

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866338

Luminaire Tested: PRLX-2002-M-935-75L-L-U-S-X-X-GREY-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P866338  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-52)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2002-M-935-75L-L-U-S-X-X-GREY-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, FLAT LENS, TRUNCATED DOME WITH GRAY INTERIOR SHADE.  
LIGHT LEVEL 8  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6244.2 lumens  
Efficiency: N/A  
Efficacy: 89.6 lumens/watt  
Spacing Criteria (0/90/45): 1.15 / 1.15 / 1.27  
Luminous Opening: Circular (Dia: 1.31' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 69.7  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.5 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P866338

CATALOG NUMBER: PRLX-2002-M-935-75L-L-U-S-X-X-GREY-X

### Luminous Intensity Polar Plot



TEST NUMBER: P866338

CATALOG NUMBER: PRLX-2002-M-935-75L-L-U-S-X-X-GREY-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89
2	103	97	91	87	101	95	90	86	92	88	84	89	85	82	86	83	80	78
3	96	87	80	75	93	86	79	74	83	77	73	80	76	72	78	74	71	69
4	89	78	71	65	86	77	70	65	75	69	64	73	67	63	71	66	62	60
5	82	71	63	57	80	70	63	57	68	61	56	66	60	56	64	59	55	53
6	76	64	56	51	74	64	56	51	62	55	50	60	54	50	59	53	49	48
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	48	44	43
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	40	36	35
10	58	46	39	34	57	45	38	34	45	38	34	44	38	33	43	37	33	32

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	24805
5°	24705
10°	24366
15°	23870
20°	23313
25°	22689
30°	22024
35°	21288
40°	20481
45°	19647
50°	18615
55°	16400
60°	8743
65°	2299
70°	947
75°	1064
80°	1214
85°	1488

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 19647 cd/sqm

TEST NUMBER: P866338

CATALOG NUMBER: PRLX-2002-M-935-75L-L-U-S-X-X-GREY-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	292.8	4.7
10°-20°	816.2	13.1
20°-30°	1190.0	19.1
30°-40°	1369.7	21.9
40°-50°	1343.8	21.5
50°-60°	995.4	15.9
60°-70°	183.7	2.9
70°-80°	36.3	0.6
80°-90°	16.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2299.0	36.8
0°-40°	3668.7	58.8
0°-60°	6007.9	96.2
0°-90°	6244.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6244.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3118	
5°	3094	293
15°	2898	816
25°	2585	1190
35°	2192	1370
45°	1746	1344
55°	1182	995
65°	122	184
75°	35	36
85°	16	16
90°	0	

TEST NUMBER: P866338

CATALOG NUMBER: PRLX-2002-M-935-75L-L-U-S-X-X-GREY-X

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3117.9
2.5°	3113.8
5°	3093.5
7.5°	3060.9
10°	3016.1
12.5°	2961.2
15°	2898.1
17.5°	2826.9
20°	2753.6
22.5°	2672.2
25°	2584.7
27.5°	2493.1
30°	2397.4
32.5°	2295.7
35°	2191.9
37.5°	2082.0
40°	1972.1
42.5°	1858.1
45°	1746.2
47.5°	1624.1
50°	1504.0
52.5°	1371.7
55°	1182.4
57.5°	893.4
60°	549.5
62.5°	282.9
65°	122.1
67.5°	52.9
70°	40.7
72.5°	38.7
75°	34.6
77.5°	30.5
80°	26.5
82.5°	22.4
85°	16.3
87.5°	8.1
90°	0.0



TEST NUMBER: P866338  
 CATALOG NUMBER: PRLX-2002-M-935-75L-L-U-S-X-X-GREY-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	20.75	22.18	21.12	22.49	22.81	20.75	22.18	21.12	22.49	22.81
	3H	20.65	21.91	21.03	22.24	22.60	20.65	21.91	21.03	22.24	22.60
	4H	20.60	21.77	21.00	22.12	22.50	20.60	21.77	21.00	22.12	22.50
	6H	20.54	21.61	20.96	21.98	22.38	20.54	21.61	20.96	21.98	22.38
	8H	20.51	21.53	20.94	21.92	22.32	20.51	21.53	20.94	21.92	22.32
	12H	20.48	21.46	20.92	21.84	22.27	20.48	21.46	20.92	21.84	22.27
4H	2H	20.60	21.77	21.01	22.12	22.50	20.60	21.77	21.01	22.12	22.50
	3H	20.52	21.46	20.93	21.86	22.26	20.52	21.46	20.93	21.86	22.26
	4H	20.46	21.29	20.89	21.71	22.15	20.46	21.29	20.89	21.71	22.15
	6H	20.41	21.13	20.87	21.58	22.04	20.41	21.13	20.87	21.58	22.04
	8H	20.37	21.05	20.84	21.50	21.97	20.37	21.05	20.84	21.50	21.97
	12H	20.35	20.95	20.83	21.43	21.90	20.35	20.95	20.83	21.43	21.90
8H	4H	20.34	21.02	20.81	21.46	21.93	20.34	21.02	20.81	21.46	21.93
	6H	20.28	20.84	20.78	21.33	21.81	20.28	20.84	20.78	21.33	21.81
	8H	20.24	20.75	20.76	21.26	21.76	20.24	20.75	20.76	21.26	21.76
	12H	20.23	20.68	20.74	21.18	21.75	20.23	20.68	20.74	21.18	21.75
12H	4H	20.30	20.90	20.78	21.38	21.85	20.30	20.90	20.78	21.38	21.85
	6H	20.22	20.73	20.74	21.24	21.73	20.22	20.73	20.74	21.24	21.73
	8H	20.21	20.66	20.72	21.16	21.73	20.21	20.66	20.72	21.16	21.73