

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865871

Luminaire Tested: PRLX-2004-S-940-15L-G-U-S-X-X-WHHR-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P865871
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2004-S-940-15L-G-U-S-X-X-WHHR-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, GLOBE LENS,
BELL WITH WHITE INTERIOR SHADE.
LIGHT LEVEL 3
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 839.9 lumens
Efficiency: N/A
Efficacy: 53.8 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.21
Luminous Opening: Circular (Dia: 0.92' x H: 0')
CIE Type: Direct

Input Watts (W): 15.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P865871

CATALOG NUMBER: PRLX-2004-S-940-15L-G-U-S-X-X-WHHR-X

Luminous Intensity Polar Plot





TEST NUMBER: P865871

CATALOG NUMBER: PRLX-2004-S-940-15L-G-U-S-X-X-WHHR-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	102	98	107	103	100	97	99	96	94	95	93	91	92	90	88	86
2	101	94	88	83	99	92	86	82	88	84	80	85	81	78	82	79	76	74
3	93	84	76	70	91	82	75	70	79	73	69	77	72	67	74	70	66	64
4	86	75	67	61	84	74	66	61	71	65	60	69	64	59	67	62	58	56
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	50	46	44
7	69	56	48	43	67	56	48	42	54	47	42	53	47	42	52	46	42	40
8	65	52	44	38	63	51	44	38	50	43	38	49	43	38	48	42	38	36
9	61	48	40	35	59	47	40	35	46	39	35	45	39	35	44	39	34	33
10	57	44	37	32	56	44	37	32	43	36	32	42	36	32	41	36	32	30

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	6433
5°	6434
10°	6416
15°	6400
20°	6358
25°	6189
30°	5895
35°	5422
40°	4871
45°	4339
50°	3776
55°	3273
60°	2838
65°	2601
70°	2475
75°	2300
80°	2245
85°	2096

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4339 cd/sqm

TEST NUMBER: P865871

CATALOG NUMBER: PRLX-2004-S-940-15L-G-U-S-X-X-WHHR-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.4	4.4
10°-20°	106.8	12.7
20°-30°	157.8	18.8
30°-40°	169.6	20.2
40°-50°	145.2	17.3
50°-60°	103.7	12.3
60°-70°	67.5	8.0
70°-80°	39.6	4.7
80°-90°	12.4	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	301.9	35.9
0°-40°	471.5	56.1
0°-60°	720.4	85.8
0°-90°	839.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	839.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	394	
5°	393	37
15°	379	107
25°	344	158
35°	272	170
45°	188	145
55°	115	104
65°	67	68
75°	36	40
85°	11	12
90°	0	

TEST NUMBER: P865871

CATALOG NUMBER: PRLX-2004-S-940-15L-G-U-S-X-X-WHHR-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	394.4
2.5°	394.4
5°	393.0
7.5°	391.6
10°	387.4
12.5°	383.2
15°	379.0
17.5°	372.0
20°	366.3
22.5°	356.5
25°	343.9
27.5°	329.9
30°	313.0
32.5°	293.4
35°	272.3
37.5°	249.8
40°	228.8
42.5°	209.1
45°	188.1
47.5°	168.4
50°	148.8
52.5°	131.9
55°	115.1
57.5°	99.7
60°	87.0
62.5°	77.2
65°	67.4
67.5°	59.0
70°	51.9
72.5°	44.9
75°	36.5
77.5°	30.9
80°	23.9
82.5°	16.8
85°	11.2
87.5°	5.6
90°	0.0

TEST NUMBER: P865871
 CATALOG NUMBER: PRLX-2004-S-940-15L-G-U-S-X-X-WHHR-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.03	16.53	15.40	16.84	17.15	15.03	16.53	15.40	16.84	17.15
	3H	16.56	17.90	16.94	18.23	18.59	16.56	17.90	16.94	18.23	18.59
	4H	17.18	18.44	17.58	18.79	19.17	17.18	18.44	17.58	18.79	19.17
	6H	17.70	18.86	18.11	19.23	19.62	17.70	18.86	18.11	19.23	19.62
	8H	17.87	18.98	18.30	19.37	19.77	17.87	18.98	18.30	19.37	19.77
	12H	18.00	19.05	18.43	19.44	19.87	18.00	19.05	18.43	19.44	19.87
4H	2H	15.53	16.79	15.93	17.14	17.51	15.53	16.79	15.93	17.14	17.51
	3H	17.32	18.36	17.73	18.76	19.16	17.32	18.36	17.73	18.76	19.16
	4H	18.07	19.01	18.50	19.42	19.86	18.07	19.01	18.50	19.42	19.86
	6H	18.73	19.55	19.19	19.99	20.45	18.73	19.55	19.19	19.99	20.45
	8H	18.96	19.72	19.42	20.17	20.63	18.96	19.72	19.42	20.17	20.63
	12H	19.13	19.82	19.61	20.29	20.77	19.13	19.82	19.61	20.29	20.77
8H	4H	18.36	19.13	18.82	19.57	20.04	18.36	19.13	18.82	19.57	20.04
	6H	19.16	19.79	19.66	20.28	20.76	19.16	19.79	19.66	20.28	20.76
	8H	19.46	20.03	19.98	20.54	21.03	19.46	20.03	19.98	20.54	21.03
	12H	19.73	20.23	20.24	20.72	21.29	19.73	20.23	20.24	20.72	21.29
12H	4H	18.39	19.08	18.87	19.55	20.03	18.39	19.08	18.87	19.55	20.03
	6H	19.22	19.79	19.73	20.30	20.79	19.22	19.79	19.73	20.30	20.79
	8H	19.58	20.09	20.09	20.58	21.14	19.58	20.09	20.09	20.58	21.14