

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866341

Luminaire Tested: PRLX-2002-M-940-07L-G-U-S-X-X-BRSS-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P866341  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-39)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2002-M-940-07L-G-U-S-X-X-BRSS-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, GLOBE LENS, TRUNCATED DOME WITH BRASS INTERIOR SHADE.  
LIGHT LEVEL 1  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 285.5 lumens  
Efficiency: N/A  
Efficacy: 34.8 lumens/watt  
Spacing Criteria (0/90/45): 1.36 / 1.36 / 1.53  
Luminous Opening: Circular (Dia: 1.31' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 8.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.5 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P866341

CATALOG NUMBER: PRLX-2002-M-940-07L-G-U-S-X-X-BRSS-X

### Luminous Intensity Polar Plot





TEST NUMBER: P866341

CATALOG NUMBER: PRLX-2002-M-940-07L-G-U-S-X-X-BRSS-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	108	103	99	95	105	101	97	93	97	93	90		93	90	87		89	87	85	83
2	98	89	82	76	95	87	81	75	84	78	73		80	76	72		77	73	70	68
3	89	78	69	62	86	76	68	62	73	66	61		70	64	60		68	63	58	56
4	81	68	59	52	78	67	58	52	64	57	51		62	56	50		60	54	50	47
5	74	61	51	44	72	59	51	44	57	50	44		55	48	43		53	47	43	40
6	68	54	45	38	66	53	45	38	51	44	38		50	43	37		48	42	37	35
7	63	49	40	34	61	48	40	33	47	39	33		45	38	33		44	37	33	31
8	59	45	36	30	57	44	35	30	42	35	29		41	34	29		40	34	29	27
9	55	41	32	27	53	40	32	26	39	31	26		38	31	26		37	31	26	24
10	51	37	29	24	50	37	29	24	36	29	24		35	28	24		34	28	23	22

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	669
5°	670
10°	675
15°	676
20°	680
25°	686
30°	698
35°	717
40°	744
45°	775
50°	798
55°	799
60°	784
65°	751
70°	702
75°	642
80°	559
85°	447

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 52.5°  
 Luminance: 802 cd/sqm

TEST NUMBER: P866341

CATALOG NUMBER: PRLX-2002-M-940-07L-G-U-S-X-X-BRSS-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	8.0	2.8
10°-20°	23.2	8.1
20°-30°	36.1	12.6
30°-40°	46.3	16.2
40°-50°	53.1	18.6
50°-60°	51.3	18.0
60°-70°	39.5	13.8
70°-80°	22.1	7.8
80°-90°	5.8	2.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	67.3	23.6
0°-40°	113.6	39.8
0°-60°	218.0	76.4
0°-90°	285.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	285.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	84	
5°	84	8
15°	82	23
25°	78	36
35°	74	46
45°	69	53
55°	58	51
65°	40	40
75°	21	22
85°	5	6
90°	0	

TEST NUMBER: P866341

CATALOG NUMBER: PRLX-2002-M-940-07L-G-U-S-X-X-BRSS-X

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	84.1
2.5°	84.1
5°	83.9
7.5°	83.7
10°	83.5
12.5°	82.9
15°	82.1
17.5°	81.1
20°	80.3
22.5°	79.1
25°	78.1
27.5°	77.1
30°	76.0
32.5°	74.8
35°	73.8
37.5°	72.8
40°	71.6
42.5°	70.6
45°	68.9
47.5°	66.9
50°	64.5
52.5°	61.4
55°	57.6
57.5°	53.5
60°	49.3
62.5°	44.8
65°	39.9
67.5°	35.3
70°	30.2
72.5°	25.5
75°	20.9
77.5°	16.4
80°	12.2
82.5°	8.3
85°	4.9
87.5°	2.2
90°	0.0



TEST NUMBER: P866341  
 CATALOG NUMBER: PRLX-2002-M-940-07L-G-U-S-X-X-BRSS-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.72	13.42	12.08	13.73	14.05	11.72	13.42	12.08	13.73	14.05
	3H	13.53	15.07	13.91	15.40	15.76	13.53	15.07	13.91	15.40	15.76
	4H	14.18	15.64	14.58	15.99	16.36	14.18	15.64	14.58	15.99	16.36
	6H	14.64	16.00	15.05	16.36	16.75	14.64	16.00	15.05	16.36	16.75
	8H	14.78	16.08	15.21	16.47	16.86	14.78	16.08	15.21	16.47	16.86
	12H	14.87	16.11	15.30	16.49	16.92	14.87	16.11	15.30	16.49	16.92
4H	2H	12.37	13.83	12.77	14.17	14.55	12.37	13.83	12.77	14.17	14.55
	3H	14.39	15.62	14.80	16.01	16.41	14.39	15.62	14.80	16.01	16.41
	4H	15.17	16.28	15.60	16.69	17.12	15.17	16.28	15.60	16.69	17.12
	6H	15.75	16.73	16.20	17.16	17.62	15.75	16.73	16.20	17.16	17.62
	8H	15.94	16.85	16.39	17.29	17.75	15.94	16.85	16.39	17.29	17.75
	12H	16.07	16.89	16.54	17.36	17.83	16.07	16.89	16.54	17.36	17.83
8H	4H	15.48	16.39	15.94	16.83	17.29	15.48	16.39	15.94	16.83	17.29
	6H	16.18	16.93	16.67	17.42	17.89	16.18	16.93	16.67	17.42	17.89
	8H	16.43	17.11	16.93	17.61	18.09	16.43	17.11	16.93	17.61	18.09
	12H	16.62	17.22	17.12	17.71	18.27	16.62	17.22	17.12	17.71	18.27
12H	4H	15.51	16.33	15.99	16.81	17.27	15.51	16.33	15.99	16.81	17.27
	6H	16.23	16.91	16.73	17.41	17.90	16.23	16.91	16.73	17.41	17.90
	8H	16.53	17.13	17.04	17.62	18.18	16.53	17.13	17.04	17.62	18.18