

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866353

Luminaire Tested: PRLX-2002-M-940-15L-L-U-S-X-X-BRSS-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P866353
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-51)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2002-M-940-15L-L-U-S-X-X-BRSS-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, FLAT LENS, TRUNCATED DOME WITH BRASS INTERIOR SHADE.
LIGHT LEVEL 2
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1321.7 lumens
Efficiency: N/A
Efficacy: 94.4 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Circular (Dia: 1.31' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P866353

CATALOG NUMBER: PRLX-2002-M-940-15L-L-U-S-X-X-BRSS-X

Luminous Intensity Polar Plot





TEST NUMBER: P866353

CATALOG NUMBER: PRLX-2002-M-940-15L-L-U-S-X-X-BRSS-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89
2	103	97	91	87	101	95	90	86	92	88	84	89	85	82	86	83	80	78
3	96	87	80	75	93	86	79	74	83	77	73	80	76	72	78	74	71	69
4	89	78	71	65	86	77	70	65	75	69	64	73	67	63	71	66	62	60
5	82	71	63	57	80	70	62	57	68	61	56	66	60	56	64	59	55	53
6	76	64	56	51	74	63	56	51	62	55	50	60	54	50	59	53	49	48
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	48	44	43
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	40	36	35
10	58	46	39	34	57	45	38	34	44	38	34	44	38	33	43	37	33	32

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	5237
5°	5216
10°	5144
15°	5046
20°	4927
25°	4799
30°	4662
35°	4506
40°	4340
45°	4154
50°	3941
55°	3394
60°	1871
65°	527
70°	209
75°	224
80°	257
85°	310

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4154 cd/sqm

TEST NUMBER: P866353

CATALOG NUMBER: PRLX-2002-M-940-15L-L-U-S-X-X-BRSS-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.8	4.7
10°-20°	172.5	13.1
20°-30°	251.7	19.0
30°-40°	290.0	21.9
40°-50°	284.7	21.5
50°-60°	208.8	15.8
60°-70°	40.9	3.1
70°-80°	7.7	0.6
80°-90°	3.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	486.0	36.8
0°-40°	776.0	58.7
0°-60°	1269.6	96.1
0°-90°	1321.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1321.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	658	
5°	653	62
15°	613	172
25°	547	252
35°	464	290
45°	369	285
55°	245	209
65°	28	41
75°	7	8
85°	3	3
90°	0	

TEST NUMBER: P866353

CATALOG NUMBER: PRLX-2002-M-940-15L-L-U-S-X-X-BRSS-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	658.3
2.5°	657.4
5°	653.1
7.5°	645.8
10°	636.7
12.5°	626.0
15°	612.6
17.5°	597.5
20°	582.0
22.5°	564.8
25°	546.7
27.5°	527.7
30°	507.5
32.5°	485.9
35°	464.0
37.5°	441.1
40°	417.9
42.5°	394.2
45°	369.2
47.5°	344.6
50°	318.4
52.5°	288.6
55°	244.7
57.5°	187.4
60°	117.6
62.5°	63.3
65°	28.0
67.5°	12.9
70°	9.0
72.5°	8.2
75°	7.3
77.5°	6.5
80°	5.6
82.5°	4.7
85°	3.4
87.5°	1.7
90°	0.0



TEST NUMBER: P866353
 CATALOG NUMBER: PRLX-2002-M-940-15L-L-U-S-X-X-BRSS-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.30	16.73	15.66	17.04	17.36	15.30	16.73	15.66	17.04	17.36
	3H	15.20	16.46	15.58	16.79	17.15	15.20	16.46	15.58	16.79	17.15
	4H	15.15	16.32	15.55	16.67	17.05	15.15	16.32	15.55	16.67	17.05
	6H	15.10	16.17	15.51	16.54	16.93	15.10	16.17	15.51	16.54	16.93
	8H	15.07	16.08	15.49	16.47	16.88	15.07	16.08	15.49	16.47	16.88
	12H	15.04	16.01	15.47	16.39	16.82	15.04	16.01	15.47	16.39	16.82
4H	2H	15.16	16.33	15.56	16.68	17.06	15.16	16.33	15.56	16.68	17.06
	3H	15.08	16.02	15.49	16.42	16.83	15.08	16.02	15.49	16.42	16.83
	4H	15.02	15.86	15.45	16.27	16.72	15.02	15.86	15.45	16.27	16.72
	6H	14.97	15.70	15.43	16.14	16.61	14.97	15.70	15.43	16.14	16.61
	8H	14.94	15.61	15.40	16.06	16.53	14.94	15.61	15.40	16.06	16.53
	12H	14.91	15.51	15.40	15.99	16.47	14.91	15.51	15.40	15.99	16.47
8H	4H	14.90	15.58	15.37	16.02	16.49	14.90	15.58	15.37	16.02	16.49
	6H	14.84	15.40	15.34	15.90	16.38	14.84	15.40	15.34	15.90	16.38
	8H	14.81	15.31	15.33	15.83	16.32	14.81	15.31	15.33	15.83	16.32
	12H	14.79	15.25	15.30	15.74	16.31	14.79	15.25	15.30	15.74	16.31
12H	4H	14.86	15.46	15.35	15.94	16.42	14.86	15.46	15.35	15.94	16.42
	6H	14.79	15.29	15.31	15.81	16.30	14.79	15.29	15.31	15.81	16.30
	8H	14.77	15.23	15.28	15.72	16.29	14.77	15.23	15.28	15.72	16.29