

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865874

Luminaire Tested: PRLX-2004-S-940-15L-L-U-S-X-X-GREY-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P865874  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-25)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2004-S-940-15L-L-U-S-X-X-GREY-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, FLAT LENS,  
BELL WITH GRAY INTERIOR SHADE.  
LIGHT LEVEL 3  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 806.0 lumens  
Efficiency: N/A  
Efficacy: 51.7 lumens/watt  
Spacing Criteria (0/90/45): 1.07 / 1.07 / 1.02  
Luminous Opening: Circular (Dia: 0.92' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 15.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.5 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P865874

CATALOG NUMBER: PRLX-2004-S-940-15L-L-U-S-X-X-GREY-X

### Luminous Intensity Polar Plot





TEST NUMBER: P865874

CATALOG NUMBER: PRLX-2004-S-940-15L-L-U-S-X-X-GREY-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	104	110	107	105	103	103	101	99	100	98	96	96	95	94	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84
3	100	93	88	83	98	92	87	82	89	85	81	86	83	80	84	81	79	77
4	95	86	80	75	93	85	79	75	83	78	74	81	76	73	79	75	72	71
5	89	80	74	69	87	79	73	68	77	72	68	75	71	67	74	70	67	65
6	84	74	68	63	83	74	67	63	72	67	63	71	66	62	69	65	62	60
7	80	70	63	58	78	69	63	58	67	62	58	66	61	58	65	61	57	56
8	75	65	59	54	74	64	58	54	63	58	54	62	57	53	61	57	53	52
9	71	61	55	50	70	60	54	50	59	54	50	59	53	50	58	53	50	48
10	68	57	51	47	67	57	51	47	56	50	47	55	50	47	54	50	46	45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	11652
5°	11398
10°	10926
15°	10499
20°	10135
25°	9801
30°	9411
35°	7323
40°	3019
45°	1197
50°	784
55°	759
60°	688
65°	648
70°	601
75°	618
80°	526
85°	524

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1197 cd/sqm

TEST NUMBER: P865874

CATALOG NUMBER: PRLX-2004-S-940-15L-L-U-S-X-X-GREY-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	65.3	8.1
10°-20°	175.3	21.7
20°-30°	250.7	31.1
30°-40°	213.1	26.4
40°-50°	48.5	6.0
50°-60°	23.4	2.9
60°-70°	17.0	2.1
70°-80°	9.8	1.2
80°-90°	3.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	491.2	60.9
0°-40°	704.3	87.4
0°-60°	776.2	96.3
0°-90°	806.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	806.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	714	
5°	696	65
15°	622	175
25°	545	251
35°	368	213
45°	52	48
55°	27	23
65°	17	17
75°	10	10
85°	3	3
90°	0	

TEST NUMBER: P865874

CATALOG NUMBER: PRLX-2004-S-940-15L-L-U-S-X-X-GREY-X

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	714.4
2.5°	711.6
5°	696.2
7.5°	678.0
10°	659.7
12.5°	641.5
15°	621.8
17.5°	603.6
20°	583.9
22.5°	564.3
25°	544.6
27.5°	525.0
30°	499.7
32.5°	450.6
35°	367.8
37.5°	247.0
40°	141.8
42.5°	82.8
45°	51.9
47.5°	35.1
50°	30.9
52.5°	28.1
55°	26.7
57.5°	23.9
60°	21.1
62.5°	19.7
65°	16.8
67.5°	15.4
70°	12.6
72.5°	11.2
75°	9.8
77.5°	7.0
80°	5.6
82.5°	4.2
85°	2.8
87.5°	1.4
90°	0.0

TEST NUMBER: P865874

CATALOG NUMBER: PRLX-2004-S-940-15L-L-U-S-X-X-GREY-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.80	6.86	6.16	7.17	7.49	5.80	6.86	6.16	7.17	7.49
	3H	7.43	8.37	7.81	8.70	9.07	7.43	8.37	7.81	8.70	9.07
	4H	8.10	8.98	8.51	9.33	9.72	8.10	8.98	8.51	9.33	9.72
	6H	8.51	9.31	8.92	9.68	10.08	8.51	9.31	8.92	9.68	10.08
	8H	8.66	9.41	9.09	9.80	10.21	8.66	9.41	9.09	9.80	10.21
	12H	8.77	9.49	9.20	9.87	10.30	8.77	9.49	9.20	9.87	10.30
4H	2H	6.27	7.14	6.67	7.49	7.88	6.27	7.14	6.67	7.49	7.88
	3H	8.10	8.82	8.52	9.23	9.63	8.10	8.82	8.52	9.23	9.63
	4H	8.92	9.56	9.36	9.98	10.43	8.92	9.56	9.36	9.98	10.43
	6H	9.44	9.99	9.91	10.44	10.92	9.44	9.99	9.91	10.44	10.92
	8H	9.64	10.15	10.12	10.60	11.08	9.64	10.15	10.12	10.60	11.08
	12H	9.80	10.24	10.29	10.73	11.21	9.80	10.24	10.29	10.73	11.21
8H	4H	9.14	9.65	9.61	10.10	10.58	9.14	9.65	9.61	10.10	10.58
	6H	9.80	10.21	10.31	10.71	11.19	9.80	10.21	10.31	10.71	11.19
	8H	10.08	10.45	10.61	10.97	11.46	10.08	10.45	10.61	10.97	11.46
	12H	10.34	10.66	10.86	11.15	11.73	10.34	10.66	10.86	11.15	11.73
12H	4H	9.14	9.58	9.63	10.07	10.55	9.14	9.58	9.63	10.07	10.55
	6H	9.83	10.20	10.36	10.72	11.21	9.83	10.20	10.36	10.72	11.21
	8H	10.18	10.50	10.70	10.99	11.57	10.18	10.50	10.70	10.99	11.57