

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865624

Luminaire Tested: PRLX-2002-S-930-10L-L-U-S-X-X-BLAK-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P865624
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-22)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2002-S-930-10L-L-U-S-X-X-BLAK-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, FLAT LENS, TRUNCATED DOME WITH BLACK INTERIOR SHADE.
LIGHT LEVEL 2
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 730.3 lumens
Efficiency: N/A
Efficacy: 69.6 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.28
Luminous Opening: Circular (Dia: 0.85' x H: 0')
CIE Type: Direct

Input Watts (W): 10.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.333 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P865624

CATALOG NUMBER: PRLX-2002-S-930-10L-L-U-S-X-X-BLAK-X

Luminous Intensity Polar Plot





TEST NUMBER: P865624

CATALOG NUMBER: PRLX-2002-S-930-10L-L-U-S-X-X-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	94	95	93	92	90
2	104	98	92	88	101	96	91	87	92	88	85	89	86	83	86	84	81	79
3	96	88	81	76	94	86	80	75	84	78	74	81	77	73	79	75	72	70
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62
5	83	72	64	58	81	71	64	58	69	62	58	67	61	57	65	60	56	55
6	77	65	57	52	75	64	57	52	63	56	51	61	55	51	60	54	50	49
7	72	60	52	46	70	59	51	46	57	51	46	56	50	46	55	49	45	44
8	67	55	47	42	65	54	47	42	53	46	41	52	46	41	51	45	41	39
9	63	50	43	38	61	50	43	38	49	42	38	48	42	37	47	41	37	36
10	59	47	39	35	58	46	39	34	45	39	34	44	38	34	43	38	34	32

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	6963
5°	6926
10°	6840
15°	6738
20°	6599
25°	6448
30°	6260
35°	6063
40°	5848
45°	5624
50°	5327
55°	4244
60°	1852
65°	382
70°	49
75°	65
80°	97
85°	194

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5624 cd/sqm

TEST NUMBER: P865624

CATALOG NUMBER: PRLX-2002-S-930-10L-L-U-S-X-X-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	34.8	4.8
10°-20°	97.6	13.4
20°-30°	143.2	19.6
30°-40°	165.4	22.6
40°-50°	162.9	22.3
50°-60°	110.3	15.1
60°-70°	14.3	2.0
70°-80°	1.0	0.1
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	275.6	37.7
0°-40°	441.0	60.4
0°-60°	714.2	97.8
0°-90°	730.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	730.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	371	
5°	367	35
15°	346	98
25°	311	143
35°	264	165
45°	212	163
55°	130	110
65°	9	14
75°	1	1
85°	1	1
90°	0	

TEST NUMBER: P865624

CATALOG NUMBER: PRLX-2002-S-930-10L-L-U-S-X-X-BLAK-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	370.7
2.5°	370.7
5°	367.3
7.5°	363.8
10°	358.6
12.5°	353.4
15°	346.5
17.5°	338.8
20°	330.1
22.5°	321.5
25°	311.1
27.5°	300.7
30°	288.6
32.5°	277.4
35°	264.4
37.5°	251.5
40°	238.5
42.5°	225.5
45°	211.7
47.5°	197.0
50°	182.3
52.5°	161.6
55°	129.6
57.5°	89.9
60°	49.3
62.5°	23.3
65°	8.6
67.5°	1.7
70°	0.9
72.5°	0.9
75°	0.9
77.5°	0.9
80°	0.9
82.5°	0.9
85°	0.9
87.5°	0.9
90°	0.0



TEST NUMBER: P865624
 CATALOG NUMBER: PRLX-2002-S-930-10L-L-U-S-X-X-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.23	16.63	15.60	16.95	17.26	15.23	16.63	15.60	16.95	17.26
	3H	15.11	16.34	15.49	16.67	17.04	15.11	16.34	15.49	16.67	17.04
	4H	15.05	16.19	15.45	16.54	16.92	15.05	16.19	15.45	16.54	16.92
	6H	14.97	16.02	15.39	16.39	16.78	14.97	16.02	15.39	16.39	16.78
	8H	14.93	15.93	15.36	16.32	16.72	14.93	15.93	15.36	16.32	16.72
	12H	14.90	15.84	15.33	16.23	16.66	14.90	15.84	15.33	16.23	16.66
4H	2H	15.06	16.21	15.47	16.56	16.94	15.06	16.21	15.47	16.56	16.94
	3H	14.95	15.87	15.36	16.27	16.67	14.95	15.87	15.36	16.27	16.67
	4H	14.87	15.68	15.30	16.10	16.54	14.87	15.68	15.30	16.10	16.54
	6H	14.79	15.49	15.25	15.94	16.40	14.79	15.49	15.25	15.94	16.40
	8H	14.74	15.39	15.21	15.84	16.31	14.74	15.39	15.21	15.84	16.31
	12H	14.70	15.28	15.18	15.76	16.23	14.70	15.28	15.18	15.76	16.23
8H	4H	14.73	15.39	15.20	15.84	16.31	14.73	15.39	15.20	15.84	16.31
	6H	14.63	15.17	15.13	15.67	16.15	14.63	15.17	15.13	15.67	16.15
	8H	14.57	15.06	15.09	15.57	16.07	14.57	15.06	15.09	15.57	16.07
	12H	14.53	14.97	15.04	15.46	16.03	14.53	14.97	15.04	15.46	16.03
12H	4H	14.69	15.27	15.17	15.75	16.22	14.69	15.27	15.17	15.75	16.22
	6H	14.57	15.06	15.09	15.57	16.06	14.57	15.06	15.09	15.57	16.06
	8H	14.52	14.96	15.03	15.46	16.03	14.52	14.96	15.03	15.46	16.03