

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865634

Luminaire Tested: PRLX-2002-S-930-15L-L-U-S-X-X-GREY-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P865634
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-21)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2002-S-930-15L-L-U-S-X-X-GREY-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, FLAT LENS, TRUNCATED DOME WITH GRAY INTERIOR SHADE.
LIGHT LEVEL 3
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1168.7 lumens
Efficiency: N/A
Efficacy: 74.9 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Circular (Dia: 0.85' x H: 0')
CIE Type: Direct

Input Watts (W): 15.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.333 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P865634

CATALOG NUMBER: PRLX-2002-S-930-15L-L-U-S-X-X-GREY-X

Luminous Intensity Polar Plot





TEST NUMBER: P865634

CATALOG NUMBER: PRLX-2002-S-930-15L-L-U-S-X-X-GREY-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69
4	89	79	71	66	87	77	71	65	75	69	64	73	68	64	71	66	63	61
5	82	71	63	58	80	70	63	57	68	62	57	66	61	56	65	60	56	54
6	76	65	57	51	75	64	56	51	62	55	51	61	55	50	59	54	50	48
7	71	59	51	46	70	58	51	46	57	50	45	55	49	45	54	49	45	43
8	66	54	46	41	65	54	46	41	52	46	41	51	45	41	50	45	40	39
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	11055
5°	10999
10°	10855
15°	10637
20°	10391
25°	10129
30°	9841
35°	9512
40°	9186
45°	8849
50°	8372
55°	6792
60°	3216
65°	978
70°	500
75°	566
80°	563
85°	841

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8849 cd/sqm

TEST NUMBER: P865634

CATALOG NUMBER: PRLX-2002-S-930-15L-L-U-S-X-X-GREY-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.2	4.7
10°-20°	154.1	13.2
20°-30°	224.9	19.2
30°-40°	259.7	22.2
40°-50°	256.1	21.9
50°-60°	177.2	15.2
60°-70°	30.3	2.6
70°-80°	7.7	0.7
80°-90°	3.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	434.2	37.2
0°-40°	693.9	59.4
0°-60°	1127.2	96.4
0°-90°	1168.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1168.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	588	
5°	583	55
15°	547	154
25°	489	225
35°	415	260
45°	333	256
55°	207	177
65°	22	30
75°	8	8
85°	4	4
90°	0	



TEST NUMBER: P865634

CATALOG NUMBER: PRLX-2002-S-930-15L-L-U-S-X-X-GREY-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	588.5
2.5°	588.5
5°	583.3
7.5°	576.8
10°	569.1
12.5°	558.7
15°	547.0
17.5°	534.1
20°	519.8
22.5°	504.2
25°	488.7
27.5°	471.8
30°	453.7
32.5°	435.5
35°	414.8
37.5°	395.4
40°	374.6
42.5°	353.9
45°	333.1
47.5°	309.8
50°	286.5
52.5°	256.7
55°	207.4
57.5°	147.8
60°	85.6
62.5°	44.1
65°	22.0
67.5°	10.4
70°	9.1
72.5°	7.8
75°	7.8
77.5°	6.5
80°	5.2
82.5°	5.2
85°	3.9
87.5°	1.3
90°	0.0



TEST NUMBER: P865634
 CATALOG NUMBER: PRLX-2002-S-930-15L-L-U-S-X-X-GREY-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.05	18.47	17.41	18.78	19.09	17.05	18.47	17.41	18.78	19.09
	3H	16.96	18.21	17.34	18.54	18.90	16.96	18.21	17.34	18.54	18.90
	4H	16.91	18.07	17.31	18.42	18.81	16.91	18.07	17.31	18.42	18.81
	6H	16.87	17.93	17.28	18.30	18.69	16.87	17.93	17.28	18.30	18.69
	8H	16.84	17.85	17.27	18.24	18.65	16.84	17.85	17.27	18.24	18.65
	12H	16.83	17.79	17.26	18.17	18.60	16.83	17.79	17.26	18.17	18.60
4H	2H	16.90	18.07	17.31	18.42	18.80	16.90	18.07	17.31	18.42	18.80
	3H	16.83	17.77	17.24	18.17	18.57	16.83	17.77	17.24	18.17	18.57
	4H	16.79	17.62	17.22	18.04	18.48	16.79	17.62	17.22	18.04	18.48
	6H	16.76	17.47	17.22	17.92	18.39	16.76	17.47	17.22	17.92	18.39
	8H	16.73	17.41	17.20	17.85	18.32	16.73	17.41	17.20	17.85	18.32
	12H	16.73	17.32	17.21	17.81	18.28	16.73	17.32	17.21	17.81	18.28
8H	4H	16.68	17.35	17.15	17.80	18.27	16.68	17.35	17.15	17.80	18.27
	6H	16.64	17.19	17.14	17.69	18.17	16.64	17.19	17.14	17.69	18.17
	8H	16.63	17.13	17.15	17.65	18.14	16.63	17.13	17.15	17.65	18.14
	12H	16.64	17.10	17.16	17.59	18.16	16.64	17.10	17.16	17.59	18.16
12H	4H	16.64	17.23	17.12	17.72	18.19	16.64	17.23	17.12	17.72	18.19
	6H	16.59	17.09	17.11	17.60	18.10	16.59	17.09	17.11	17.60	18.10
	8H	16.60	17.05	17.11	17.55	18.12	16.60	17.05	17.11	17.55	18.12