

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865656

Luminaire Tested: PRLX-2002-S-935-05L-L-U-S-X-X-BLAK-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P865656  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-22)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2002-S-935-05L-L-U-S-X-X-BLAK-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, FLAT LENS, TRUNCATED DOME WITH BLACK INTERIOR SHADE.  
LIGHT LEVEL 1  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 382.4 lumens  
Efficiency: N/A  
Efficacy: 61.7 lumens/watt  
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.28  
Luminous Opening: Circular (Dia: 0.85' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 6.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.333 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P865656

CATALOG NUMBER: PRLX-2002-S-935-05L-L-U-S-X-X-BLAK-X

### Luminous Intensity Polar Plot





TEST NUMBER: P865656

CATALOG NUMBER: PRLX-2002-S-935-05L-L-U-S-X-X-BLAK-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	94	95	93	92	90
2	104	98	92	88	101	96	91	87	92	88	85	89	86	83	86	84	81	79
3	96	88	81	76	94	86	80	75	84	78	74	81	77	73	79	75	72	70
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62
5	83	72	64	58	81	71	64	58	69	62	58	67	61	57	65	60	56	55
6	77	65	57	52	75	64	57	52	63	56	51	61	55	51	60	54	50	49
7	72	60	52	46	70	59	51	46	57	51	46	56	50	46	55	49	45	44
8	67	55	47	42	65	54	47	42	53	46	41	52	46	41	50	45	41	39
9	63	50	43	38	61	50	43	38	49	42	38	48	42	37	47	41	37	36
10	59	47	39	35	58	46	39	34	45	39	34	44	38	34	43	38	34	32

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	3646
5°	3626
10°	3580
15°	3528
20°	3454
25°	3376
30°	3277
35°	3174
40°	3063
45°	2943
50°	2791
55°	2224
60°	969
65°	200
70°	27
75°	36
80°	54
85°	108

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2943 cd/sqm

TEST NUMBER: P865656

CATALOG NUMBER: PRLX-2002-S-935-05L-L-U-S-X-X-BLAK-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	18.2	4.8
10°-20°	51.1	13.4
20°-30°	75.0	19.6
30°-40°	86.6	22.6
40°-50°	85.3	22.3
50°-60°	57.7	15.1
60°-70°	7.5	2.0
70°-80°	0.5	0.1
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	144.3	37.7
0°-40°	230.8	60.4
0°-60°	373.9	97.8
0°-90°	382.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	382.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	194	
5°	192	18
15°	181	51
25°	163	75
35°	138	87
45°	111	85
55°	68	58
65°	4	7
75°	0	1
85°	0	0
90°	0	

TEST NUMBER: P865656

CATALOG NUMBER: PRLX-2002-S-935-05L-L-U-S-X-X-BLAK-X

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	194.1
2.5°	194.1
5°	192.3
7.5°	190.5
10°	187.7
12.5°	185.0
15°	181.4
17.5°	177.3
20°	172.8
22.5°	168.3
25°	162.9
27.5°	157.4
30°	151.1
32.5°	145.2
35°	138.4
37.5°	131.6
40°	124.9
42.5°	118.1
45°	110.8
47.5°	103.1
50°	95.5
52.5°	84.6
55°	67.9
57.5°	47.0
60°	25.8
62.5°	12.2
65°	4.5
67.5°	0.9
70°	0.5
72.5°	0.5
75°	0.5
77.5°	0.5
80°	0.5
82.5°	0.5
85°	0.5
87.5°	0.5
90°	0.0



TEST NUMBER: P865656  
 CATALOG NUMBER: PRLX-2002-S-935-05L-L-U-S-X-X-BLAK-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.97	14.38	13.34	14.69	15.00	12.97	14.38	13.34	14.69	15.00
	3H	12.85	14.08	13.23	14.41	14.78	12.85	14.08	13.23	14.41	14.78
	4H	12.79	13.93	13.19	14.28	14.66	12.79	13.93	13.19	14.28	14.66
	6H	12.72	13.76	13.13	14.13	14.53	12.72	13.76	13.13	14.13	14.53
	8H	12.68	13.67	13.11	14.06	14.46	12.68	13.67	13.11	14.06	14.46
	12H	12.64	13.59	13.07	13.97	14.40	12.64	13.59	13.07	13.97	14.40
4H	2H	12.81	13.95	13.21	14.30	14.68	12.81	13.95	13.21	14.30	14.68
	3H	12.69	13.61	13.10	14.01	14.41	12.69	13.61	13.10	14.01	14.41
	4H	12.61	13.42	13.04	13.84	14.28	12.61	13.42	13.04	13.84	14.28
	6H	12.53	13.23	13.00	13.68	14.15	12.53	13.23	13.00	13.68	14.15
	8H	12.48	13.14	12.95	13.58	14.05	12.48	13.14	12.95	13.58	14.05
	12H	12.44	13.02	12.92	13.50	13.98	12.44	13.02	12.92	13.50	13.98
8H	4H	12.47	13.13	12.94	13.58	14.05	12.47	13.13	12.94	13.58	14.05
	6H	12.37	12.92	12.88	13.41	13.89	12.37	12.92	12.88	13.41	13.89
	8H	12.31	12.80	12.83	13.32	13.81	12.31	12.80	12.83	13.32	13.81
	12H	12.27	12.71	12.78	13.21	13.78	12.27	12.71	12.78	13.21	13.78
12H	4H	12.43	13.01	12.91	13.49	13.97	12.43	13.01	12.91	13.49	13.97
	6H	12.31	12.80	12.83	13.31	13.81	12.31	12.80	12.83	13.31	13.81
	8H	12.26	12.71	12.78	13.20	13.77	12.26	12.71	12.78	13.20	13.77