

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865658

Luminaire Tested: PRLX-2002-S-935-05L-L-U-S-X-X-GREY-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P865658
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-21)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2002-S-935-05L-L-U-S-X-X-GREY-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, FLAT LENS, TRUNCATED DOME WITH GRAY INTERIOR SHADE.
LIGHT LEVEL 1
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 407.9 lumens
Efficiency: N/A
Efficacy: 65.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Circular (Dia: 0.85' x H: 0')
CIE Type: Direct

Input Watts (W): 6.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.333 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P865658

CATALOG NUMBER: PRLX-2002-S-935-05L-L-U-S-X-X-GREY-X

Luminous Intensity Polar Plot





TEST NUMBER: P865658

CATALOG NUMBER: PRLX-2002-S-935-05L-L-U-S-X-X-GREY-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69
4	89	79	71	66	87	77	71	65	75	69	64	73	68	64	71	66	63	61
5	82	71	63	58	80	70	63	57	68	62	57	66	61	56	65	60	56	54
6	76	65	57	51	75	64	56	51	62	55	51	61	55	50	59	54	50	48
7	71	59	51	46	70	58	51	46	57	50	45	55	49	45	54	49	45	43
8	66	54	46	41	65	54	46	41	52	46	41	51	45	41	50	45	40	39
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3858
5°	3839
10°	3788
15°	3712
20°	3626
25°	3534
30°	3434
35°	3320
40°	3205
45°	3090
50°	2922
55°	2371
60°	1123
65°	342
70°	176
75°	196
80°	195
85°	302

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3090 cd/sqm

TEST NUMBER: P865658

CATALOG NUMBER: PRLX-2002-S-935-05L-L-U-S-X-X-GREY-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	19.3	4.7
10°-20°	53.8	13.2
20°-30°	78.5	19.2
30°-40°	90.6	22.2
40°-50°	89.4	21.9
50°-60°	61.9	15.2
60°-70°	10.6	2.6
70°-80°	2.7	0.7
80°-90°	1.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	151.5	37.2
0°-40°	242.2	59.4
0°-60°	393.4	96.4
0°-90°	407.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	407.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	205	
5°	204	19
15°	191	54
25°	170	78
35°	145	91
45°	116	89
55°	72	62
65°	8	11
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P865658

CATALOG NUMBER: PRLX-2002-S-935-05L-L-U-S-X-X-GREY-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	205.4
2.5°	205.4
5°	203.6
7.5°	201.3
10°	198.6
12.5°	195.0
15°	190.9
17.5°	186.4
20°	181.4
22.5°	176.0
25°	170.5
27.5°	164.7
30°	158.3
32.5°	152.0
35°	144.8
37.5°	138.0
40°	130.7
42.5°	123.5
45°	116.3
47.5°	108.1
50°	100.0
52.5°	89.6
55°	72.4
57.5°	51.6
60°	29.9
62.5°	15.4
65°	7.7
67.5°	3.6
70°	3.2
72.5°	2.7
75°	2.7
77.5°	2.3
80°	1.8
82.5°	1.8
85°	1.4
87.5°	0.5
90°	0.0



TEST NUMBER: P865658
 CATALOG NUMBER: PRLX-2002-S-935-05L-L-U-S-X-X-GREY-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.39	14.81	13.76	15.12	15.44	13.39	14.81	13.76	15.12	15.44
	3H	13.30	14.55	13.68	14.88	15.24	13.30	14.55	13.68	14.88	15.24
	4H	13.26	14.42	13.66	14.77	15.15	13.26	14.42	13.66	14.77	15.15
	6H	13.21	14.28	13.63	14.65	15.04	13.21	14.28	13.63	14.65	15.04
	8H	13.19	14.20	13.62	14.59	14.99	13.19	14.20	13.62	14.59	14.99
	12H	13.17	14.14	13.60	14.52	14.95	13.17	14.14	13.60	14.52	14.95
4H	2H	13.25	14.41	13.65	14.76	15.14	13.25	14.41	13.65	14.76	15.14
	3H	13.18	14.11	13.59	14.51	14.92	13.18	14.11	13.59	14.51	14.92
	4H	13.13	13.96	13.57	14.38	14.82	13.13	13.96	13.57	14.38	14.82
	6H	13.10	13.82	13.56	14.26	14.73	13.10	13.82	13.56	14.26	14.73
	8H	13.08	13.75	13.55	14.20	14.67	13.08	13.75	13.55	14.20	14.67
	12H	13.07	13.67	13.56	14.15	14.62	13.07	13.67	13.56	14.15	14.62
8H	4H	13.02	13.69	13.49	14.14	14.61	13.02	13.69	13.49	14.14	14.61
	6H	12.98	13.54	13.48	14.03	14.51	12.98	13.54	13.48	14.03	14.51
	8H	12.97	13.48	13.49	13.99	14.48	12.97	13.48	13.49	13.99	14.48
	12H	12.99	13.44	13.50	13.94	14.50	12.99	13.44	13.50	13.94	14.50
12H	4H	12.98	13.58	13.47	14.06	14.53	12.98	13.58	13.47	14.06	14.53
	6H	12.93	13.44	13.45	13.95	14.44	12.93	13.44	13.45	13.95	14.44
	8H	12.94	13.40	13.46	13.89	14.46	12.94	13.40	13.46	13.89	14.46