

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P600599

Luminaire Tested: PRLX-225-90-30K-LL7-UNV-STD-X-X-WHHR-FL-X

Issue Date: 7/6/2022

Test Information

Test Method: LM-79-2019
Report Number: P600599
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2203-582-11)
Test Lab: INNOVATION CENTER
Issue Date: 7/6/2022
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PentaLux
Catalog Number: PRLX-225-90-30K-LL7-UNV-STD-X-X-WHHR-FL-X
Description: PentaLux 200 SERIES 3D PRINTED LUMINAIRE
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5665.7 lumens
Efficiency: N/A
Efficacy: 102.3 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.17
Luminous Opening: Circular (Dia: 1.33' x H: 0')
CIE Type: Direct


Input Watts (W): 55.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P600599

CATALOG NUMBER: PRLX-225-90-30K-LL7-UNV-STD-X-X-WHHR-FL-X

Luminous Intensity Polar Plot





TEST NUMBER: P600599

CATALOG NUMBER: PRLX-225-90-30K-LL7-UNV-STD-X-X-WHHR-FL-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	107	103	100	108	105	101	99	100	98	95		97	95	93		93	91	90	88
2	103	96	90	86	100	94	89	85	91	86	83		88	84	81		85	82	79	77
3	95	87	80	74	93	85	79	74	82	77	72		80	75	71		77	73	70	68
4	89	79	71	65	87	77	70	65	75	69	64		73	68	63		71	66	63	61
5	83	72	64	58	81	71	63	58	69	62	57		67	61	57		65	60	56	54
6	77	66	58	52	75	65	57	52	63	56	52		61	56	51		60	55	51	49
7	72	60	53	47	71	60	52	47	58	52	47		57	51	46		56	50	46	44
8	68	56	48	43	66	55	48	43	54	47	43		53	47	42		52	46	42	41
9	64	52	44	39	62	51	44	39	50	44	39		49	43	39		48	43	39	37
10	60	48	41	36	59	48	41	36	47	40	36		46	40	36		45	40	36	34

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	28755
5°	25535
10°	23591
15°	23012
20°	22764
25°	22713
30°	22557
35°	22362
40°	19821
45°	8069
50°	7101
55°	6869
60°	6725
65°	6445
70°	6183
75°	5936
80°	5696
85°	5590

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8069 cd/sqm



TEST NUMBER: P600599

CATALOG NUMBER: PRLX-225-90-30K-LL7-UNV-STD-X-X-WHHR-FL-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	307.2	5.4
10°-20°	815.1	14.4
20°-30°	1230.2	21.7
30°-40°	1467.0	25.9
40°-50°	758.6	13.4
50°-60°	457.5	8.1
60°-70°	350.6	6.2
70°-80°	210.3	3.7
80°-90°	69.0	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2352.6	41.5
0°-40°	3819.6	67.4
0°-60°	5035.7	88.9
0°-90°	5665.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5665.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3730	
5°	3300	307
15°	2883	815
25°	2670	1230
35°	2376	1467
45°	740	759
55°	511	458
65°	353	351
75°	199	210
85°	63	69
90°	0	



TEST NUMBER: P600599

CATALOG NUMBER: PRLX-225-90-30K-LL7-UNV-STD-X-X-WHHR-FL-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	3730.0
2.5°	3611.6
5°	3299.7
7.5°	3110.3
10°	3013.6
12.5°	2944.5
15°	2883.3
17.5°	2828.1
20°	2774.8
22.5°	2725.4
25°	2670.2
27.5°	2609.0
30°	2534.0
32.5°	2445.2
35°	2376.1
37.5°	2303.1
40°	1969.6
42.5°	1312.4
45°	740.1
47.5°	659.2
50°	592.1
52.5°	544.7
55°	511.1
57.5°	475.6
60°	436.2
62.5°	394.7
65°	353.3
67.5°	313.8
70°	274.3
72.5°	234.9
75°	199.3
77.5°	161.8
80°	128.3
82.5°	94.7
85°	63.2
87.5°	31.6
90°	0.0

(END OF REPORT)