

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865660

Luminaire Tested: PRLX-2002-S-935-10L-G-U-S-X-X-BLAK-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P865660
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2002-S-935-10L-G-U-S-X-X-BLAK-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, GLOBE LENS, TRUNCATED DOME WITH BLACK INTERIOR SHADE.
LIGHT LEVEL 2
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 282.8 lumens
Efficiency: N/A
Efficacy: 26.9 lumens/watt
Spacing Criteria (0/90/45): 1.51 / 1.51 / 1.65
Luminous Opening: Circular (Dia: 0.85' x H: 0')
CIE Type: Direct

Input Watts (W): 10.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.333 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P865660

CATALOG NUMBER: PRLX-2002-S-935-10L-G-U-S-X-X-BLAK-X

Luminous Intensity Polar Plot





TEST NUMBER: P865660

CATALOG NUMBER: PRLX-2002-S-935-10L-G-U-S-X-X-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	108	103	98	94	105	100	96	92	96	93	89		92	89	87		89	86	84	82
2	97	88	81	75	95	87	80	74	83	77	72		80	75	71		77	73	69	67
3	88	77	68	61	86	75	67	61	72	65	59		69	63	58		67	62	57	55
4	80	67	58	51	78	66	57	51	63	56	50		61	54	49		59	53	48	46
5	73	60	50	43	71	59	50	43	56	48	42		54	47	42		52	46	41	39
6	67	53	44	37	65	52	43	37	50	42	37		49	42	36		47	41	36	34
7	62	48	39	32	60	47	38	32	46	38	32		44	37	32		43	36	31	29
8	58	43	35	28	56	43	34	28	41	34	28		40	33	28		39	33	28	26
9	54	40	31	25	52	39	31	25	38	30	25		37	30	25		36	29	25	23
10	50	36	28	23	49	36	28	23	35	28	23		34	27	22		33	27	22	21

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1369
5°	1380
10°	1404
15°	1431
20°	1465
25°	1511
30°	1570
35°	1644
40°	1743
45°	1854
50°	1923
55°	1922
60°	1882
65°	1818
70°	1708
75°	1575
80°	1417
85°	1272

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 52.5°
 Luminance: 1925 cd/sqm

TEST NUMBER: P865660

CATALOG NUMBER: PRLX-2002-S-935-10L-G-U-S-X-X-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	7.0	2.5
10°-20°	20.8	7.4
20°-30°	33.7	11.9
30°-40°	45.1	15.9
40°-50°	53.7	19.0
50°-60°	52.3	18.5
60°-70°	40.4	14.3
70°-80°	23.1	8.2
80°-90°	6.7	2.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	61.6	21.8
0°-40°	106.6	37.7
0°-60°	212.6	75.2
0°-90°	282.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	282.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	73	
5°	73	7
15°	74	21
25°	73	34
35°	72	45
45°	70	54
55°	59	52
65°	41	40
75°	22	23
85°	6	7
90°	0	

TEST NUMBER: P865660

CATALOG NUMBER: PRLX-2002-S-935-10L-G-U-S-X-X-BLAK-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	72.9
2.5°	72.9
5°	73.2
7.5°	73.5
10°	73.6
12.5°	73.6
15°	73.6
17.5°	73.5
20°	73.3
22.5°	73.2
25°	72.9
27.5°	72.7
30°	72.4
32.5°	72.1
35°	71.7
37.5°	71.5
40°	71.1
42.5°	70.8
45°	69.8
47.5°	68.4
50°	65.8
52.5°	62.4
55°	58.7
57.5°	54.6
60°	50.1
62.5°	45.6
65°	40.9
67.5°	36.1
70°	31.1
72.5°	26.4
75°	21.7
77.5°	17.3
80°	13.1
82.5°	9.2
85°	5.9
87.5°	3.1
90°	0.0



TEST NUMBER: P865660
 CATALOG NUMBER: PRLX-2002-S-935-10L-G-U-S-X-X-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.84	16.57	15.21	16.88	17.20	14.84	16.57	15.21	16.88	17.20
	3H	16.67	18.24	17.05	18.56	18.92	16.67	18.24	17.05	18.56	18.92
	4H	17.34	18.82	17.74	19.17	19.54	17.34	18.82	17.74	19.17	19.54
	6H	17.84	19.22	18.25	19.58	19.97	17.84	19.22	18.25	19.58	19.97
	8H	18.00	19.32	18.43	19.71	20.11	18.00	19.32	18.43	19.71	20.11
	12H	18.12	19.38	18.55	19.77	20.19	18.12	19.38	18.55	19.77	20.19
4H	2H	15.50	16.98	15.90	17.33	17.70	15.50	16.98	15.90	17.33	17.70
	3H	17.54	18.79	17.95	19.19	19.59	17.54	18.79	17.95	19.19	19.59
	4H	18.34	19.48	18.77	19.89	20.32	18.34	19.48	18.77	19.89	20.32
	6H	18.97	19.97	19.42	20.40	20.86	18.97	19.97	19.42	20.40	20.86
	8H	19.18	20.12	19.64	20.56	21.02	19.18	20.12	19.64	20.56	21.02
	12H	19.35	20.19	19.83	20.66	21.13	19.35	20.19	19.83	20.66	21.13
8H	4H	18.67	19.60	19.13	20.04	20.50	18.67	19.60	19.13	20.04	20.50
	6H	19.42	20.20	19.91	20.68	21.15	19.42	20.20	19.91	20.68	21.15
	8H	19.71	20.40	20.21	20.91	21.39	19.71	20.40	20.21	20.91	21.39
	12H	19.95	20.57	20.45	21.06	21.61	19.95	20.57	20.45	21.06	21.61
12H	4H	18.71	19.55	19.19	20.02	20.49	18.71	19.55	19.19	20.02	20.49
	6H	19.48	20.18	19.99	20.68	21.17	19.48	20.18	19.99	20.68	21.17
	8H	19.83	20.45	20.33	20.93	21.49	19.83	20.45	20.33	20.93	21.49