

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865665

Luminaire Tested: PRLX-2002-S-935-10L-L-U-S-X-X-BRSS-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P865665  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-20)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2002-S-935-10L-L-U-S-X-X-BRSS-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, FLAT LENS, TRUNCATED DOME WITH BRASS INTERIOR SHADE.  
LIGHT LEVEL 2  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 820.1 lumens  
Efficiency: N/A  
Efficacy: 78.1 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27  
Luminous Opening: Circular (Dia: 0.85' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 10.5  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.333 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P865665

CATALOG NUMBER: PRLX-2002-S-935-10L-L-U-S-X-X-BRSS-X

### Luminous Intensity Polar Plot



TEST NUMBER: P865665

CATALOG NUMBER: PRLX-2002-S-935-10L-L-U-S-X-X-BRSS-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	111	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	80
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71
4	89	79	71	66	87	77	70	65	75	69	64	73	68	63	71	66	63
5	82	71	63	58	80	70	63	57	68	62	57	66	61	56	65	60	56
6	76	65	57	51	75	64	56	51	62	55	50	60	55	50	59	54	50
7	71	59	51	46	70	58	51	46	57	50	45	55	49	45	54	49	45
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	37	34

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	7733
5°	7712
10°	7593
15°	7442
20°	7270
25°	7107
30°	6908
35°	6680
40°	6434
45°	6200
50°	5871
55°	4772
60°	2277
65°	724
70°	346
75°	392
80°	389
85°	582

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 6200 cd/sqm

TEST NUMBER: P865665

CATALOG NUMBER: PRLX-2002-S-935-10L-L-U-S-X-X-BRSS-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	38.7	4.7
10°-20°	107.9	13.2
20°-30°	157.7	19.2
30°-40°	182.0	22.2
40°-50°	179.4	21.9
50°-60°	124.7	15.2
60°-70°	21.7	2.6
70°-80°	5.6	0.7
80°-90°	2.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	304.3	37.1
0°-40°	486.3	59.3
0°-60°	790.4	96.4
0°-90°	820.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	820.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	412	
5°	409	39
15°	383	108
25°	343	158
35°	291	182
45°	233	179
55°	146	125
65°	16	22
75°	5	6
85°	3	2
90°	0	

TEST NUMBER: P865665

CATALOG NUMBER: PRLX-2002-S-935-10L-L-U-S-X-X-BRSS-X

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	411.7
2.5°	411.7
5°	409.0
7.5°	403.5
10°	398.1
12.5°	391.8
15°	382.7
17.5°	374.6
20°	363.7
22.5°	353.8
25°	342.9
27.5°	330.2
30°	318.5
32.5°	304.9
35°	291.3
37.5°	276.9
40°	262.4
42.5°	247.9
45°	233.4
47.5°	217.1
50°	200.9
52.5°	180.0
55°	145.7
57.5°	105.0
60°	60.6
62.5°	31.7
65°	16.3
67.5°	7.2
70°	6.3
72.5°	6.3
75°	5.4
77.5°	4.5
80°	3.6
82.5°	3.6
85°	2.7
87.5°	0.9
90°	0.0



TEST NUMBER: P865665  
 CATALOG NUMBER: PRLX-2002-S-935-10L-L-U-S-X-X-BRSS-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.90	17.32	16.26	17.63	17.95	15.90	17.32	16.26	17.63	17.95
	3H	15.81	17.06	16.19	17.39	17.75	15.81	17.06	16.19	17.39	17.75
	4H	15.76	16.93	16.17	17.28	17.66	15.76	16.93	16.17	17.28	17.66
	6H	15.72	16.78	16.13	17.15	17.55	15.72	16.78	16.13	17.15	17.55
	8H	15.69	16.71	16.12	17.10	17.50	15.69	16.71	16.12	17.10	17.50
	12H	15.68	16.64	16.11	17.02	17.45	15.68	16.64	16.11	17.02	17.45
4H	2H	15.76	16.92	16.16	17.27	17.65	15.76	16.92	16.16	17.27	17.65
	3H	15.69	16.62	16.10	17.03	17.43	15.69	16.62	16.10	17.03	17.43
	4H	15.64	16.48	16.08	16.89	17.34	15.64	16.48	16.08	16.89	17.34
	6H	15.61	16.33	16.07	16.77	17.24	15.61	16.33	16.07	16.77	17.24
	8H	15.59	16.26	16.05	16.71	17.18	15.59	16.26	16.05	16.71	17.18
	12H	15.58	16.18	16.06	16.66	17.13	15.58	16.18	16.06	16.66	17.13
8H	4H	15.53	16.21	16.00	16.65	17.12	15.53	16.21	16.00	16.65	17.12
	6H	15.49	16.05	15.99	16.54	17.02	15.49	16.05	15.99	16.54	17.02
	8H	15.48	15.98	16.00	16.50	16.99	15.48	15.98	16.00	16.50	16.99
	12H	15.49	15.94	16.00	16.44	17.01	15.49	15.94	16.00	16.44	17.01
12H	4H	15.49	16.09	15.98	16.57	17.05	15.49	16.09	15.98	16.57	17.05
	6H	15.44	15.94	15.96	16.46	16.95	15.44	15.94	15.96	16.46	16.95
	8H	15.45	15.90	15.96	16.40	16.97	15.45	15.90	15.96	16.40	16.97