

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865693

Luminaire Tested: PRLX-2002-S-940-05L-G-U-S-X-X-BRSS-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P865693
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2002-S-940-05L-G-U-S-X-X-BRSS-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, GLOBE LENS, TRUNCATED DOME WITH BRASS INTERIOR SHADE.
LIGHT LEVEL 1
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 178.3 lumens
Efficiency: N/A
Efficacy: 28.8 lumens/watt
Spacing Criteria (0/90/45): 1.36 / 1.36 / 1.52
Luminous Opening: Circular (Dia: 0.85' x H: 0')
CIE Type: Direct

Input Watts (W): 6.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.333 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P865693

CATALOG NUMBER: PRLX-2002-S-940-05L-G-U-S-X-X-BRSS-X

Luminous Intensity Polar Plot





TEST NUMBER: P865693

CATALOG NUMBER: PRLX-2002-S-940-05L-G-U-S-X-X-BRSS-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	105	101	97	93	97	93	90	93	90	87	89	87	85	83
2	98	89	82	76	95	87	81	75	84	78	73	80	76	72	77	74	70	68
3	89	78	69	63	86	76	68	62	73	66	61	70	65	60	68	63	59	56
4	81	69	59	52	79	67	59	52	65	57	51	62	56	51	60	54	50	48
5	74	61	52	45	72	60	51	44	58	50	44	56	49	43	54	48	43	41
6	68	55	45	39	66	54	45	38	52	44	38	50	43	38	48	42	37	35
7	63	49	40	34	61	48	40	34	47	39	33	45	38	33	44	38	33	31
8	59	45	36	30	57	44	36	30	43	35	30	41	35	29	40	34	29	27
9	55	41	33	27	53	40	32	27	39	32	27	38	31	26	37	31	26	24
10	51	38	30	24	50	37	29	24	36	29	24	35	29	24	34	28	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	997
5°	999
10°	1007
15°	1011
20°	1019
25°	1030
30°	1045
35°	1071
40°	1108
45°	1150
50°	1169
55°	1156
60°	1120
65°	1071
70°	1011
75°	936
80°	844
85°	754

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 50°
 Luminance: 1169 cd/sqm

TEST NUMBER: P865693

CATALOG NUMBER: PRLX-2002-S-940-05L-G-U-S-X-X-BRSS-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	5.1	2.8
10°-20°	14.7	8.2
20°-30°	22.9	12.9
30°-40°	29.3	16.4
40°-50°	33.3	18.7
50°-60°	31.4	17.6
60°-70°	23.9	13.4
70°-80°	13.7	7.7
80°-90°	4.0	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	42.7	23.9
0°-40°	72.0	40.4
0°-60°	136.7	76.7
0°-90°	178.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	178.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	53	
5°	53	5
15°	52	15
25°	50	23
35°	47	29
45°	43	33
55°	35	31
65°	24	24
75°	13	14
85°	4	4
90°	0	

TEST NUMBER: P865693

CATALOG NUMBER: PRLX-2002-S-940-05L-G-U-S-X-X-BRSS-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	53.1
2.5°	53.1
5°	53.0
7.5°	53.0
10°	52.8
12.5°	52.4
15°	52.0
17.5°	51.5
20°	51.0
22.5°	50.3
25°	49.7
27.5°	48.9
30°	48.2
32.5°	47.5
35°	46.7
37.5°	46.0
40°	45.2
42.5°	44.4
45°	43.3
47.5°	41.9
50°	40.0
52.5°	37.7
55°	35.3
57.5°	32.6
60°	29.8
62.5°	27.0
65°	24.1
67.5°	21.3
70°	18.4
72.5°	15.7
75°	12.9
77.5°	10.3
80°	7.8
82.5°	5.6
85°	3.5
87.5°	1.8
90°	0.0

TEST NUMBER: P865693

CATALOG NUMBER: PRLX-2002-S-940-05L-G-U-S-X-X-BRSS-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.90	14.60	13.27	14.91	15.22	12.90	14.60	13.27	14.91	15.22
	3H	14.70	16.23	15.07	16.56	16.92	14.70	16.23	15.07	16.56	16.92
	4H	15.37	16.82	15.76	17.16	17.54	15.37	16.82	15.76	17.16	17.54
	6H	15.86	17.21	16.27	17.57	17.96	15.86	17.21	16.27	17.57	17.96
	8H	16.03	17.32	16.45	17.71	18.11	16.03	17.32	16.45	17.71	18.11
	12H	16.15	17.39	16.58	17.77	18.19	16.15	17.39	16.58	17.77	18.19
4H	2H	13.54	14.99	13.94	15.34	15.71	13.54	14.99	13.94	15.34	15.71
	3H	15.56	16.78	15.96	17.17	17.57	15.56	16.78	15.96	17.17	17.57
	4H	16.36	17.46	16.79	17.87	18.31	16.36	17.46	16.79	17.87	18.31
	6H	16.98	17.95	17.44	18.39	18.84	16.98	17.95	17.44	18.39	18.84
	8H	17.20	18.11	17.66	18.55	19.01	17.20	18.11	17.66	18.55	19.01
	12H	17.37	18.19	17.85	18.66	19.13	17.37	18.19	17.85	18.66	19.13
8H	4H	16.68	17.58	17.14	18.03	18.49	16.68	17.58	17.14	18.03	18.49
	6H	17.43	18.19	17.92	18.67	19.15	17.43	18.19	17.92	18.67	19.15
	8H	17.72	18.40	18.23	18.91	19.39	17.72	18.40	18.23	18.91	19.39
	12H	17.97	18.57	18.47	19.06	19.62	17.97	18.57	18.47	19.06	19.62
12H	4H	16.72	17.53	17.19	18.01	18.48	16.72	17.53	17.19	18.01	18.48
	6H	17.49	18.17	18.00	18.68	19.16	17.49	18.17	18.00	18.68	19.16
	8H	17.85	18.45	18.35	18.94	19.50	17.85	18.45	18.35	18.94	19.50