

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865722

Luminaire Tested: PRLX-2002-S-940-20L-L-U-S-X-X-GREY-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P865722  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-21)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2002-S-940-20L-L-U-S-X-X-GREY-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, FLAT LENS, TRUNCATED DOME WITH GRAY INTERIOR SHADE.  
LIGHT LEVEL 4  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1687.3 lumens  
Efficiency: N/A  
Efficacy: 77.4 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27  
Luminous Opening: Circular (Dia: 0.85' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 21.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.333 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P865722

CATALOG NUMBER: PRLX-2002-S-940-20L-L-U-S-X-X-GREY-X

### Luminous Intensity Polar Plot





TEST NUMBER: P865722

CATALOG NUMBER: PRLX-2002-S-940-20L-L-U-S-X-X-GREY-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69
4	89	79	71	66	87	77	71	65	75	69	64	73	68	64	71	66	63	61
5	82	71	63	58	80	70	63	57	68	62	57	66	61	56	65	60	56	54
6	76	65	57	51	75	64	56	51	62	55	51	61	55	50	59	54	50	48
7	71	59	51	46	70	58	51	46	57	50	45	55	49	45	54	49	45	43
8	66	54	46	41	65	54	46	41	52	46	41	51	45	41	50	45	40	39
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	15961
5°	15881
10°	15671
15°	15359
20°	15002
25°	14624
30°	14207
35°	13734
40°	13263
45°	12778
50°	12087
55°	9805
60°	4640
65°	1413
70°	719
75°	813
80°	811
85°	1207

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 12778 cd/sqm

TEST NUMBER: P865722

CATALOG NUMBER: PRLX-2002-S-940-20L-L-U-S-X-X-GREY-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	79.7	4.7
10°-20°	222.5	13.2
20°-30°	324.8	19.2
30°-40°	375.0	22.2
40°-50°	369.7	21.9
50°-60°	255.8	15.2
60°-70°	43.7	2.6
70°-80°	11.1	0.7
80°-90°	5.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	626.9	37.2
0°-40°	1001.9	59.4
0°-60°	1627.4	96.5
0°-90°	1687.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1687.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	850	
5°	842	80
15°	790	222
25°	706	325
35°	599	375
45°	481	370
55°	299	256
65°	32	44
75°	11	11
85°	6	5
90°	0	

TEST NUMBER: P865722

CATALOG NUMBER: PRLX-2002-S-940-20L-L-U-S-X-X-GREY-X

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	849.7
2.5°	849.7
5°	842.2
7.5°	832.8
10°	821.6
12.5°	806.6
15°	789.8
17.5°	771.1
20°	750.5
22.5°	728.0
25°	705.6
27.5°	681.2
30°	655.0
32.5°	628.8
35°	598.9
37.5°	570.8
40°	540.9
42.5°	510.9
45°	481.0
47.5°	447.3
50°	413.6
52.5°	370.6
55°	299.4
57.5°	213.4
60°	123.5
62.5°	63.6
65°	31.8
67.5°	15.0
70°	13.1
72.5°	11.2
75°	11.2
77.5°	9.4
80°	7.5
82.5°	7.5
85°	5.6
87.5°	1.9
90°	0.0



TEST NUMBER: P865722  
 CATALOG NUMBER: PRLX-2002-S-940-20L-L-U-S-X-X-GREY-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.32	19.74	18.69	20.06	20.37	18.32	19.74	18.69	20.06	20.37
	3H	18.23	19.48	18.61	19.81	20.18	18.23	19.48	18.61	19.81	20.18
	4H	18.19	19.35	18.59	19.70	20.08	18.19	19.35	18.59	19.70	20.08
	6H	18.14	19.21	18.56	19.58	19.97	18.14	19.21	18.56	19.58	19.97
	8H	18.12	19.13	18.55	19.52	19.92	18.12	19.13	18.55	19.52	19.92
	12H	18.10	19.07	18.53	19.45	19.88	18.10	19.07	18.53	19.45	19.88
4H	2H	18.18	19.34	18.58	19.69	20.07	18.18	19.34	18.58	19.69	20.07
	3H	18.11	19.04	18.52	19.45	19.85	18.11	19.04	18.52	19.45	19.85
	4H	18.06	18.89	18.50	19.31	19.76	18.06	18.89	18.50	19.31	19.76
	6H	18.03	18.75	18.49	19.20	19.66	18.03	18.75	18.49	19.20	19.66
	8H	18.01	18.68	18.48	19.13	19.60	18.01	18.68	18.48	19.13	19.60
	12H	18.00	18.60	18.49	19.08	19.55	18.00	18.60	18.49	19.08	19.55
8H	4H	17.95	18.62	18.42	19.07	19.54	17.95	18.62	18.42	19.07	19.54
	6H	17.92	18.47	18.42	18.97	19.45	17.92	18.47	18.42	18.97	19.45
	8H	17.90	18.41	18.42	18.92	19.41	17.90	18.41	18.42	18.92	19.41
	12H	17.92	18.37	18.43	18.86	19.43	17.92	18.37	18.43	18.86	19.43
12H	4H	17.91	18.51	18.40	18.99	19.46	17.91	18.51	18.40	18.99	19.46
	6H	17.86	18.37	18.38	18.88	19.37	17.86	18.37	18.38	18.88	19.37
	8H	17.88	18.33	18.39	18.82	19.39	17.88	18.33	18.39	18.82	19.39