

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P735770

Luminaire Tested: PRLX-UHBS-2436-MV-L84050-BLAK(4000K\_L36\_277V)

Issue Date: 1/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P735770  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2312-243-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-UHBS-2436-MV-L84050-BLAK(4000K\_L36\_277V)  
Description: PRENTALUX LARGE HIGH BAY LUMINAIRE WITH BLACK SHADE  
LIGHT LEVEL 3 - 36,0000 NOMINAL LUMENS  
Light Source: 4000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 22960.4 lumens  
Efficiency: N/A  
Efficacy: 99.4 lumens/watt  
Spacing Criteria (0/90/45): 1.31 / 1.31 / 1.23  
Luminous Opening: Vertical Cylinder (Dia: 1.71' x H: 1.04')  
CIE Type: Direct

Input Watts (W): 230.9  
Input Voltage (V): 277  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P735770

CATALOG NUMBER: PRLX-UHBS-2436-MV-L84050-BLAK(4000K\_L36\_277V)

### Luminous Intensity Polar Plot





TEST NUMBER: P735770

CATALOG NUMBER: PRLX-UHBS-2436-MV-L84050-BLAK(4000K\_L36\_277V)

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	109	106	104	110	107	105	102	103	101	99		99	98	96		96	95	93	91
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89	87	84	83
3	99	91	86	81	97	90	85	80	87	83	79		85	81	78		82	79	76	75
4	93	84	77	72	91	82	76	72	80	75	71		78	74	70		76	72	69	67
5	87	77	70	65	85	76	69	64	74	68	64		72	67	63		70	66	63	61
6	81	71	63	58	79	70	63	58	68	62	58		67	61	57		65	61	57	55
7	76	65	58	53	75	64	58	53	63	57	52		62	56	52		60	56	52	50
8	71	60	53	48	70	60	53	48	58	52	48		57	52	48		56	51	47	46
9	67	56	49	44	66	55	49	44	54	48	44		53	48	44		52	47	44	42
10	63	52	45	41	62	51	45	40	50	44	40		50	44	40		49	44	40	39

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	60729
5°	57170
10°	54602
15°	52839
20°	51139
25°	49738
30°	46039
35°	38483
40°	29622
45°	21651
50°	14083
55°	2255
60°	285
65°	254
70°	241
75°	209
80°	149
85°	75

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 21651 cd/sqm

TEST NUMBER: P735770

CATALOG NUMBER: PRLX-UHBS-2436-MV-L84050-BLAK(4000K\_L36\_277V)

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1238.3	5.4
10°-20°	3716.3	16.2
20°-30°	5987.1	26.1
30°-40°	6405.7	27.9
40°-50°	4458.9	19.4
50°-60°	1031.2	4.5
60°-70°	60.9	0.3
70°-80°	46.4	0.2
80°-90°	15.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	10941.7	47.7
0°-40°	17347.4	75.6
0°-60°	22837.5	99.5
0°-90°	22960.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	22960.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	12932	
5°	12951	###
15°	13129	3716
25°	13074	5987
35°	10362	6406
45°	5791	4459
55°	581	1031
65°	61	61
75°	45	46
85°	14	16
90°	0	

TEST NUMBER: P735770

CATALOG NUMBER: PRLX-UHBS-2436-MV-L84050-BLAK(4000K\_L36\_277V)

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	12931.9
2.5°	12922.7
5°	12951.4
7.5°	12981.2
10°	13018.0
12.5°	13075.4
15°	13129.3
17.5°	13140.8
20°	13124.7
22.5°	13107.5
25°	13074.2
27.5°	12922.7
30°	12296.0
32.5°	11408.7
35°	10361.8
37.5°	9217.4
40°	7980.0
42.5°	6802.3
45°	5791.0
47.5°	4817.6
50°	3711.1
52.5°	2175.2
55°	580.8
57.5°	98.7
60°	71.2
62.5°	64.3
65°	60.8
67.5°	57.4
70°	55.1
72.5°	50.5
75°	44.8
77.5°	37.9
80°	29.8
82.5°	21.8
85°	13.8
87.5°	6.9
90°	0.0

(END OF REPORT)