

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P867184

Luminaire Tested: PRLX-2004-L-927-117L-G-X-X-BLAK-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P867184
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-75)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2004-L-927-117L-G-X-X-BLAK-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, GLOBE LENS,
BELL WITH BLACK INTERIOR SHADE.
LIGHT LEVEL 7
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1405.1 lumens
Efficiency: N/A
Efficacy: 14.8 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.19
Luminous Opening: Circular (Dia: 1.67' x H: 0')
CIE Type: Direct

Input Watts (W): 95.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.333 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P867184

CATALOG NUMBER: PRLX-2004-L-927-117L-G-X-X-BLAK-X

Luminous Intensity Polar Plot





TEST NUMBER: P867184

CATALOG NUMBER: PRLX-2004-L-927-117L-G-X-X-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75
4	93	84	77	72	91	83	76	72	80	75	71	78	74	70	76	72	69	67
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61
6	81	71	64	59	80	70	63	58	68	62	58	67	62	58	65	61	57	55
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	51
8	72	60	53	49	70	60	53	48	59	53	48	58	52	48	56	51	48	46
9	67	56	49	45	66	56	49	44	55	49	44	54	48	44	53	48	44	42
10	64	52	45	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4226
5°	4242
10°	4263
15°	4269
20°	4280
25°	4314
30°	4204
35°	3753
40°	3110
45°	2331
50°	1445
55°	558
60°	120
65°	99
70°	81
75°	72
80°	80
85°	51

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2331 cd/sqm

TEST NUMBER: P867184

CATALOG NUMBER: PRLX-2004-L-927-117L-G-X-X-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.6	5.8
10°-20°	236.1	16.8
20°-30°	363.4	25.9
30°-40°	385.8	27.5
40°-50°	256.1	18.2
50°-60°	67.9	4.8
60°-70°	8.7	0.6
70°-80°	4.1	0.3
80°-90°	1.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	681.1	48.5
0°-40°	1066.9	75.9
0°-60°	1390.9	99.0
0°-90°	1405.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1405.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	856	
5°	856	82
15°	836	236
25°	792	363
35°	623	386
45°	334	256
55°	65	68
65°	8	9
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P867184

CATALOG NUMBER: PRLX-2004-L-927-117L-G-X-X-BLAK-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	856.5
2.5°	856.5
5°	856.5
7.5°	855.6
10°	850.9
12.5°	844.3
15°	835.8
17.5°	825.4
20°	815.1
22.5°	803.8
25°	792.5
27.5°	775.6
30°	737.9
32.5°	687.1
35°	623.1
37.5°	556.3
40°	482.8
42.5°	409.4
45°	334.1
47.5°	259.8
50°	188.2
52.5°	123.3
55°	64.9
57.5°	21.6
60°	12.2
62.5°	10.4
65°	8.5
67.5°	7.5
70°	5.6
72.5°	4.7
75°	3.8
77.5°	2.8
80°	2.8
82.5°	1.9
85°	0.9
87.5°	0.9
90°	0.0

TEST NUMBER: P867184

CATALOG NUMBER: PRLX-2004-L-927-117L-G-X-X-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.18	0.50	0.00	0.00	0.00	0.18	0.50
	3H	0.00	0.19	0.00	0.52	0.88	0.00	0.19	0.00	0.52	0.88
	4H	0.00	0.27	0.00	0.62	1.00	0.00	0.27	0.00	0.62	1.00
	6H	0.00	0.31	0.00	0.68	1.07	0.00	0.31	0.00	0.68	1.07
	8H	0.00	0.31	0.00	0.71	1.11	0.00	0.31	0.00	0.71	1.11
	12H	0.00	0.29	0.00	0.67	1.10	0.00	0.29	0.00	0.67	1.10
4H	2H	0.00	0.00	0.00	0.02	0.41	0.00	0.00	0.00	0.02	0.41
	3H	0.00	0.09	0.00	0.50	0.91	0.00	0.09	0.00	0.50	0.91
	4H	0.00	0.24	0.00	0.66	1.11	0.00	0.24	0.00	0.66	1.11
	6H	0.00	0.38	0.25	0.83	1.30	0.00	0.38	0.25	0.83	1.30
	8H	0.00	0.44	0.35	0.89	1.36	0.00	0.44	0.35	0.89	1.36
	12H	0.00	0.40	0.40	0.89	1.37	0.00	0.40	0.40	0.89	1.37
8H	4H	0.00	0.11	0.03	0.56	1.04	0.00	0.11	0.03	0.56	1.04
	6H	0.00	0.35	0.40	0.85	1.33	0.00	0.35	0.40	0.85	1.33
	8H	0.05	0.46	0.58	0.98	1.47	0.05	0.46	0.58	0.98	1.47
	12H	0.13	0.50	0.65	0.99	1.57	0.13	0.50	0.65	0.99	1.57
12H	4H	0.00	0.03	0.03	0.51	0.99	0.00	0.03	0.03	0.51	0.99
	6H	0.00	0.30	0.42	0.82	1.31	0.00	0.30	0.42	0.82	1.31
	8H	0.09	0.45	0.61	0.95	1.53	0.09	0.45	0.61	0.95	1.53