

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P867186

Luminaire Tested: PRLX-2004-L-927-117L-G-X-X-GREY-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P867186
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-74)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2004-L-927-117L-G-X-X-GREY-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, GLOBE LENS,
BELL WITH GRAY INTERIOR SHADE.
LIGHT LEVEL 7
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2076.2 lumens
Efficiency: N/A
Efficacy: 21.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.15
Luminous Opening: Circular (Dia: 1.67' x H: 0')
CIE Type: Direct

Input Watts (W): 95.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.333 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P867186

CATALOG NUMBER: PRLX-2004-L-927-117L-G-X-X-GREY-X

Luminous Intensity Polar Plot





TEST NUMBER: P867186

CATALOG NUMBER: PRLX-2004-L-927-117L-G-X-X-GREY-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	98		98	96	95		95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86		90	87	84		87	85	82	80
3	97	89	83	78	95	88	82	77	85	80	76		82	78	75		80	77	74	72
4	91	81	74	69	89	80	74	69	78	72	68		76	71	67		74	70	66	64
5	85	75	67	62	83	73	67	62	72	66	61		70	64	60		68	63	60	58
6	79	68	61	56	78	68	61	56	66	60	55		64	59	55		63	58	54	53
7	74	63	56	51	73	62	55	50	61	55	50		60	54	50		58	53	49	48
8	70	58	51	46	68	58	51	46	56	50	46		55	50	45		54	49	45	44
9	66	54	47	42	64	54	47	42	53	46	42		52	46	42		51	45	42	40
10	62	50	43	39	61	50	43	39	49	43	39		48	42	39		47	42	38	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	6209
5°	6214
10°	6191
15°	6111
20°	6004
25°	5862
30°	5566
35°	4955
40°	4183
45°	3290
50°	2319
55°	1352
60°	817
65°	703
70°	625
75°	557
80°	509
85°	481

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3290 cd/sqm

TEST NUMBER: P867186

CATALOG NUMBER: PRLX-2004-L-927-117L-G-X-X-GREY-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	119.2	5.7
10°-20°	337.1	16.2
20°-30°	493.8	23.8
30°-40°	510.8	24.6
40°-50°	362.7	17.5
50°-60°	151.0	7.3
60°-70°	60.9	2.9
70°-80°	31.4	1.5
80°-90°	9.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	950.1	45.8
0°-40°	1460.9	70.4
0°-60°	1974.5	95.1
0°-90°	2076.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2076.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1258	
5°	1255	119
15°	1196	337
25°	1077	494
35°	823	511
45°	472	363
55°	157	151
65°	60	61
75°	29	31
85°	8	9
90°	0	

TEST NUMBER: P867186

CATALOG NUMBER: PRLX-2004-L-927-117L-G-X-X-GREY-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	1258.4
2.5°	1257.5
5°	1254.6
7.5°	1248.1
10°	1235.8
12.5°	1217.9
15°	1196.3
17.5°	1171.8
20°	1143.6
22.5°	1112.5
25°	1076.8
27.5°	1036.3
30°	977.0
32.5°	905.5
35°	822.6
37.5°	737.0
40°	649.4
42.5°	560.0
45°	471.5
47.5°	385.0
50°	302.1
52.5°	227.8
55°	157.2
57.5°	104.5
60°	82.8
62.5°	71.5
65°	60.2
67.5°	51.8
70°	43.3
72.5°	35.8
75°	29.2
77.5°	23.5
80°	17.9
82.5°	13.2
85°	8.5
87.5°	3.8
90°	0.0

TEST NUMBER: P867186
 CATALOG NUMBER: PRLX-2004-L-927-117L-G-X-X-GREY-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.28	9.57	8.64	9.88	10.19	8.28	9.57	8.64	9.88	10.19
	3H	9.35	10.49	9.73	10.82	11.18	9.35	10.49	9.73	10.82	11.18
	4H	9.74	10.80	10.15	11.15	11.54	9.74	10.80	10.15	11.15	11.54
	6H	10.05	11.02	10.46	11.39	11.78	10.05	11.02	10.46	11.39	11.78
	8H	10.15	11.07	10.58	11.46	11.87	10.15	11.07	10.58	11.46	11.87
	12H	10.22	11.10	10.65	11.48	11.91	10.22	11.10	10.65	11.48	11.91
4H	2H	8.59	9.64	8.99	9.99	10.38	8.59	9.64	8.99	9.99	10.38
	3H	9.87	10.73	10.29	11.14	11.54	9.87	10.73	10.29	11.14	11.54
	4H	10.38	11.15	10.82	11.57	12.02	10.38	11.15	10.82	11.57	12.02
	6H	10.81	11.47	11.27	11.92	12.39	10.81	11.47	11.27	11.92	12.39
	8H	10.96	11.57	11.43	12.02	12.49	10.96	11.57	11.43	12.02	12.49
	12H	11.07	11.61	11.55	12.10	12.57	11.07	11.61	11.55	12.10	12.57
8H	4H	10.54	11.16	11.01	11.60	12.08	10.54	11.16	11.01	11.60	12.08
	6H	11.07	11.58	11.58	12.07	12.56	11.07	11.58	11.58	12.07	12.56
	8H	11.29	11.74	11.81	12.26	12.75	11.29	11.74	11.81	12.26	12.75
	12H	11.48	11.88	11.99	12.38	12.95	11.48	11.88	11.99	12.38	12.95
12H	4H	10.54	11.08	11.02	11.56	12.04	10.54	11.08	11.02	11.56	12.04
	6H	11.09	11.55	11.61	12.06	12.55	11.09	11.55	11.61	12.06	12.55
	8H	11.36	11.76	11.88	12.26	12.83	11.36	11.76	11.88	12.26	12.83