

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P867194

Luminaire Tested: PRLX-2004-L-927-133L-G-X-X-GREY-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P867194
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-74)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2004-L-927-133L-G-X-X-GREY-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, GLOBE LENS,
BELL WITH GRAY INTERIOR SHADE.
LIGHT LEVEL 8
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2377.4 lumens
Efficiency: N/A
Efficacy: 21.3 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.15
Luminous Opening: Circular (Dia: 1.67' x H: 0')
CIE Type: Direct

Input Watts (W): 111.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.333 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P867194

CATALOG NUMBER: PRLX-2004-L-927-133L-G-X-X-GREY-X

Luminous Intensity Polar Plot





TEST NUMBER: P867194

CATALOG NUMBER: PRLX-2004-L-927-133L-G-X-X-GREY-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	98		98	96	95		95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86		90	87	84		87	85	82	80
3	97	89	83	78	95	88	82	77	85	80	76		82	78	75		80	77	74	72
4	91	81	74	69	89	80	74	69	78	72	68		76	71	67		74	70	66	64
5	85	75	67	62	83	73	67	62	72	66	61		70	64	60		68	63	60	58
6	79	68	61	56	78	68	61	56	66	60	55		64	59	55		63	58	54	53
7	74	63	56	51	73	62	55	50	61	55	50		60	54	50		58	53	49	48
8	70	58	51	46	68	58	51	46	56	50	46		55	50	45		54	49	45	44
9	66	54	47	42	64	54	47	42	53	46	42		52	46	42		51	45	42	40
10	62	50	43	39	61	50	43	39	49	43	39		48	42	39		47	42	38	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	7110
5°	7115
10°	7090
15°	6997
20°	6875
25°	6712
30°	6373
35°	5674
40°	4790
45°	3768
50°	2656
55°	1548
60°	935
65°	806
70°	716
75°	637
80°	582
85°	549

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3768 cd/sqm

TEST NUMBER: P867194

CATALOG NUMBER: PRLX-2004-L-927-133L-G-X-X-GREY-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.5	5.7
10°-20°	386.0	16.2
20°-30°	565.4	23.8
30°-40°	584.9	24.6
40°-50°	415.3	17.5
50°-60°	172.9	7.3
60°-70°	69.8	2.9
70°-80°	36.0	1.5
80°-90°	10.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1087.9	45.8
0°-40°	1672.8	70.4
0°-60°	2261.0	95.1
0°-90°	2377.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2377.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1441	
5°	1437	136
15°	1370	386
25°	1233	565
35°	942	585
45°	540	415
55°	180	173
65°	69	70
75°	33	36
85°	10	11
90°	0	

TEST NUMBER: P867194

CATALOG NUMBER: PRLX-2004-L-927-133L-G-X-X-GREY-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	1441.0
2.5°	1439.9
5°	1436.7
7.5°	1429.1
10°	1415.1
12.5°	1394.6
15°	1369.9
17.5°	1341.8
20°	1309.5
22.5°	1273.9
25°	1233.0
27.5°	1186.6
30°	1118.7
32.5°	1036.8
35°	942.0
37.5°	843.9
40°	743.7
42.5°	641.3
45°	540.0
47.5°	440.8
50°	346.0
52.5°	260.8
55°	180.0
57.5°	119.6
60°	94.8
62.5°	81.9
65°	69.0
67.5°	59.3
70°	49.6
72.5°	41.0
75°	33.4
77.5°	26.9
80°	20.5
82.5°	15.1
85°	9.7
87.5°	4.3
90°	0.0



TEST NUMBER: P867194
 CATALOG NUMBER: PRLX-2004-L-927-133L-G-X-X-GREY-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.75	10.03	9.11	10.35	10.66	8.75	10.03	9.11	10.35	10.66
	3H	9.82	10.95	10.20	11.28	11.65	9.82	10.95	10.20	11.28	11.65
	4H	10.21	11.27	10.62	11.62	12.00	10.21	11.27	10.62	11.62	12.00
	6H	10.52	11.49	10.93	11.86	12.25	10.52	11.49	10.93	11.86	12.25
	8H	10.62	11.54	11.05	11.93	12.33	10.62	11.54	11.05	11.93	12.33
	12H	10.69	11.57	11.12	11.95	12.38	10.69	11.57	11.12	11.95	12.38
4H	2H	9.05	10.11	9.46	10.46	10.85	9.05	10.11	9.46	10.46	10.85
	3H	10.34	11.20	10.76	11.61	12.01	10.34	11.20	10.76	11.61	12.01
	4H	10.85	11.62	11.29	12.04	12.48	10.85	11.62	11.29	12.04	12.48
	6H	11.28	11.94	11.74	12.39	12.85	11.28	11.94	11.74	12.39	12.85
	8H	11.42	12.04	11.89	12.49	12.96	11.42	12.04	11.89	12.49	12.96
	12H	11.54	12.08	12.02	12.56	13.04	11.54	12.08	12.02	12.56	13.04
8H	4H	11.01	11.63	11.48	12.07	12.55	11.01	11.63	11.48	12.07	12.55
	6H	11.54	12.05	12.04	12.54	13.03	11.54	12.05	12.04	12.54	13.03
	8H	11.76	12.21	12.28	12.73	13.22	11.76	12.21	12.28	12.73	13.22
	12H	11.95	12.35	12.46	12.84	13.42	11.95	12.35	12.46	12.84	13.42
12H	4H	11.00	11.55	11.49	12.03	12.51	11.00	11.55	11.49	12.03	12.51
	6H	11.56	12.02	12.08	12.53	13.02	11.56	12.02	12.08	12.53	13.02
	8H	11.83	12.23	12.35	12.73	13.30	11.83	12.23	12.35	12.73	13.30